



NBNC75BFG7

The rearTWIST HD BNC cable connector offers a true 75 Ω design and is perfectly suitable for HD applications.

The patented rearTWIST boot guarantees easy access even in high density applications and offers color coding.

Suitable cables:

Argosy Image 360, Belden 1855ENH, Bryant BD SD01, CAE HD0628LSZH, Canford SDV, Canford SDV-LFH, Canford SDV-X-LFH, Cordial CVI 06-28, Cordial CVI 06-28HD, Cordial CVI 06-28HD-FRNC, Cordial CVI 3-7, Draka 0.6/2.8 AF, Draka 0.6 L/2.8 AF, Extron BNC-5RC, Fuzion SD-1, Klotz V06/28, Klotz VMXx75Y, Kabeltronik HFV 0.6/2.8 AF-FRNC, Kabeltronik MVP 5x 0.6/2.8 AF-FRNC, Nexans HF 75 0,6/2,9 02YS(ST)CH, Percon VK5, Quadtronics CABPGHD70MW-500, Sommer 600-0101M, Sommer 600-0104M, Tesca Supra

Crimp size:

Pin: 1.6 mm (square)

Shield: 5.0 mm (hex)

Features & Benefits

- “rearTWIST Principle” locking/unlocking using the easily accessible soft touch boot (Patent DE 100 48507)
- True 75 Ω design meets the stringent HDTV / DVD requirements
- Snug-fit center pin insert provides tactile feedback
- Excellent cable protection and retention
- Accessories include color coded boots in 10 standard colors, crimp tool and dies
- Ideal for recessed bulkheads where access to the “head” of the connector might be an issue. These connectors turn from the back and not the front.
- Leading area: Avoids tilting due to side forces to protect contacts from deformation. Guarantees a lifetime of min. 1000 mating cycles!
- Shield and jacket crimp technology prevents the problem of an exposed grounding braid on cable assemblies
- Precise Swiss machined brass parts for outstanding durability

Technical Information

Product	
Title	NBNC75BFG7
Connection Type	BNC 75 Ω
Gender	male

Electrical	
Contact resistance	≤ 3 mΩ (inner)
Contact resistance	≤ 2 mΩ (outer)
Dielectric strength	1,5 kVdc
Impedance	75 Ω
Insulation resistance	> 5 GΩ
Rated voltage	<50 V
VSWR	≤1.050/>32 dB up to 1 GHz ≤1.065/>30 dB up to 2 GHz ≤1.100/>26 dB up to 3 Ghz

Mechanical

Cable O.D.	4.7 mm
Cable retention	> 30 N (Center)
Crimp size	5 Hex crimp (shield) acc. MIL22520/5-43(B)
Crimp size (pin)	1,6 Square crimp (pin) acc. IEC 60803 (die designation 2)
Insertion force	< 25 N
Lifetime	> 1000 mating cycles
Wiresize	
Locking device	Bayonett
Cable anchoring	Jacket crimping

Material

Contacts	Brass (CuZn35Pb2), 0.2 µm AuCo (Center contact)
Insert	PTFE
Shell	Brass (CuZn39Pb3)
Shell plating	Optalloy®

Environmental

Temperature range	-30 °C to +85 °C
Contact crimpability	Complies with IEC 60803 and IEC 60352-2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Neutrik:](#)

[NBNC75BFG7](#)