

F

E

D

C

B

A

MATERIAL NUMBER	ENG. NUMBER	LENGTH
1201088538	E10A00716M020	2M (6' 7")
1201088539	E10A00716M050	5M (16; 5")
1201088540	E10A00716M100	10M (32' 10")
1201088541	E10A00716M200	20M (65' 7")

CHART


CABLE LENGTH TOLERANCES	
>.3M [1FT]:	+19mm-0 [+.75in-0]
.3 - .9M [1 - 3FT]:	+44.5mm-0 [+1.75in-0]
.9 - 1.8M [3 - 6FT]:	+55.6mm-0 [+2.19in-0]
1.8 - 3.7M [6 - 12FT]:	+88.9mm-0 [+3.50in-0]
3.7 - 7.3M [12 - 24FT]:	+165.1mm-0 [+6.50in-0]
7.3-14.6M [24 - 48FT]:	+317.5mm-0 [+12.50in-0]
14.6 - 30.5M [48-100FT]:	+622.3mm-0 [+24.50in-0]
OVER 30M [100FT]	+2% OF FINISHED LENGTH

CABLE TYPE

E10A00716MXXX

LENGTH


M005 - 0.5M
M050 - 5M
M200 - 20M



ADDITIONAL CABLE INFORMATION


PHYSICAL CHARACTERISTICS:	
CONDUCTOR SIZE	24AWG 2 PAIR (19/0.12mm) BARE COPPER
INSULATION MATERIAL	POLYOLEFIN
SHIELD/BRAID	TINNED COPPER 85% COVERAGE
JACKET MATERIAL	PUR (TEAL)
CONDUCTOR	ORANGE, ORANGE-WHITE & GREEN, GREEN-WHITE
TAPE	ALUMINUM-POLYESTER

CABLE:	
TEMPERATURE RATING (STORAGE)	-40 / +80°C
TEMPERATURE RATING (OPERATION)	-20 / +50°C
WELD SLAG RESISTANCE	YES, S-300 MOLEX TEST
FREE SUBSTANCE'S	FCKW, SILICONE, AND PB
FIRE PERFORMANCE	IEC60332-1, UL1581
OIL RESISTANCE	ISO6722, UL758/2556



WIRING DIAGRAM

- NOTES:
- 1. MATERIAL: AS NOTED
 - 2. FINISH: AS NOTED
 - 3. ELECTRICAL:
VOLTAGE: 125V
CURRENT: 1.5A
 - 4. TEMP RATING: AS NOTED
 - PROTECTION: IP67 (WHEN MATED)
 - 6. ALL DIMS ARE FOR REFERENCE
UNLESS NOTED OTHERWISE



FACE VIEW - MALE

6	WRAP LABEL	VINYL	BLACK/YELLOW
5	INSERT	PUR	BLACK
4	M12 MALE PIN CONTACT	COPPER ALLOY	GOLD PLATED
3	M12 COUPLING NUT	BRASS	NICKEL PLATED
2	OVERMOLD	PUR	BLACK
1	CABLE: 2 X 2, 24 AWG, SHIELDED	PUR	TEAL
ITEM	DESCRIPTION	MATERIAL	FINISH

RELEASED EC NO: IPG2018-0091 DRWN: RSTONE 2017/08/04 CHKD: --- APPR: BWOODMAN2017/08/11	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽C=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE IN/MM		SCALE ---	DESIGN UNITS INCH	THIRD ANGLE PROJECTION 				
				mm	INCH	DRAWN BY RSTONE	DATE 2017/08/04	TITLE MICRO-CHANGE CABLE ASSY D-CODE, MALE 90D 2TP X 24AWG PUR TEAL						
			4 PLACES	±---	±---	CHECKED BY ----	DATE ---							
			3 PLACES	±---	±---	APPROVED BY BWOODMAN		DATE 2017/08/11		MOLEX INCORPORATED				
			2 PLACES	±---	±---	MATERIAL NO. SEE CHART								
			1 PLACE	±---	±---	SIZE B			THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					
			ANGULAR ±---°											
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS														
1	REV													

F

E

D

C

B

A

MATERIAL NUMBER	ENG. NUMBER	LENGTH
1201088538	E10A00716M020	2M (6' 7")
1201088539	E10A00716M050	5M (16; 5")
1201088540	E10A00716M100	10M (32' 10")
1201088541	E10A00716M200	20M (65' 7")

CHART


CABLE LENGTH TOLERANCES	
>.3M [1FT]:	+19mm-0 [+.75in-0]
.3 - .9M [1 - 3FT]:	+44.5mm-0 [+1.75in-0]
.9 - 1.8M [3 - 6FT]:	+55.6mm-0 [+2.19in-0]
1.8 - 3.7M [6 - 12FT]:	+88.9mm-0 [+3.50in-0]
3.7 - 7.3M [12 - 24FT]:	+165.1mm-0 [+6.50in-0]
7.3-14.6M [24 - 48FT]:	+317.5mm-0 [+12.50in-0]
14.6 - 30.5M [48-100FT]:	+622.3mm-0 [+24.50in-0]
OVER 30M [100FT]	+2% OF FINISHED LENGTH

CABLE TYPE

E10A00716MXXX

LENGTH


M005 - 0.5M
M050 - 5M
M200 - 20M



ADDITIONAL CABLE INFORMATION


PHYSICAL CHARACTERISTICS:	
CONDUCTOR SIZE	24AWG 2 PAIR (19/0.12mm) BARE COPPER
INSULATION MATERIAL	POLYOLEFIN
SHIELD/BRAID	TINNED COPPER 85% COVERAGE
JACKET MATERIAL	PUR (TEAL)
CONDUCTOR	ORANGE, ORANGE-WHITE & GREEN, GREEN-WHITE
TAPE	ALUMINUM-POLYESTER

CABLE:	
TEMPERATURE RATING (STORAGE)	-40 / +80°C
TEMPERATURE RATING (OPERATION)	-20 / +50°C
WELD SLAG RESISTANCE	YES, S-300 MOLEX TEST
FREE SUBSTANCE'S	FCKW, SILICONE, AND PB
FIRE PERFORMANCE	IEC60332-1, UL1581
OIL RESISTANCE	ISO6722, UL758/2556



WIRING DIAGRAM

- NOTES:
1. MATERIAL: AS NOTED
 2. FINISH: AS NOTED
 3. ELECTRICAL:
VOLTAGE: 125V
CURRENT: 1.5A
 4. TEMP RATING: AS NOTED
 - PROTECTION: IP67 (WHEN MATED)
 6. ALL DIMS ARE FOR REFERENCE
UNLESS NOTED OTHERWISE



FACE VIEW - MALE

6	WRAP LABEL	VINYL	BLACK/YELLOW
5	INSERT	PUR	BLACK
4	M12 MALE PIN CONTACT	COPPER ALLOY	GOLD PLATED
3	M12 COUPLING NUT	BRASS	NICKEL PLATED
2	OVERMOLD	PUR	BLACK
1	CABLE: 2 X 2, 24 AWG, SHIELDED	PUR	TEAL
ITEM	DESCRIPTION	MATERIAL	FINISH

RELEASED EC NO: IPG2018-0091 DRWN: RSTONE 2017/08/04 CHKD: ! APPR: BWOODMAN2017/08/11	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽C=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE IN/MM		SCALE ---	DESIGN UNITS INCH	THIRD ANGLE PROJECTION ⊙ □			
				mm	INCH	DRAWN BY RSTONE	DATE 2017/08/04	TITLE MICRO-CHANGE CABLE ASSY D-CODE, MALE 90D 2TP X 24AWG PUR TEAL					
			4 PLACES	±---	±---	CHECKED BY ----	DATE ---						
			3 PLACES	±---	±---								
			2 PLACES	±---	±---	APPROVED BY BWOODMAN		DATE 2017/08/11	molex	MOLEX INCORPORATED			
			1 PLACE	±---	±---	ANGULAR ±---°							
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			MATERIAL NO. SEE CHART		DOCUMENT NO. SD-120108-100				SHEET NO. 1 OF 1	
						SIZE B	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						
1	REV												

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1201088538