



NBNC75BTS11

The rearTWIST HD BNC cable connector offers a true 75 Ω design and is perfectly suitable for HD applications.

The patented rearTWIST boot guarantees easy access even in high density applications and offers color coding.

Suitable cable:

CAE HD10460LSZH, Eupen 705 CRT 5V-HS, Tesca Prima

Crimp size:

Pin: 1.6 mm (square)

Shield: 7.01 mm (hex)

Features & Benefits

- "rearTWIST Principle" locking/unlocking using the easily accessible soft touch boot (Patent DE 100 48507)
- True 75 Ω design meets the stringent HDTV / DVD requirements
- Snug-fit center pin insert provides tactile feedback
- Excellent cable protection and retention
- Accessories include color coded boots in 10 standard colors, crimp tool and dies
- Ideal for recessed bulkheads where access to the "head" of the connector might be an issue. These connectors turn from the back and not the front.
- Leading area: Avoids tilting due to side forces to protect contacts from deformation. Guarantees a lifetime of min. 1000 mating cycles!
- Shield and jacket crimp technology prevents the problem of an exposed grounding braid on cable assemblies
- Precise Swiss machined brass parts for outstanding durability

Technical Information

Product	
Title	NBNC75BTS11
Connection Type	BNC 75 Ω
Gender	male

Electrical	
Contact resistance	$\leq 3 \text{ m}\Omega$ (inner)
Contact resistance	$\leq 2 \text{ m}\Omega$ (outer)
Dielectric strength	1,5 kVdc
Impedance	75 Ω
Insulation resistance	$> 5 \text{ G}\Omega$
Rated voltage	$<50 \text{ V}$
VSWR	$\leq 1.050 / >32 \text{ dB}$ up to 1 GHz $\leq 1.065 / >30 \text{ dB}$ up to 2 GHz $\leq 1.100 / >26 \text{ dB}$ up to 3 Ghz

Mechanical

Cable O.D.	6.9 mm
Cable retention	> 30 N (Center)
Crimp size	7,01 Hex crimp (shield) acc. IEC 60803 (die designation F)
Crimp size (pin)	1,6 Square crimp (pin) acc. IEC 60803 (die designation 2)
Insertion force	< 25 N
Lifetime	> 1000 mating cycles
Wiresize	
Locking device	Bayonett
Cable anchoring	Jacket crimping

Material

Contacts	Brass (CuZn35Pb2), 0.2 µm AuCo (Center contact)
Insert	PTFE
Shell	Brass (CuZn39Pb3)
Shell plating	Optalloy®

Environmental

Temperature range	-30 °C to +85 °C
Contact crimpability	Complies with IEC 60803 and IEC 60352-2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Neutrik:](#)

[NBNC75BTY11](#) [NBNC75BTS11](#)