

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION


Part Number: 0919992041
Status: Active
Overview: RAST Connector System
Description: Appli-Mate RAST 5 Header, Vertical, 5 Circuits, Tin (Sn) Plating, Glow-Wire Capable

Documents:
[Drawing \(PDF\)](#) [Packaging Specification PK-90858-001-001 \(PDF\)](#)
[Product Specification PS-99020-0037-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification
CSA LR19980
UL E29179
Application tooling part link
Application Tooling Part Link 216658-0200

General
Product Family PCB Headers
Series 91999
Application Power, Wire-to-Board
Comments "*****This Molex product is manufactured from material that has the following ratings, tested by independent agencies:. a) A Glow Wire Ignition Temperature (GWIT) of at least 775 deg C per IEC 60695-2-13.. b) A Glow Wire Flammability Index (GWFI) above 850 deg C per IEC 60695-2-12.and hence complies with the requirements set out in the International Standard IEC 60335-1 5th edition - household and similar electrical appliances - safety, section 30 Resistance to heat and fire. <P><P> The customers using this product must determine its suitability for use in their particular application through testing or other acceptable means as described in end-product glow-wire flammability test standard IEC 60695-2-11 and any applicable product end-use standard(s). <P> If it is determined during the customer's evaluation of suitability, that higher performance is required, please contact Molex for possible product options."*****
[RAST Connector System](#)
Overview RAST 5
Product Name 884982449954
UPC

Physical
Breakaway No
Circuits (Loaded) 5
Circuits (maximum) 5
Color - Resin Natural
Durability (mating cycles max) 10
First Mate / Last Break No
Flammability 94V-0
Glow-Wire Capable Yes
Guide to Mating Part No
Keying to Mating Part Yes
Lock to Mating Part Yes
Material - Metal Brass
Material - Plating Mating Tin
Material - Plating Termination Nickel



Series image - Reference only

EU ELV
Not Relevant
EU RoHS **China RoHS**
Compliant
REACH SVHC
Not Contained Per -
D(2021)4569-DC (8
July 2021)
Halogen-Free
Status
Not Low-Halogen
For more information, please visit [Contact US](#)
China ROHS Green Image
ELV Not Relevant
RoHS Phthalates Not Contained

Search Parts in this Series
91999 Series

Mates With
Appli-Mate RAST 5 IDT Housing 91778 ,
91779

Use With
RAST Standard Interface

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.
Global

Description	Product #
RAST 5 Power	2166580200
Semi-Automatic IDC Machine	

Material - Resin	Nylon
Net Weight	5.631/g
Number of Rows	1
Orientation	Vertical
PC Tail Length	3.90mm
PCB Locator	Yes
PCB Retention	None
PCB Thickness - Recommended	1.40mm
Packaging Type	Bag
Pitch - Mating Interface	5.00mm
Pitch - Termination Interface	5.00mm
Shrouded	Fully
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-20° to +120°C
Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	16.0A
Voltage - Maximum	250V AC
Solder Process Data	
Lead-freeProcess Capability	WAVE
Material Info	
Reference - Drawing Numbers	
Packaging Specification	PK-90858-001-001
Product Specification	PS-99020-0037-001

This document was generated on 10/04/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

91999-2041