



## NC5FX

PHASE OUT

direct replacement / successor: NC5FXX

5 pole female cable connector with Nickel housing and silver contacts.

The "industry standard" XLR cable connector, easy to assemble with only 4 parts and no screws.

Compact design with sturdy diecast shell, fibreglass reinforced hard plastic insert and chuck type strain relief for secure clamping of all cables.

## Features & Benefits

- ✓ Rugged zinc diecast shell, long lasting and durable
- ✓ Chuck type strain relief system for secure clamping of cables
- ✓ Boot with rubber gland gives high protection against bending stresses
- ✓ Coloured rings and boots available for coding and marking
- ✓ UL recognized components

## Technical Information

Product	
Title	NC5FX
Connection Type	XLR
Gender	female

## Electrical

Capacitance between contacts	$\leq 7$ pF
Contact resistance	$\leq 3$ m $\Omega$
Dielectric strength	1,5 kVdc
Insulation resistance	> 10 G $\Omega$ (initial)
Rated current per contact	7,5 A
Rated voltage	< 50 V

## Mechanical

Cable O.D.	3.5 - 8.0 mm
Insertion force	$\leq 20$ N
Withdrawal force	$\leq 20$ N
Lifetime	> 1000 mating cycles
Wiresize	max. 1.0 mm <sup>2</sup>
Wiresize	max. 18 AWG
Wiring	Solder contacts
Locking device	Latch lock

Material	
Boot	Polyurethan
Contact plating	2 µm Ag
Contacts	Brass (CuZn39Pb3)
Insert	Polyamide (PA66)
Locking element	St3K32 (latch) / Ck 67 (spring)
Locking element plating	Nickel
Shell	Zinc diecast (ZnAl4Cu1)
Shell plating	Nickel
Strain relief	Polyacetal (POM)

Environmental	
Approvals	UL
Flammability	UL 94 V-0
Standard compliance	IEC 61076-2-103
Protection class	IP 40
Solderability	Complies with IEC 68-2-20
Temperature range	-30 °C to +80 °C

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Neutrik:](#)

[NC5FX](#)