

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0011184448](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: Conductor Punch

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family Application Tooling
Series [207126](#)
Comments See Tooling Specification (PDF) Above
Function Cutter
Geographic Area Global
Level of Automation Semi-Automatic
More Detailed Tech Information applicationtooling@molex.com
Overview [Application Tooling](#)
Product Name N/A
Tool Type Applicator
UPC 800753889514
Warranty Disclaimer CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info
Engineering Number 60739A101

Reference - Drawing Numbers
Application Tooling Documents ATS-STANDARD-PARTS-001



Series image - Reference only

EU ELV
Not Relevant

EU RoHS **China RoHS**
Compliant
REACH SVHC
Not Contained Per -
D(2021)4569-DC (8
July 2021)
Halogen-Free
Status
Not Relevant

For more information, please visit [Contact US](#)

China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[207126](#) Series

Use With
[11182080](#) , [11182232](#) , [11183075](#) ,
[638031000](#) , [638031070](#) , [638031200](#) ,
[638031270](#) , [638821000](#) , [638821070](#) ,
[6388212 00](#) , [638821270](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

11-18-4448