

Product Specification

NHD-10.1-HDMI-A-RSXP

TFT Liquid Crystal Display

NHD-	Newhaven Display
10.1-	10.1" Diagonal
HDMI-	HDMI Interface
A-	1024x600 Resolution, HDMI Audio Support
RSXP-	IPS Display

Table of Contents

Document Revision History.....	2
Mechanical Drawing	3
Schematics	4
Electrical Characteristics	8
HDMI Receiver Information	8
Audio Amplifier Information	8
Technical Resource	8
EDID Array.....	9
EDID Timing.....	9
Quality Information.....	10

Additional Resources

- **Support Forum:** <https://support.newhavendisplay.com/hc/en-us/community/topics>
- **GitHub:** <https://github.com/newhavendisplay>
- **Example Code:** <https://support.newhavendisplay.com/hc/en-us/categories/4409527834135-Example-Code/>
- **Knowledge Center:** https://www.newhavendisplay.com/knowledge_center.html
- **Quality Center:** https://www.newhavendisplay.com/quality_center.html
- **Precautions for using LCDs/LCMs:** <https://www.newhavendisplay.com/specs/precautions.pdf>
- **Warranty / Terms & Conditions:** <https://www.newhavendisplay.com/terms.html>




Document Revision History



Revision	Date	Description	Changed By
0	07/13/2022	Initial Release	CJ
1	09/08/2022	Updated the Electrical characteristics and Quality Information	JT

Mechanical Drawing

SYMBOL	REVISION	DATE



[read caution below]



Product Description: 10.1" IPS HDMI TFT Module


1. TFT Driver IC: TFP401A
2. TFT Interface: HDMI
3. TFT Power Requirement: 6V/1.7A
4. Optical Features: Normally Black, Transmissive, Anti-Glare, 800 cd/m²

Improper handling of the FPC connections at the bottom edge of this module may cause damage resulting in display or touch failure. Take special care when handling this area of the display module to make sure these connections are never strained nor creased.


Standard Tolerance: (Unless otherwise specified) Linear: ±0.3mm	 NEWHAVEN DISPLAY INTERNATIONAL	
	Drawing/Part Number: NHD-10.1-HDMI-A-RSXP	
	Drawn By: C. Johnson	Approved By: C. Johnson
	Drawn Date: 07/12/2022	Approved Date: 07/12/2022
Unless otherwise specified: • Dimensions are in Millimeters • Third Angle Projection	Revision: -	
	Size: A3	
Do Not Scale Drawing		Scale: NS
Sheet 1 of 1		
This drawing is solely the property of Newhaven Display International, Inc. The information it contains is not to be disclosed, reproduced or copied in whole or part without written approval from Newhaven Display.		

ADU7611 (Low Power 165 MHz HDMI Receiver)


PUDD Decoupling




CUDD Decoupling





TUDD Decoupling



DVDDIO Decoupling








DVDD Decoupling



PIXEL PORT CONFIGURATION = 010 (DEFAULT 011)

Standard Tolerance: (Unless otherwise specified)		NEWHAVEN DISPLAY INTERNATIONAL	
Linear: ±0.3mm		Drawing/Part Number: NHD-10.1-HDMI-A-SCH	
Unless otherwise specified: • Dimensions are in Millimeters • Third Angle Projection		Drawn By: Z.Palrang Drawn Date: 08/12/2021	Approved By: Z.Palrang Approved Date: 08/12/2021
		Revision: - Size: A3 Scale: NS	
		Do Not Scale Drawing	
		Sheet 1 of 4	
This drawing is solely the property of Newhaven Display International, Inc. The information it contains is not to be disclosed, reproduced or copied in whole or part without written approval from Newhaven Display.			

[illegible]

Standard Tolerance: (Unless otherwise specified) Linear: $\pm 0.3\text{mm}$	 NEWHAVEN DISPLAY INTERNATIONAL													
Unless otherwise specified: • Dimensions are in Millimeters • Third Angle Projection 	<table border="1"> <tr> <td colspan="2" data-bbox="2341 1761 2757 1806"> Drawing/Part Number: NHD-10.1-HDMI-A-SCH </td> <td data-bbox="2757 1761 2837 1806"> Revision: - </td> </tr> <tr> <td data-bbox="2341 1806 2543 1848"> Drawn By: Z.Palrang </td> <td data-bbox="2543 1806 2757 1848"> Approved By: Z.Palrang </td> <td data-bbox="2757 1806 2837 1848"> Size: A3 </td> </tr> <tr> <td data-bbox="2341 1848 2543 1894"> Drawn Date: 08/12/2021 </td> <td data-bbox="2543 1848 2757 1894"> Approved Date: 08/12/2021 </td> <td data-bbox="2757 1848 2837 1894"> Scale: NS </td> </tr> <tr> <td colspan="2" data-bbox="2341 1894 2647 1925"> Do Not Scale Drawing </td> <td data-bbox="2647 1894 2837 1925"> Sheet 2 of 4 </td> </tr> </table>		Drawing/Part Number: NHD-10.1-HDMI-A-SCH		Revision: -	Drawn By: Z.Palrang	Approved By: Z.Palrang	Size: A3	Drawn Date: 08/12/2021	Approved Date: 08/12/2021	Scale: NS	Do Not Scale Drawing		Sheet 2 of 4
Drawing/Part Number: NHD-10.1-HDMI-A-SCH		Revision: -												
Drawn By: Z.Palrang	Approved By: Z.Palrang	Size: A3												
Drawn Date: 08/12/2021	Approved Date: 08/12/2021	Scale: NS												
Do Not Scale Drawing		Sheet 2 of 4												
This drawing is solely the property of Newhaven Display International, Inc. The information it contains is not to be disclosed, reproduced or copied in whole or part without written approval from Newhaven Display.														

A




C




E



F



10-W Digital Audio Power Amplifier



Electrical Characteristics

Item	Symbol	Condition	Min.	Typical	Max.	Unit
Operating Temperature Range	T _{OP}	Absolute Max	-20	-	+70	°C
Storage Temperature Range	T _{ST}	Absolute Max	-30	-	+80	°C
Backlight PWM Voltage	V _{PWM}	-	1.5	3.3	5.5	V
Backlight PWM Frequency	f _{PWM}	V _{PWM} = 3.3V	200	-	2000	Hz
Module Supply Voltage	V _{DD}	-	6.0	7.5	9.0	V
Module Supply Current	I _{DD}	V _{DD} = 6V	-	1.7	1.9	A
		V _{DD} = 9V	-	1.0	1.2	A

HDMI Receiver Information

On-board Analog Devices ADV7611 Low Power HDMI Receiver.

To view the full ADV7611 specification, please download it by accessing the link below:

<https://support.newhavendisplay.com/hc/en-us/articles/6963189583127-ADV7611>

Audio Amplifier Information

On-board Texas Instruments TAS5717 Digital Audio Power Amplifier.

To view the full TAS5717 specification, please download it by accessing the link below:

<https://support.newhavendisplay.com/hc/en-us/articles/7397555534615>

Technical Resource

3D Model	TFT Panel Used	Display Type	Luminance Rating	Optimal Viewing Angle	Touch Panel
NHD-10.1-1024600BF-ASXP	NHD-10.1-1024600BF-ASXP	IPS	800 cd/m ²	80° all angles	No Touch



EDID Array

```
const unsigned char NHD_HDMI10.1A[] = {
0x00, 0xFF, 0xFF, 0xFF, 0xFF, 0xFF, 0xFF, 0x00, 0x39, 0x04, 0x03, 0x00, 0x00, 0x00, 0x00, 0x00,
0x01, 0x1B, 0x01, 0x03, 0xA1, 0x16, 0x0D, 0x78, 0x02, 0xBB, 0xD0, 0x94, 0x57, 0x55, 0x91, 0x27,
0x21, 0x50, 0x54, 0x00, 0x00, 0x00, 0x01, 0x00, 0x01, 0x01, 0x01, 0x01, 0x01, 0x01, 0x01, 0x01,
0x01, 0x01, 0x01, 0x01, 0x01, 0x01, 0xB0, 0x13, 0x00, 0x40, 0x41, 0x58, 0x19, 0x20, 0x30, 0x20,
0x3A, 0x00, 0xDF, 0x7D, 0x00, 0x00, 0x00, 0x18, 0x01, 0x1D, 0x00, 0x72, 0x51, 0xD0, 0x1E, 0x20,
0x6E, 0x28, 0x55, 0x00, 0xDF, 0x7D, 0x00, 0x00, 0x00, 0x18, 0x00, 0x00, 0x00, 0xFC, 0x00, 0x4E,
0x48, 0x44, 0x2D, 0x31, 0x30, 0x2E, 0x31, 0x20, 0x4C, 0x56, 0x44, 0x53, 0x00, 0x00, 0x00, 0xFD,
0x00, 0x00, 0x3C, 0x00, 0x2D, 0x08, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x01, 0x65,
0x02, 0x03, 0x10, 0x60, 0x63, 0x03, 0x0C, 0x00, 0x83, 0x01, 0x00, 0x00, 0x23, 0x09, 0x04, 0x04,
0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00,
0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00,
0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00,
0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00,
0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00,
0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00,
0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x00, 0x61
};
```

EDID Timing

Pixel Clock:	50.40	☐ Interlaced
H. Active Pixels:	1024	V. Active Lines: 600
H. Blank:	320	V. Blank: 25
H. Front Porch:	48	V. Front Porch: 3
H. Sync Width:	32	V. Sync Width: 10
H. Image Size:	223	V. Image Size: 125
H. Border:	0	V. Border: 0
H. Clock: 37.50 kHz	V. Clock: 60.00 Hz	

Quality Information

Test Item	Content of Test	Test Condition	Note
High Temperature storage	Endurance test applying the high storage temperature for a long time.	+80°C, 240 hrs.	2
Low Temperature storage	Endurance test applying the low storage temperature for a long time.	-30°C, 240 hrs.	1,2
High Temperature Operation	Endurance test applying the electric stress (voltage & current) and the high thermal stress for a long time.	+70°C, 120 hrs.	2
Low Temperature Operation	Endurance test applying the electric stress (voltage & current) and the low thermal stress for a long time.	-20°C, 120 hrs.	1,2
High Temperature / Humidity Operation	Endurance test applying the electric stress (voltage & current) and the high thermal with high humidity stress for a long time.	+50°C, 90% RH, 120 hrs.	1,2
Thermal Shock resistance	Endurance test applying the electric stress (voltage & current) during a cycle of low and high thermal stress.	-30°C, 30min->25°C, 10min -> 80°C, 30min 10 cycles	
Vibration test	Endurance test applying vibration to simulate transportation and use.	Frequency:250r/min Amplitude: 1 inch Time:45min	3
Static electricity test	Endurance test applying electric static discharge.	Air: $V_s=\pm 8KV$, Contact: $V_s=\pm 4KV$ 10 Times	

Note 1: No condensation to be observed.

Note 2: Conducted after 4 hours of storage at 25°C, 0%RH.

Note 3: Test performed on product itself, not inside a container.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Newhaven Display:

[NHD-10.1-HDMI-A-RSXP](#)