

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0022287103

Status:

Active

Overview:

[KK Interconnect Solutions](#)

Description:

KK 254 Breakaway Header, Right-Angle, 10 Circuits, 0.38µm (15µ") Gold (Au)
Selective Plating, Mating Pin Length 10.29mm (.405"), with Kinked PC Tails

Documents:

3D Model	Packaging Specification PK-40873-0041-001 (PDF)
3D Model (PDF)	Packaging Specification PK-40873-0043-001 (PDF)
Drawing (PDF)	Symbol Footprint Data SYM-22-28-6103-001 (PDF)
Product Specification PS-10-07-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR19980
UL	E29179

Application tooling part link

Application Tooling Part Link	11-20-1230
-------------------------------	------------

General

Product Family	PCB Headers
Series	42376
Application	Board-to-Board, Signal, Wire-to-Board
Overview	KK Interconnect Solutions
Product Name	KK 254
UPC	800753806207

Physical

Breakaway	Yes
Circuits (Loaded)	10
Circuits (maximum)	10
Color - Resin	Black
Durability (mating cycles max)	25
Flammability	94V-0
Glow-Wire Capable	No
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	0.928/g
Number of Rows	1
Orientation	Right Angle
PC Tail Length	3.43mm
PCB Locator	No
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Bag
Pitch - Mating Interface	2.54mm
Plating min - Mating	0.381µm
Plating min - Termination	2.540µm
Polarized to Mating Part	No
Polarized to PCB	No
Shrouded	No
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	See Product Specification
Termination Interface: Style	Through Hole



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[42376](#) Series

Mates With

KK Crimp Housing [2695](#) , [6471](#) , [7880](#) , KK
PC Board Connector [4455](#)

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	500V

Solder Process Data

Duration at Max. Process Temperature (seconds)	005
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	235

Material Info

Engineering Number	42376-0360
--------------------	------------

Reference - Drawing Numbers

Packaging Specification	PK-40873-0041-001, PK-40873-0043-001
Product Specification	PS-10-07-001
Sales Drawing	SD-42376-001-001, SD-42376-001-002
Symbol/Footprint Data	SYM-22-28-6103-001

This document was generated on 12/14/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[22-28-7103](#)