

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0191600009

Status:

Active

Overview:

[Splices](#)

Description:

Closed-End Insulated Splice for 12-22 AWG Wire

Documents:

[Drawing \(PDF\)](#)

[Product Specification PS-19902-013-001 \(PDF\)](#)

[Packaging Specification PK-19408-109-001 \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification	
CSA	LR18689
UL	E32244
General	
Product Family	Splices
Series	19160
Crimp Quality Equipment	Yes
Overview	Splices
Product Name	Closed-End Insulated
UPC	800753110182
Physical	
Barrel Type	Closed
Color - Resin	Natural
Flammability	94V-2
Insulation	Nylon (PA)
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.689/g
Packaging Type	Carton
Temperature Range - Operating	105°C
Wire Insulation Diameter	6.86mm max.
Wire Size AWG	12, 14, 16, 18, 20, 22
Electrical	
Voltage - Maximum	600V
Material Info	
Engineering Number	NC-2212
Reference - Drawing Numbers	
Packaging Specification	PK-19408-109-001
Product Specification	PS-19902-013-001
Sales Drawing	PS-19160-006-001, SD-19160-001-001



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[19160](#) Series

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Hand Crimp Tool	640010900
Crimp Head for the AT-200 Pneumatic Hand Tool	640050900
Crimp Head for the AT-200 Pneumatic Hand Tool	640053600

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

19160-0009