


USW

 7mmL, For Audio Equipment


- Acoustic series, with 7mm height.
- Compliant to the RoHS directive (2011/65/EU,(EU)2015/863).


USW

 Smaller
UMW



Specifications

Item	Performance Characteristics							
Category Temperature Range	-40 to +85°C							
Rated Voltage Range	6.3 to 50V							
Rated Capacitance Range	1 to 220μF							
Capacitance Tolerance	±20% at 120Hz, 20°C							
Leakage Current	After 2 minutes' application of rated voltage at 20°C, leakage current is not more than 0.01CV or 3 (μA) , whichever is greater.							
Tangent of loss angle (tan δ)	Measurement frequency : 120Hz at 20°C							
	Rated voltage (V)	6.3	10	16	25	35	50	
	tan δ (MAX.)	0.24	0.20	0.16	0.14	0.12	0.10	
Stability at Low Temperature	Measurement frequency : 120Hz							
	Rated voltage (V)		6.3	10	16	25	35	50
	Impedance ratio (MAX.)	Z-25°C / Z+20°C	4	3	2	2	2	2
Z-40°C / Z+20°C		8	6	4	4	3	3	
Endurance	The specifications listed at right shall be met when the capacitors are restored to 20°C after the rated voltage is applied for 1000 hours at 85°C.						Capacitance change	Within ±20% of the initial capacitance value
							tan δ	200% or less than the initial specified value
							Leakage current	Less than or equal to the initial specified value
Shelf Life	After storing the capacitors under no load at 85°C for 1000 hours and then performing voltage treatment based on JIS C 5101-4 clause 4.1 at 20°C, they shall meet the specified values for the endurance characteristics listed above.							
Marking	Printed with black color letter on gold sleeve.							

Radial Lead Type



Type numbering system (Example : 10V 33μF)



Dimensions

V		6.3	10	16	25	35	50
Cap.(μF)	Code	0J	1A	1C	1E	1V	1H
1	010						4 × 7 10
2.2	2R2						4 × 7 19
3.3	3R3						4 × 7 24
4.7	4R7					4 × 7 24	4 × 7 28
10	100			4 × 7 28	4 × 7 28	4 × 7 31	5 × 7 38
22	220	4 × 7 34	4 × 7 35	4 × 7 39	5 × 7 48	5 × 7 52	6.3 × 7 58
33	330	4 × 7 40	4 × 7 43	5 × 7 55	5 × 7 58	6.3 × 7 65	
47	470	4 × 7 48	5 × 7 59	5 × 7 65	6.3 × 7 71		
100	101	5 × 7 78	6.3 × 7 87	6.3 × 7 98			
220	221	6.3 × 7 120					Case size φ D × L (mm)

Frequency coefficient of rated ripple current

Frequency	50Hz	120Hz	300Hz	1kHz	10kHz or more
Coefficient	0.70	1.00	1.17	1.36	1.50

Rated ripple current (mA rms) at 85°C 120Hz

Please refer to page 20, 21, 22 about the formed or taped product spec.
Please refer to page 4 for the minimum order quantity.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Nichicon:

[USW0J101MDD](#) [USW0J220MDD](#) [USW0J221MDD](#) [USW0J330MDD](#) [USW0J470MDD](#) [USW1A101MDD](#)
[USW1A220MDD](#) [USW1A330MDD](#) [USW1A470MDD](#) [USW1C100MDD](#) [USW1C101MDD](#) [USW1C220MDD](#)
[USW1C330MDD](#) [USW1C470MDD](#) [USW1E100MDD](#) [USW1E220MDD](#) [USW1E330MDD](#) [USW1E470MDD](#)
[USW1H010MDD](#) [USW1H100MDD](#) [USW1H220MDD](#) [USW1H2R2MDD](#) [USW1H3R3MDD](#) [USW1H4R7MDD](#)
[USW1HR22MDD](#) [USW1HR33MDD](#) [USW1HR47MDD](#) [USW1V100MDD](#) [USW1V220MDD](#) [USW1V330MDD](#)
[USW1V4R7MDD](#) [USW1HOR1MDD](#) [USW1H0R1MDD](#) [USW1E470MDD1TE](#) [USW1A101MDD1TP](#)
[USW1E470MDD1TP](#) [USW1H100MDD1TE](#) [USW0J470MDD1TE](#) [USW1V220MDD1TP](#) [USW1C101MDD1TE](#)
[USW1V330MDD1TP](#) [USW1H3R3MDD1TE](#) [USW1H220MDD1TE](#) [USW0J221MDD1TP](#) [USW0J330MDD1TP](#)
[USW1H010MDD1TE](#) [USW1H220MDD1TP](#) [USW1V4R7MDD1TP](#) [USW0J220MDD1TP](#) [USW1A330MDD1TP](#)