

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0622018807

Status:


Active

Overview:

Application Tooling

Description:

Impact 85 Ohm Backplane Press-In Tool for 6-Pair by 10-Column Assemblies



Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Application Tooling
Series	207123
Comments	See Tooling Specification (PDF) Above
Function	Insertion
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	Impact
Tool Type	Press-Fit Insertion Tool
UPC	884982555112
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.
Material Info	
Reference - Drawing Numbers	ATS-622018807-001, TM-622018799-001
Application Tooling Documents	

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Contained Per -ED/01/2018 (15 January 2018)	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

207123 Series

Use With

170535 Impact 85 Ohm Backplane Assembly, 6-Pair by 10 Column Assemblies

Application Tooling Description	FAQ Product #
Impact 85 Ohm Plus 6 Pair Vertical Backplane Header, Unguided, Open Endwalls, 10 Columns, 180 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead Free	1705351107
Impact 85 Ohm Plus 6 Pair Vertical Backplane Header, Unguided, Open Endwalls, 10	1705351108

Columns, 180
Circuits, Pin Length
5.50mm, Plated
Through Hole
Dimension 0.39mm,
Lead Free
Impact 85 Ohm 1705351127
Plus 6 Pair Vertical
Backplane Header,
Unguided, Dual
Endwalls, 10
Columns, 180
Circuits, Pin Length
4.90mm, Plated
Through Hole
Dimension 0.39mm,
Lead Free
Impact 85 Ohm 1705353107
Plus 6 Pair Vertical
Backplane Header,
Left Guided,
Open Endwall,
10 Columns, 180
Circuits, Pin Length
4.90mm, Plated
Through Hole
Dimension 0.39mm,
Lead Free
Impact 85 Ohm 1705355107
Plus 6 Pair Vertical
Backplane Header,
Right Guided,
Open Endwall,
10 Columns, 180
Circuits, Pin Length
4.90mm, Plated
Through Hole
Dimension 0.39mm,
Lead Free
Impact 85 Ohm 1705357107
Plus 6 Pair Vertical
Backplane Header,
Left Guided, Endwall,
10 Columns, 180
Circuits, Pin Length
4.90mm, Plated
Through Hole
Dimension 0.39mm,
Lead Free
Impact 85 Ohm 1705359107
Plus 6 Pair Vertical
Backplane Header,
Right Guided,
Endwall, 10
Columns, 180
Circuits, Pin Length
4.90mm, Plated
Through Hole
Dimension 0.39mm,
Lead Free

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[62201-8807](#)