

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0768290010

Status:

Active

Overview:

Mega-Fit Power Connectors

Description:

Mega-Fit Vertical Header, Through Hole, 5.70mm Pitch, Dual Row, 10 Circuits, 1.52µm Tin (Sn) Plating, Glow-Wire Capable, Black

- Documents:
- 3D Model (PDF)

3D Model

Drawing (PDF)

Product Specification 1720631000-PS-000 (PDF)

Product Specification PS-76823-100-001 (PDF)

Application Specification 768232000-AS-000 (PDF)

Application Specification AS-76823-100-001 (PDF)

Packaging Specification PK-31301-976-000 (PDF)

Test Summary TS-76823-100-001 (PDF)

Test Summary TS-76829-001-001 (PDF)

Datasheet (PDF)

Symbol Footprint Data SYM-76829-0010-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	PCB Headers
Series	76829
Application	Power, Wire-to-Board
Overview	Mega-Fit Power Connectors
Product Name	Mega-Fit
UPC	887191454221
Physical	
Breakaway	No
Circuits (Loaded)	10
Circuits (maximum)	10
Color - Resin	Black
Durability (mating cycles max)	25
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	Yes
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Mated Height	16.78mm
Material - Metal	High Conductivity Copper
Material - Plating Mating	Matte Tin
Material - Plating Termination	Matte Tin
Material - Resin	Liquid Crystal Polymer
Net Weight	5.656/g
Number of Rows	2
Orientation	Vertical
PC Tail Length	3.73mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.58mm, 2.36mm
Packaging Type	Tray
Pitch - Mating Interface	5.70mm
Pitch - Termination Interface	5.70mm
Plating min - Mating	1.524µm
Plating min - Termination	1.524µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2021)4569-DC (8 July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

76829 Series

Mates With

Mega-Fit Receptacle Housings [171692](#) , [170001](#) . Mega-Fit Discrete Cable Assembly [45136](#)

Shrouded	Yes
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole
Unmated Height	14.80mm
Electrical	
Current - Maximum per Contact	23.5A
Voltage - Maximum	600V AC (RMS)/DC
Solder Process Data	
Duration at Max. Process Temperature (seconds)	030
Lead-freeProcess Capability	SMC&WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	260
Material Info	
Reference - Drawing Numbers	
Application Specification	768232000-AS-000, AS-76823-100-001
Packaging Specification	PK-31301-976-000
Product Specification	1720631000-PS-000, PS-76823-100-001
Sales Drawing	SD-76829-0100-000
Symbol/Footprint Data	SYM-76829-0010-001
Test Summary	TS-76823-100-001, TS-76829-001-001

This document was generated on 02/08/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[76829-0010](#)