

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1552100091

Status:


Active

Overview:

Flamar Standard and Custom Cables for Industrial Automation

Description:

Flamar Sensor Cable, PVC Jacket, Unshielded, 5 Circuits, 0.34mm² with Green-Yellow Ground / 22 AWG with Green-Yellow Ground, 5.50mm (.217") Diameter, 600.0m (1968.50') Length, Gray



Series image - Reference only

Documents:

Product Specification 1552100001-P1E (PDF)

RoHS Certificate of Compliance (PDF)

Brochure (PDF)

General	
Product Family	Cable
Series	155210
Comments	3 reels of 200.0m each
Crimp Quality Equipment	Yes
Geographic Area	Global
Overview	Flamar Standard and Custom Cables for Industrial Automation
Product Name	Flamar, Signal and Control
UPC	889056450492
Physical	
Bending Radius - Minimum	> 15xOD
Cable Length	600.0m
Circuits (Loaded)	5
Color - Cable Jacket	Gray
Insulation	TPE
Material - Outer Jacket	PVC
Net Weight	0.010/g
Outer Jacket Diameter	5.50mm
Packaging Type	Reel
Temperature Range - Operating	+5° to +80°C
Wire Size AWG	22
Wire Size mm²	0.34
Wire/Cable Type	UL AWM 2464 / CSA
Electrical	
Current - Maximum per Contact	Contact Molex
Voltage - Maximum	300V
Material Info	
Engineering Number	3X200M
Reference - Drawing Numbers	
Product Specification	1552100001-P1E

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

155210 Series

Use With

Nano-Change (M8) 120091 , Micro-Change (M12) 120071 , Ultra-Lock (M12) 120085

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

155210-0091