

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1553219004](#)
Status: **Active**
Overview: [Flamar Standard and Custom Cables for Industrial Automation](#)
Description: Flamar Feedback Cable, WSOR Jacket, Braided Shielding Overall, 8 Circuits, 3x(2x0.14mm² with Spiral Shield) + 2x(0.50mm² with Spiral Shield) / 3x(2x26 AWG with Spiral Shield) + 2x(21 AWG with Spiral Shield), 9.00mm (.354") Diameter, 200.0m (656.17') Length, Green

Documents:
[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Cable
Series	155321
Crimp Quality Equipment	Yes
Geographic Area	Global
Overview	Flamar Standard and Custom Cables for Industrial Automation
Product Name	Flamar, Servo Motor
UPC	889056461122
Physical	
Bending Radius - Minimum	> 10xOD
Cable Length	200.0m
Circuits (Loaded)	8 (6+2)
Color - Cable Jacket	Green
Insulation	TPE
Material - Outer Jacket	WSOR
Net Weight	0.010/g
Outer Jacket Diameter	9.00mm
Packaging Type	Reel
Temperature Range - Operating	-25° to +80°C
Wire Size AWG	21, 26
Wire Size mm²	0.14, 0.50
Wire/Cable Type	UL AWM 21215 / CSA
Electrical	
Current - Maximum per Contact	Contact Molex
Voltage - Maximum	600V
Material Info	
Engineering Number	1X200M



Series image - Reference only

EU ELV Not Reviewed	
EU RoHS Not Reviewed REACH SVHC Not Reviewed Halogen-Free Status Not Reviewed	China RoHS
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[155321](#) Series

Use With
Brad M23 [120230](#) , [120233](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

155321-9004