


Dot Graphic VFD Module

GU128x64F-7003

- ❑ 128x64 Dot Graphic
- ❑ Single 5V Supply
- ❑ High Brightness Blue Green Display
- ❑ Operating Temp -40°C to +85°C
- ❑ 11 Multi Sized Fonts
- ❑ Async. & Sync. Serial Interface

The module includes the Vacuum Fluorescent Display glass, VF drivers and micro-controller ICs with refresh RAM, character generator and interface logic. The asynchronous serial interface accepts baud rates up to 115,200 with none parity. The module is ready to receive ASCII characters without initialization commands.



Dimensions in mm & subject to tolerances.
Mounting holes 3.5mm dia.

ELECTRICAL SPECIFICATION

Parameter	Symbol	Value	Condition
Power Supply Voltage	VCC	5.0VDC +/- 5%	GND=0V
Power Supply Current	ICC	1000mADC typ.	VCC=5V
Logic High Input	VIH	0.8xVCC min. Vcc max.	VCC=5V
Logic Low Input	VIL	0VDCmin 0.2xVCC max.	VCC=5V
Logic High Output	VOH	3.8VDC min. Vcc max.	IOH = -1.5mA
Logic Low Output	VOL	0VDC min. 0.6VDC max.	IOL = 1.6mA

The power on rise time should be less than 100ms. Inrush current at power on can be 2 x ICC.

OPTICAL and ENVIRONMENTAL SPECIFICATIONS

Parameter	Value
Display Area (XxY mm)	83.1 x 41.5
Dot Size/Pitch (XxY mm)	0.5 x 0.5 / 0.65 x 0.65
Luminance	1000 cd/m ² Typ.
Colour of Illumination	Blue-Green (Filter for colours)
Operating Temperature	-40°C to +85°C
Storage Temperature	-40°C to +85°C
Operating Humidity (non condensing)	20 to 80% RH @ 25°C

SOFTWARE COMMANDS – Popular codes, more included

Command	Code
Write Character to Display	20H-FFH
BS, HT, LF, CR, Display Clear	08H, 09H, 0AH, 0DH, 0CH
Initialize Display	1BH 40H
Specify International Font	1BH 52H n
Vertical Scroll Mode	1FH 02H
Horizontal Scroll Mode	1FH 03H
Cursor Set	1FH 24H xL xH yL yH
Scroll Display Action	1FH 28H 61H 10H wL wH cL cH s
Display Blank	1FH 28H 61H 11H p t1 t2 c
Screen Saver	1FH 28H 61H 40H p
Bit Image Display Group	1FH 28H 66H 11H xL xH
Font Magnified Display	1FH 28H 67H 40H x y
Brightness Level Setting	1FH 58H n

The module defaults to 5x7 font, cursor top left at power on.

COMMON FONT

	00	10	20	30	40	50	60	70
00								
01								
02								
03								
04								
05								
06								
07								
08								
09								
0A								
0B								
0C								
0D								
0E								
0F								

INTERNATIONAL FONTS (n=0)

	80	90	A0	B0	C0	D0	E0	F0
00								
01								
02								
03								
04								
05								
06								
07								
08								
09								
0A								
0B								
0C								
0D								
0E								
0F								

(n=19)

CN1 is not used on this module.

Full specification available on request.

SERIAL INTERFACE – CN3 (select with J2)

Pin	Async. Sig	Sync. Sig
1	VCC (5V)	VCC (5V)
2	SIN	SIN
3	GND	GND
4	SBUSY	SBUSY
5	NC	SCK
6	/RESET	/RESET

CONTACT

Noritake Sales Office Tel Nos
 Nagoya Japan: +81 (0)52-561-9867
 Canada: +1-416-291-2946
 Chicago USA: +1-847-439-9020
 Munchen (D): +49 (0)89-3214-290
 Itron UK: +44 (0)1493 601144
 Rest Europe: +49 (0)61-0520-9220
www.noritake-iron.com

Subject to change without notice.
 IUK Doc Ref:10567 Iss:1 23Nov07

NORITAKE ITRON VFD MODULES

128 x 64 Dot Graphic

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Noritake:](#)

[GU128X64F-7003](#)