


# Frequency Divider Evaluation Board

**ABLNO-EVAL**

 **RoHS Compliant**




## OVERALL CAPABILITY

**ABLNO-EVAL**; Frequency Divider Evaluation Board shown in figure (1) is designed to facilitate engineering evaluation of Abracon's Ultra Low Noise – ABLNO series of fixed clock and voltage controlled crystal oscillators. Further, there is a provision through the RF\_IN SMA Connector to supply any other oscillator signal between 10MHz and 200MHz; if ABLNO series is not being characterized.

This Evaluation Board is ideal to conduct the following measurements:

- Phase Noise and rms jitter for  $\div 1$ ,  $\div 2$ ,  $\div 4$  and  $\div 8$  frequency outputs
- Frequency Pull Characteristics of the ABLNO by using the Vc port as the control voltage
- Frequency Stability over operating temperature ( $-40^{\circ}\text{C}$  to  $+85^{\circ}\text{C}$ )



**Figure (1)**


Designers who are interested in using the ABLNO as an Ultra Low Noise platform device to generate additional Low Noise frequencies will find this Evaluation Board to be of exceptional value. Abracon has implemented Ultra Low Noise  $\div 2$ ,  $\div 4$  and  $\div 8$  circuitry on this board, that can also be incorporated in end-customer solutions; please contact [tech-spport@abracon.com](mailto:tech-spport@abracon.com) for additional details.

Typical Phase Noise and jitter performance in  $\div 1$ ,  $\div 2$ ,  $\div 4$  and  $\div 8$  modes is depicted in section 2.0.

# Frequency Divider Evaluation Board

**ABLNO- EVAL**

 **RoHS Compliant**



## COMPONENT DESCRIPTION

Component	Description	Functionality
<b>RF_IN</b>	External Oscillator Input	Input a 10MHz to 200MHz oscillator signal into this SMA connector for evaluation... <i>see Note #5</i>
<b>Vc</b>	Control Port	When characterizing the ABLNO series of VCXO's, apply control voltage to this port to characterize frequency pull
<b>VDD</b>	Supply Voltage	This port simultaneously biases the ABLNO Oscillator and the divider scheme (+3.3V ±5%) ..... <i>see Note #4</i>
<b>RF_Out</b>	Evaluation Board Output	Either ABLNO or RF_IN frequency is divided down by 1, 2, 4 or 8 and is present at this port
<b>S1</b>	Switch # 1	If the tab is moved to the “up position ( <b>UP</b> )”, RF_IN signal is selected. If the tab is moved to the “down position ( <b>DN</b> )”, ABLNO signal is selected
<b>S2</b>	Switch # 2	If the tab is moved to the “up position ( <b>UP</b> )”, RF_IN signal is divided down by 2 and is present at RF_Out
<b>S3</b>	Switch # 3	If the tab is moved to the “up position ( <b>UP</b> )”, RF_IN signal is divided down by 4 and is present at RF_Out. S2 should also be in the “up position ( <b>UP</b> )”... please see truth table #1
<b>S4</b>	Switch # 4	If the tab is moved to the “up position ( <b>UP</b> )”, RF_IN signal is divided down by 8 and is present at RF_Out. S2 & S3 should also be in the “up position ( <b>UP</b> )”... please see truth table #1





Figure (2)

# Frequency Divider Evaluation Board

**ABLNO-EVAL**

 **RoHS Compliant**



## TRUTH TABLE

Table # 1

S1	S2	S3	S4	Description
DN	DN	DN	DN	ABLNO's RF Output = ÷1
DN	UP	DN	DN	ABLNO's RF Output = ÷2
DN	UP	UP	DN	ABLNO's RF Output = ÷4
DN	UP	UP	UP	ABLNO's RF Output = ÷8

Table # 2

S1	S2	S3	S4	Description
UP	DN	DN	DN	RF_IN Port's RF Output = ÷1
UP	UP	DN	DN	RF_IN Port's RF Output = ÷2
UP	UP	UP	DN	RF_IN Port's RF Output = ÷4
UP	UP	UP	UP	RF_IN Port's RF Output = ÷8

**Note # 1:** **DN** = Down Position; **UP** = Up Position

**Note # 2:** All four switches are shipped with yellow protective tape on top, please remove before use

**Note # 3:** To evaluate Abracon's ABLNO Crystal Oscillator, please solder it down in the section outlined with a rectangle and labeled ABLNO. Please follow the orientation shown in figure (3) below.




Figure (3)


**Note # 4:** VDD Port biases both the ABLNO device, as well as the divider circuitry. Since ABLNO's VDD range is  $+3.3V \pm 5\%$ , the recommended VDD range while evaluating ABLNO oscillators is  $+3.135V$  to  $+3.465V$ . However, since the divider circuitry can be biased between  $+1.8V$  &  $+5.5V$ , while evaluating RF\_IN external signal; lower or higher biasing voltage can be used, as long as the peak-to-peak signal from the RF\_IN port does not exceed the bias voltage (VDD).

**Note # 5:** RF\_IN port expects a LVCMOS signal. If a clipped Sinewave or Sinewave signal with lower amplitude is used; it might be necessary to square-that-up. There is a provision above (S1) to add a buffer to achieve this. Please contact [tech-support@abracon.com](mailto:tech-support@abracon.com).

# Frequency Divider Evaluation Board


**ABLNO-EVAL**

 **RoHS Compliant**




100MHz ABLNO was used to conduct  $\div 1$ ,  $\div 2$ ,  $\div 4$  and  $\div 8$  measurements

Typical Phase Noise Performance @ 100.00 MHz Carrier ( $\div 1$  Mode) @ Vdd = +3.3V (25°C±3°C)



S1	S2	S3	S4	Description
DN	DN	DN	DN	ABLNO's RF Output = $\div 1$

Typical Phase Noise Performance @ 50.00 MHz Carrier ( $\div 2$  Mode) @ Vdd = +3.3V (25°C±3°C)



S1	S2	S3	S4	Description
DN	UP	DN	DN	ABLNO's RF Output = $\div 2$

ABRACON IS  
ISO9001:2008  
CERTIFIED



Visit [www.abracon.com](http://www.abracon.com) for Terms & Conditions of Sale **Revised: 06.06.13**


30332 Esperanza, Rancho Santa Margarita, California 92688

tel 949-546-8000 | fax 949-546-8001 | [www.abracon.com](http://www.abracon.com)


# Frequency Divider Evaluation Board

**ABLNO-EVAL**

 **RoHS Compliant**




## Typical Phase Noise Performance @ 25.00 MHz Carrier ( $\div 4$ Mode) @ Vdd = +3.3V (25°C $\pm$ 3°C)



S1	S2	S3	S4	Description
DN	UP	UP	DN	ABLNO's RF Output = $\div 4$

## Typical Phase Noise Performance @ 12.50 MHz Carrier ( $\div 8$ Mode) @ Vdd = +3.3V (25°C $\pm$ 3°C)



S1	S2	S3	S4	Description
DN	UP	UP	UP	ABLNO's RF Output = $\div 8$

ABRACON IS  
ISO9001:2008  
CERTIFIED



Visit [www.abracon.com](http://www.abracon.com) for Terms & Conditions of Sale **Revised: 06.06.13**


30332 Esperanza, Rancho Santa Margarita, California 92688

tel 949-546-8000 | fax 949-546-8001 | [www.abracon.com](http://www.abracon.com)

# Frequency Divider Evaluation Board

**ABLNO-EVAL**


 **RoHS Compliant**



## PHASE NOISE & RMS JITTER PERFORMANCE SUMMARY

Offset From the Carrier	Measured Phase Noise (dBc/Hz)			
	100MHz	50MHz	25MHz	12.5MHz
10Hz	-88.32	-95.38	-100.24	-105.61
100Hz	-119.16	-124.38	-130.33	-136.13
1,000Hz	-143.44	-145.07	-143.74	-146.90
10,000Hz	-156.60	-156.02	-154.70	-157.75
100,000Hz	-160.44	-163.50	-162.75	-164.90
1,000,000Hz	-164.00	-165.54	-166.01	-166.90
5,000,000Hz	-165.11	-167.31	-167.21	-168.04


Carrier	100MHz	50MHz	25MHz	12.5MHz
Measured Jitter (12kHz to 20MHz) in <i>femto seconds</i>	<b>30.22</b>	47.86	95.01	168.15
<b>Additive rms Jitter</b> (12kHz to 20MHz) in <i>femto seconds</i>		17.64	64.80	137.93





# Frequency Divider Evaluation Board

**ABLNO-EVAL**

 **RoHS Compliant**



## OUTLINE DIMENSION:



**Packaging:** Units are packaged in ESD bags, single unit per bag.

**ATTENTION:** Abracon Corporation's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependant Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon Corporation is required. Please contact Abracon Corporation for more information.

ABRACON IS  
ISO9001:2008  
CERTIFIED



Visit [www.abracon.com](http://www.abracon.com) for Terms & Conditions of Sale **Revised: 06.06.13**  
30332 Esperanza, Rancho Santa Margarita, California 92688  
tel 949-546-8000 | fax 949-546-8001 | [www.abracon.com](http://www.abracon.com)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ABRACON:](#)

[ABLS-20.000MHZ-L4Q-T](#) [ABLS-30.000MHZ-L4QF-T](#) [ABLNO-EVAL](#)