







Technical drawing showing a 2x3 grid of rectangular features. Dimensions are provided in inches and millimeters.

- Overall width: 0.039 ± 0.001 [0.99 ± 0.02]
- Overall height: 0.102 TYP. [2.59]
- Horizontal spacing between columns: 0.027 ± 0.001 [0.69 ± 0.02]
- Vertical spacing between rows: 0.075 [1.90]




Pin No.	Configuration
1	PDB, OE,CLKI
2	GND
3	FREFIN
4	VDD
5	CSEL,CLK2
6	CLK0



1. Dimensions and tolerances are as per ANSI Y14.5M, 1982
2. Package surface to be mirror finish.
3. Die is facing up for mold. Die is facing down for trim/form.i.e. reverse trim/form.
4. The foot measuring is based on the gauge plane method.

 Dimensions are exclusive of mold flash & gate burr.

UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCH(MM) SURFACE FINISH: TOLERANCES: LINEAR: ANGULAR:		FINISH:		DEBUR AND BREAK SHARP EDGES		DO NOT SCALE DRAWING		REVISION		-
	NAME	SIGNATURE	DATE			 ABRACON CORPORATION 30332 Esperanza, Rancho Santa margarita, California 92688				
DRAWN	-									
CHK'D	XXXXXX					TITLE: -				
APPV'D										
MFG						DWG NO. ABMJB-902				
Q.A										
						A3				
						SCALE:20:1				
						SHEET 1 OF 1				
						WEIGHT:				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ABRACON:

[ABMJB-902-154USY-T5](#) [ABMJB-902-Q74USY-T5](#) [ABMJB-902-155USY-T5](#) [ABMJB-902-156USY-T5](#) [ABMJB-902-155USY-T3](#) [ABMJB-902-104USY-T5](#) [ABMJB-902-154USY-T3](#) [ABMJB-902-151USY-T3](#) [ABMJB-902-Q82USY-T3](#) [ABMJB-902-Q76USY-T3](#) [ABMJB-902-Q76USY-T5](#) [ABMJB-902-Q42USY-T5](#) [ABMJB-902-104USY-T3](#) [ABMJB-902-Q57USY-T5](#) [ABMJB-902-Q74USY-T3](#) [ABMJB-902-153USY-T3](#) [ABMJB-902-Q78USY-T3](#) [ABMJB-902-153USY-T5](#) [ABMJB-902-Q57USY-T3](#) [ABMJB-902-Q78USY-T5](#) [ABMJB-902-156USY-T3](#) [ABMJB-902-Q42USY-T3](#) [ABMJB-902-151USY-T5](#) [ABMJB-902-Q82USY-T5](#)