

2140 MHz SMD SAW Filter

ABSTS5A2-3H4M02CM

Request Samples



Check Inventory



1.1 x 0.9 x 0.5 mm
RoHS/RoHS II Compliant
MSL Level = 3

Features

- Low Insertion Loss
- SMD Mount Filter
- Compact Package Size of 1.1 x 0.9 x 0.5mm

Applications

- Mobile Phones
- Cellular 4G LTE/ UMTS/ W-CDMA systems
- Low loss RF Filter for Receive path

Electrical Specifications

Parameters		Specifications		
		Min	Typ	Max
Nominal Center Frequency (Fc) (MHz)			2140	
Insertion Loss (2110 ~ 2170 MHz) (dB)			1.9	2.5
Amplitude Ripple (2110 ~ 2170 MHz) (dB)			0.6	1.5
Input VSWR (2110 ~ 2170 MHz)			1.8	2.3
Output VSWR (2110 ~ 2155 MHz)			1.8	2.3
Attenuation (dB)	50 ~ 1710 MHz	35	40	
	1710 ~ 1755 MHz	40	42	
	1920 ~ 1980 MHz	42	45	
	4220 ~ 4340 MHz	30	42	
Terminating Source & Load Impedance (Ω)			50	
Maximum Input Power (dBm)			10	
DC Voltage (V)			0	

Mechanical Specifications

Parameters	Specifications
Filter Dimension	1.1 x 0.9 x 0.5 mm
Mounting Type	SMD Mount

Environmental Specifications

Parameters	Specifications
Operating Temperature Range	-30°C ~ +85°C
Storage Temperature Range	-40°C ~ +85°C
RoHS/ RoHS II Compliant	Yes
MSL level	3
ESD	50V (MM), 100V (HBM)

2140 MHz SMD SAW Filter

ABSTS5A2-3H4M02CM

Request Samples




Check Inventory



1.1 x 0.9 x 0.5 mm
RoHS/RoHS II Compliant
MSL Level = 3

Package Dimensions



All tolerances are +/-0.05 mm unless otherwise specified
Coplanarity: 0.1mm max
1 to 5: Pin numbers
Unit: mm

Pin No.	Symbol	Function
1	IN	Input
2	GND	Ground
3	GND	Ground
4	OUT	Output
5	GND	Ground

Marking Description:

X: Year/Month Code (Follow the table)

YEAR/Month	1	2	3	4	5	6	7	8	9	10	11	12
2013	A	B	C	D	E	F	G	H	J	K	L	M
2014	N	P	Q	R	S	T	U	V	W	X	Y	Z
2015	a	b	c	d	e	f	g	h	j	k	l	m
2016	n	p	q	r	s	t	u	v	w	x	y	z
2017	<u>A</u>	<u>B</u>	<u>C</u>	<u>D</u>	<u>E</u>	<u>F</u>	<u>G</u>	<u>H</u>	<u>J</u>	<u>K</u>	<u>L</u>	<u>M</u>
2018	<u>N</u>	<u>P</u>	<u>Q</u>	<u>R</u>	<u>S</u>	<u>T</u>	<u>U</u>	<u>V</u>	<u>W</u>	<u>X</u>	<u>Y</u>	<u>Z</u>
2019	<u>a</u>	<u>b</u>	<u>c</u>	<u>d</u>	<u>e</u>	<u>f</u>	<u>g</u>	<u>h</u>	<u>j</u>	<u>k</u>	<u>l</u>	<u>m</u>
2020	<u>n</u>	<u>p</u>	<u>q</u>	<u>r</u>	<u>s</u>	<u>t</u>	<u>u</u>	<u>v</u>	<u>w</u>	<u>x</u>	<u>y</u>	<u>z</u>

2140 MHz SMD SAW Filter

ABSTS5A2-3H4M02CM

Request Samples




Check Inventory




1.1 x 0.9 x 0.5 mm
RoHS/RoHS II Compliant
MSL Level = 3

PCB Footprint



Measurement Circuit



2140 MHz SMD SAW Filter

ABSTS5A2-3H4M02CM

Request Samples




Check Inventory




1.1 x 0.9 x 0.5 mm
RoHS/RoHS II Compliant
MSL Level = 3

Transmission Characteristics

S21 (Narrowband)



S21 (Broadband)



2140 MHz SMD SAW Filter

ABSTS5A2-3H4M02CM

Request Samples




Check Inventory




1.1 x 0.9 x 0.5 mm
RoHS/RoHS II Compliant
MSL Level = 3

VSWR Graphs

S11 (Narrowband)



S22 (Narrowband)



2140 MHz SMD SAW Filter

ABSTS5A2-3H4M02CM

Request Samples




Check Inventory




1.1 x 0.9 x 0.5 mm
RoHS/RoHS II Compliant
MSL Level = 3

Smith Charts

S11 (Narrowband)



S22 (Narrowband)



2140 MHz SMD SAW Filter

ABSTS5A2-3H4M02CM

Request Samples




Check Inventory



1.1 x 0.9 x 0.5 mm
RoHS/RoHS II Compliant
MSL Level = 3

Recommended Reflow Profile

1. Preheating shall be fixed at 150°C~180°C for 60-90 seconds.
2. Ascending time to preheating temperature 150°C shall be 30 seconds minimum.
3. Heating shall be fixed at 220°C for 50~80 seconds and at 260°C+0/-5°C peak (20~40sec.)
4. Time :2 times.



2140 MHz SMD SAW Filter

ABSTS5A2-3H4M02CM

Request Samples



Check Inventory




1.1 x 0.9 x 0.5 mm
RoHS/RoHS II Compliant
MSL Level = 3

Packaging

Packaging Type: Reel and Tape
Pieces per Reel: 5k

Reel Dimension



Unit: mm

2140 MHz SMD SAW Filter

ABSTS5A2-3H4M02CM

Request Samples




Check Inventory



1.1 x 0.9 x 0.5 mm
RoHS/RoHS II Compliant
MSL Level = 3

Tape Dimension



ATTENTION: Abracon LLC's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependent Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon LLC is required. Please contact Abracon LLC for more information.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ABRACON:](#)

[ABSTS5A2-3H4M02CM](#)