

LARGE CURRENT/LOW DCR MULTILAYER CHIP BEAD

ACML-0603U

RoHS
Compliant



1.65 x 0.8 x 0.8mm

FEATURES:

- Suitable for large current applications, current rating up to 6A
- Nickel barrier terminations provide excellent solder heat resistance
- Suitable for flow and reflow soldering
- Other sizes are available

APPLICATIONS:

- Video equipment, audio equipment
- Automotive electrical equipment
- Communication equipment
- OA equipment and other

STANDARD SPECIFICATIONS:

Operating Temperature
-55°C to +125°C

Storage Temperature
-10°C to +40°C, 70% RH max.

Part Number	Impedance (Ω) $\pm$ 25%	Z Test Freq. (MHz)	DCR (m Ω) Max.	Ir (mA) Max.
ACML-0603U-300	30	100	60	1800
ACML-0603U-600	60	100	100	1200
ACML-0603U-101A	100	100	150	1000
ACML-0603U-220	22	100	10	6000
ACML-0603U-700	70	100	20	4000
ACML-0603U-331	330	100	70	1500
ACML-0603U-391	390	100	120	1200
ACML-0603U-471	470	100	120	1200
ACML-0603U-101B	100	100	30	3000
ACML-0603U-181	180	100	50	2000
ACML-0603U-221	220	100	50	2000
ACML-0603U-601	600	100	150	1000

Test Conditions and equipments

DCR: Milliohmmeter-HP4338B or equivalent.

Z: RF Impedance /Material Analyzer-HP4291B or equivalent; Fixture: HP16192A;

Ir: Electric Power, Electric current meter, Thermometer. Ir is direct electric current as chip surface temperature rose by 20°C against chip initial surface temperature (Ta)

Test Frequency: 100MHz, -20dBm or 50mV

Unless specified, test condition should be Temp.=5~35°C, Humidity=45~85%.

PART NUMBER IDENTIFICATION

ACML-0603U- -

Impedance Code

Please refer to the Table

Packaging

T: 4kpcs/reel

LARGE CURRENT/LOW DCR MULTILAYER CHIP BEAD













ACML-0603U

RoHS
Compliant



1.65 x 0.8 x 0.8mm

IMPEDANCE FREQUENCY CHARACTERISTICS



LARGE CURRENT/LOW DCR MULTILAYER CHIP BEAD


ACML-0603U

RoHS
Compliant



1.65 x 0.8 x 0.8mm


OUTLINE DIMENSIONS



Series	L	W	T	a
ACML-0603U	1.65±0.15	0.80±0.15	0.80±0.15	0.30±0.20


Dimension: mm

Materials



Code	Part Name	Material Name
①	Ferrite Body	Ferrite Powder
②	Inner Coils	Silver Paste
③	Pull-out Electrode (Ag)	Silver Paste
④-1	Terminal Electrode: Inside Ag	Termination Silver Composition
④-2	Electro-Plating: Ni/Sn plating	Plating Chemicals

REFLOW PROFILE



- 1~2 °C /sec. Ramp
- Pre-heating: 150~190 °C /90±30 sec.
- Time above 240 °C: 20~40sec
- Peak temperature: 260 °C Max./10sec.
- Solder paste: Sn/3.0Ag/0.5Cu
- Max.2 times for re-flowing

LARGE CURRENT/LOW DCR MULTILAYER CHIP BEAD

ACML-0603U


RoHS
Compliant




1.65 x 0.8 x 0.8mm

TAPE & REEL

T= tape and reel (4,000pcs/reel)



A	B	P	T Max
1.0 ± 0.2	1.8 ± 0.2	4.0 ± 0.1	1.1



Dimension: mm

ATTENTION: Abracon Corporation's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependant Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon Corporation is required. Please contact Abracon Corporation for more information.

ABRACON IS
ISO 9001:2008
CERTIFIED



ABRACON
CORPORATION

Visit www.abracon.com for Terms & Conditions of Sale

30332 Esperanza, Rancho Santa Margarita, California 92688
tel 949-546-8000 | fax 949-546-800 | www.abracon.com

Revised: 05.19.14

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ABRACON:

[ACML-0603U-471-T](#) [ACML-0603U-600-T](#) [ACML-0603U-601-T](#) [ACML-0603U-700-T](#) [ACML-0603U-181-T](#) [ACML-0603U-220-T](#) [ACML-0603U-221-T](#) [ACML-0603U-300-T](#) [ACML-0603U-331-T](#) [ACML-0603U-391-T](#) [ACML-0603U-101A-T](#) [ACML-0603U-101B-T](#)