

### APPLICATIONS



- Battery-powered devices
- High switching frequency SMPS
- IoT
- Wearable
- Portable devices
- Input filters

### FEATURES

- Size 2.0mmx1.6mmx1.0mm
- Low Profile
- Low Audible Noise
- Molded Construction
- Soft Saturation
- Stable Over High Temperatures
- Low DCR
- Max Operating Temp +125°C
- RoHS/REACH-Compliant, Halogen-Free







### ELECTRICAL CHARACTERISTICS

Parameter			Value	Unit
Inductance <sup>(1)</sup>	<i>L</i>	±20%	0.47	μH
Resistance	<i>R<sub>DC</sub></i>	Typ	27	mΩ
Resistance <sub>MAX</sub>	<i>R<sub>DC MAX</sub></i>	Max	32	mΩ
Rated Current <sup>(2)</sup>	<i>I<sub>R</sub></i>	Typ	4.5	A
Saturation Current <sub>25°C</sub> <sup>(3)</sup>	<i>I<sub>SAT 25°C</sub></i>	Typ	5.7	A
Saturation Current <sub>100°C</sub> <sup>(4)</sup>	<i>I<sub>SAT 100°C</sub></i>	Typ	5.7	A
Resonance Frequency	<i>f<sub>r</sub></i>	Typ	142	MHz

### GENERAL SPECIFICATIONS


<b>(1) Inductance</b>	Measured at 100kHz, 100mA
<b>(2) Rated Current</b>	Rated current will cause the coil temperature rise ΔT of 40K <i>I<sub>R</sub> measured with the inductor soldered in a single-layer PCB. Copper layer thickness 35μm Cu / PCB size 30x50mm. Temperature behavior dependent on circuit design, PCB layout, proximity to other components, and trace dimensions and thickness.</i>
<b>(3) Saturation Current <sub>25°C</sub></b>	Saturation current will cause L to drop from 30% at 25°C ambient temperature
<b>(4) Saturation Current <sub>100°C</sub></b>	Saturation current will cause L to drop from 30% at 100°C ambient temperature
<b>Temperature Test Condition</b>	Electrical specifications measured at 25°C, 35% RH if not given differently
<b>Operating Condition</b>	Operating temperature: -40°C to +125°C (including temp rise) Should not exceed +125°C under worst-case operation conditions
<b>Storage Condition</b>	Tape and Reel packaging: -10°C to +40°C Humidity: <50% RH

**TYPICAL PERFORMANCE CURVES**




## DIMENSIONS

### PRODUCT PACKAGE



### RECOMMENDED LAND PATTERN



## TOP MARKING

### Marking

Start of Winding . (dot)

## ORDERING INFORMATION

Part Number	$L^{(1)}$ ±20% (μH)	$R_{DC}$ Typ (mΩ)	$I_R^{(2)}$ Typ (A)	$I_{SAT\ 25^{\circ}C}^{(3)}$ Typ (A)	$I_{SAT\ 100^{\circ}C}^{(4)}$ Typ (A)
MPL-AT2010-R47	0.47	27	4.5	5.7	5.7
MPL-AT2010-R68	0.68	41	3.6	4.9	4.9
MPL-AT2010-1R0	1.0	50	3.3	4.2	4.2
MPL-AT2010-1R5	1.5	85	2.4	3.2	3.2
MPL-AT2010-2R2	2.2	125	2.0	2.6	2.6
MPL-AT2010-4R7	4.7	215	1.5	1.9	1.9

## GENERAL SPECIFICATIONS

<b>(1) Inductance</b>	Measured at 100kHz, 100mA
<b>(2) Rated Current</b>	Rated current will cause the coil temperature rise $\Delta T$ of 40K <i><math>I_R</math> measured with the inductor soldered in a single-layer PCB. Copper layer thickness 35μm Cu / PCB size 30x50mm. Temperature behavior dependent on circuit design, PCB layout, proximity to other components, and trace dimensions and thickness.</i>
<b>(3) Saturation Current 25°C</b>	Saturation current will cause L to drop from 30% at 25°C ambient temperature
<b>(4) Saturation Current 100°C</b>	Saturation current will cause L to drop from 30% at 100°C ambient temperature
<b>Temperature Test Condition</b>	Electrical specifications measured at 25°C, 35% RH if not given differently
<b>Operating Condition</b>	Operating temperature: -40°C to +125°C (including temp rise) Should not exceed +125°C under worst-case operation conditions
<b>Storage Condition</b>	Tape and Reel packaging: -10°C to +40°C Humidity: <50% RH

## REVISION HISTORY

Revision #	Revision Date	Description	Pages Updated
1.0	7/11/2019	Initial Release	-
1.1	8/1/2019	Updated Impedance vs. Frequency Curve	2
1.2	7/7/2023	Updated the $I_R$ (Typ) and $f_r$ (Typ) values, and made minor formatting edits in the Electrical Characteristics section	1
		Updated all the Typical Performance Curves	2
		Reordered the Dimensions section; updated the Product Package and Recommended Land Pattern images	3
		Updated the following values in the Ordering Information section: <ul style="list-style-type: none"> <li>• MPL-AT2010-R47: Updated <math>I_R</math> (Typ)</li> <li>• MPL-AT2010-R68: Updated <math>I_R</math> (Typ)</li> <li>• MPL-AT2010-1R0: Updated <math>I_R</math> (Typ)</li> <li>• MPL-AT2010-1R5: Updated <math>R_{DC}</math> (Typ)</li> <li>• MPL-AT2010-2R2: Updated <math>R_{DC}</math> (Typ), <math>I_R</math> (Typ), <math>I_{SAT}</math> 25°C (Typ), and <math>I_{SAT}</math> 100°C (Typ)</li> </ul>	4

**Notice:** The information in this document is subject to change without notice. Please contact MPS for current specifications. Users should warrant and guarantee that third-party Intellectual Property rights are not infringed upon when integrating MPS products into any application. MPS will not assume any legal responsibility for any said applications.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Monolithic Power Systems \(MPS\):](#)

[MPL-AT2010-R47](#)