


SMD MOLDED WOUND CHIP INDUCTORS

AIMS-1210



RoHS/RoHS II Compliant



3.2 x 2.5 x 2.2mm

FEATURES:

- High current rating coupled with high Q
- Exceptionally reliable over wide operating temperature and under humid environment
- Resilient to mechanical shocks
- Terminals constructed to withstand excessive pulling force
- Suitable for RoHS compliant reflow soldering

APPLICATIONS:

- VCRs, Video Cameras
- LCD TVs, portable VCRs
- Computer Products & Peripherals

ELECTRICAL SPECIFICATIONS:

PARAMETERS

ABRACON P/N:	AIMS-1210-xxx Series
Operating temperature :	-40°C to + 85°C
Storage temperature :	+5°C to +40°C, Humidity < 70%RH

Part No. AIMS-1210-Inductance Code	L(μH)	Tolerance	Q (min)	Test Freq. (MHz)	SRF(MHz) (min)	DCR(Ω) (max)	Idc(mA) (max)
AIMS-1210-10N	0.010	J, K, M	15	100	2500	0.13	450
AIMS-1210-12N	0.012	J, K, M	17	100	2300	0.14	450
AIMS-1210-15N	0.015	J, K, M	19	100	2100	0.16	450
AIMS-1210-18N	0.018	J, K, M	21	100	1900	0.18	450
AIMS-1210-22N	0.022	J, K, M	23	100	1700	0.20	450
AIMS-1210-27N	0.027	J, K, M	23	100	1500	0.22	450
AIMS-1210-33N	0.033	J, K, M	25	100	1400	0.24	450
AIMS-1210-39N	0.039	J, K, M	25	100	1300	0.27	450
AIMS-1210-47N	0.047	J, K, M	26	100	1200	0.30	450
AIMS-1210-56N	0.056	J, K, M	26	100	1100	0.33	450
AIMS-1210-68N	0.068	J, K, M	27	100	1000	0.36	450
AIMS-1210-82N	0.082	J, K, M	27	100	900	0.40	450
AIMS-1210-R10	0.10	J, K, M	28	100	700	0.44	450
AIMS-1210-R12	0.12	J, K, M	30	25.2	500	0.22	450
AIMS-1210-R15	0.15	J, K, M	30	25.2	450	0.25	450
AIMS-1210-R18	0.18	J, K, M	30	25.2	400	0.28	450
AIMS-1210-R22	0.22	J, K, M	30	25.2	350	0.32	450
AIMS-1210-R27	0.27	J, K, M	30	25.2	320	0.36	450
AIMS-1210-R33	0.33	J, K, M	30	25.2	300	0.40	450
AIMS-1210-R39	0.39	J, K, M	30	25.2	250	0.45	450
AIMS-1210-R47	0.47	J, K, M	30	25.2	220	0.50	450
AIMS-1210-R56	0.56	J, K, M	30	25.2	180	0.55	450
AIMS-1210-R68	0.68	J, K, M	30	25.2	160	0.60	450
AIMS-1210-R82	0.82	J, K, M	30	25.2	140	0.65	450
AIMS-1210-1R0	1.0	J, K, M	30	7.96	120	0.70	400
AIMS-1210-1R2	1.2	J, K, M	30	7.96	100	0.75	390
AIMS-1210-1R5	1.5	J, K, M	30	7.96	85	0.85	370
AIMS-1210-1R8	1.8	J, K, M	30	7.96	80	0.90	350
AIMS-1210-2R2	2.2	J, K, M	30	7.96	75	1.00	320
AIMS-1210-2R7	2.7	J, K, M	30	7.96	70	1.10	290
AIMS-1210-3R3	3.3	J, K, M	30	7.96	60	1.20	260
AIMS-1210-3R9	3.9	J, K, M	30	7.96	55	1.30	250
AIMS-1210-4R7	4.7	J, K, M	30	7.96	50	1.50	220
AIMS-1210-5R6	5.6	J, K, M	30	7.96	45	1.60	200
AIMS-1210-6R8	6.8	J, K, M	30	7.96	40	1.80	180
AIMS-1210-8R2	8.2	J, K, M	30	7.96	35	2.0	170
AIMS-1210-100	10	J, K, M	30	2.52	30	2.1	150
AIMS-1210-120	12	J, K, M	30	2.52	20	2.5	140
AIMS-1210-150	15	J, K, M	30	2.52	20	2.8	130




SMD MOLDED WOUND CHIP INDUCTORS

AIMS-1210



RoHS/RoHS II Compliant



3.2 x 2.5 x 2.2mm

Part No. AIMS-1210-Inductance Code	L(μH)	Tolerance (%)	Q (min)	Test Freq. (MHz)	SRF(MHz) (min)	DCR(Ω) (max)	Idc(mA) (max)
AIMS-1210-180	18	J, K, M	30	2.52	20	3.3	120
AIMS-1210-220	22	J, K, M	30	2.52	20	3.7	110
AIMS-1210-270	27	J, K, M	30	2.52	18	5.0	80
AIMS-1210-330	33	J, K, M	30	2.52	17	5.6	70
AIMS-1210-390	39	J, K, M	30	2.52	16	6.4	65
AIMS-1210-470	47	J, K, M	30	2.52	15	7.0	60
AIMS-1210-560	56	J, K, M	30	2.52	13	8.0	55
AIMS-1210-680	68	J, K, M	30	2.52	12	9.0	50
AIMS-1210-820	82	J, K, M	30	2.52	11	10	45
AIMS-1210-101	100	J, K, M	20	0.796	10	10	40
AIMS-1210-121	120	J, K, M	20	0.796	9	11	70
AIMS-1210-151	150	J, K, M	20	0.796	7	15	65
AIMS-1210-181	180	J, K, M	20	0.796	7	17	60
AIMS-1210-221	220	J, K, M	20	0.796	6	21	50
AIMS-1210-271	270	J, K, M	20	0.796	5	28	45
AIMS-1210-331	330	J, K, M	20	0.796	5	34	40

Test Conditions

Isat: $\Delta L/L$ (initial) $\geq$ -10%

PART NUMBER IDENTIFICATION



AIMS-1210- -

Inductance Code
Please refer to the table above


Tolerance %
J: $\pm$ 5%
K: $\pm$ 10%
M: $\pm$ 20%

Packaging
T: Tape and Reel
(2000pcs / reel)

OUTLINE DIMENSIONS:



Recommended Land Pattern



A	B	C	D	E	F	I	J	H
3.2±0.3	2.5±0.2	2.2±0.2	0.6 ref	0.2 min	1.9±0.1	1.2	2.0	2.0

Dimension: mm




SMD MOLDED WOUND CHIP INDUCTORS

AIMS-1210




RoHS/RoHS II Compliant



3.2 x 2.5 x 2.2mm


REFLOW PROFILE:



Item	mark	
Temperature rise gradient		3°C/sec (max)
Heating time	Tsoak	50s ~ 150s
Heating temperature		120°C~180°C
Time maintained above: -Temperature (T1) -Time(t1)	T1/t1	217°C/60 sec max
Peak temperature	Tpeak	250 max.
Time 25°C to peak		6 minutes max.

TAPE & REEL::

T: 2,000pcs / reel



SECTION A-A

A0	B0	K0	P	F	W	t	A	B	C	D
2.88 ± 0.1	3.65 ± 0.1	2.5 ± 0.1	4 ± 0.1	3.5 ± 0.05	8 ± 0.2	0.25 ± 0.05	9.0 ± 0.5	60 ± 2.0	13.5 ± 0.5	178 ± 2.0

Dimension: mm

ATTENTION: Abracon Corporation's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependant Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon Corporation is required. Please contact Abracon Corporation for more information.

ABRACON IS
ISO 9001:2008
CERTIFIED



ABRACON
CORPORATION

Visit www.abracon.com for Terms & Conditions of Sale

30332 Esperanza, Rancho Santa Margarita, California 92688
tel 949-546-8000| fax 949-546-8001| www.abracon.com

Revised: 10.04.13

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ABRACON:](#)

[AISM-1210-221K-T](#) [AISM-1210-R18M-T](#) [AISM-1210-6R8K-T](#) [AISM-1210-R15M-T](#) [AISM-1210-R56M-T](#) [AISM-1210-R22M-T](#) [AISM-1210-5R6K-T](#) [AISM-1210-1R5K-T](#) [AISM-1210-1R2K-T](#) [AISM-1210-820K-T](#) [AISM-1210-R12M-T](#) [AISM-1210-3R9K-T](#) [AISM-1210-680K-T](#) [AISM-1210-121K-T](#) [AISM-1210-R68M-T](#) [AISM-1210-120K-T](#) [AISM-1210-470K-T](#) [AISM-1210-4R7K-T](#) [AISM-1210-3R3K-T](#) [AISM-1210-100K-T](#) [AISM-1210-R82M-T](#) [AISM-1210-151K-T](#) [AISM-1210-1R0K-T](#) [AISM-1210-390K-T](#) [AISM-1210-2R2K-T](#) [AISM-1210-330K-T](#) [AISM-1210-1R8K-T](#) [AISM-1210-220K-T](#) [AISM-1210-181K-T](#) [AISM-1210-150K-T](#) [AISM-1210-2R7K-T](#) [AISM-1210-R10M-T](#) [AISM-1210-R47M-T](#) [AISM-1210-101K-T](#) [AISM-1210-R27M-T](#) [AISM-1210-270K-T](#) [AISM-1210-8R2K-T](#) [AISM-1210-R33M-T](#) [AISM-1210-R39M-T](#) [AISM-1210-180K-T](#) [AISM-1210-560K-T](#) [AISM-1210-271J-T](#)