


**SERIES****0805R**

# Open Construction Wirewound Surface Mount Inductors



 Actual Size (Max.)

## Physical Parameters

|   | Inches            | Millimeters      |
|---|-------------------|------------------|
| A | 0.090 Max.        | 2.29 Max.        |
| B | 0.068 Max.        | 1.73 Max.        |
| C | 0.060 Max.        | 1.52 Max.        |
| D | 0.050 (Ref. only) | 1.27 (Ref. only) |
| E | 0.018 (Ref. only) | 0.44 (Ref. only) |
| F | 0.040 (Ref. only) | 1.03 (Ref. only) |
| G | 0.070             | 1.78             |
| H | 0.040             | 1.02             |
| I | 0.030             | 0.76             |


**Operating Temperature Range** -40°C to +125°C

**Inductance and Q** tested on HP4291A using HP16193A test fixture, or equivalent

**Packaging** Tape & reel (8mm): 7" reel, 2000 pieces max.

| DASH NUMBER*              | INDUCTANCE (nH) ±10% | INDUCTANCE TEST FREQUENCY (MHz) | FREQUENCY Q MINIMUM | SRF MINIMUM (MHz) | Q TEST FREQUENCY (MHz) | DC RESISTANCE MAXIMUM (OHMS) | CURRENT RATING MAXIMUM (mA) |
|---------------------------|----------------------|---------------------------------|---------------------|-------------------|------------------------|------------------------------|-----------------------------|
| SERIES 0805R CERAMIC CORE |                      |                                 |                     |                   |                        |                              |                             |
| -2N8K                     | 2.8                  | 250                             | 80                  | 1500              | 7900                   | 0.06                         | 800                         |
| -3N0K                     | 3.0                  | 250                             | 65                  | 1500              | 7900                   | 0.06                         | 800                         |
| -3N3K                     | 3.3                  | 250                             | 50                  | 1500              | 6000                   | 0.08                         | 600                         |
| -5N6K                     | 5.6                  | 250                             | 65                  | 1000              | 5500                   | 0.08                         | 600                         |
| -6N8K                     | 6.8                  | 250                             | 50                  | 1000              | 5500                   | 0.11                         | 600                         |
| -7N5K                     | 7.5                  | 250                             | 50                  | 1000              | 4500                   | 0.14                         | 600                         |
| -8N2K                     | 8.2                  | 250                             | 50                  | 1000              | 4700                   | 0.12                         | 600                         |
| -10NK                     | 10                   | 250                             | 60                  | 500               | 4200                   | 0.10                         | 600                         |
| -12NK                     | 12                   | 250                             | 50                  | 500               | 4000                   | 0.15                         | 600                         |
| -15NK                     | 15                   | 250                             | 50                  | 500               | 3400                   | 0.17                         | 600                         |
| -18NK                     | 18                   | 250                             | 50                  | 500               | 3300                   | 0.20                         | 600                         |
| -22NK                     | 22                   | 250                             | 55                  | 500               | 2600                   | 0.22                         | 500                         |
| -24NK                     | 24                   | 250                             | 50                  | 500               | 2000                   | 0.22                         | 500                         |
| -27NK                     | 27                   | 250                             | 55                  | 500               | 2500                   | 0.25                         | 500                         |
| -33NK                     | 33                   | 250                             | 60                  | 500               | 2050                   | 0.27                         | 500                         |
| -36NK                     | 36                   | 250                             | 55                  | 500               | 1700                   | 0.27                         | 500                         |
| -39NK                     | 39                   | 250                             | 60                  | 500               | 2000                   | 0.29                         | 500                         |
| -43NK                     | 43                   | 200                             | 60                  | 500               | 1650                   | 0.34                         | 500                         |
| -47NK                     | 47                   | 200                             | 60                  | 500               | 1650                   | 0.31                         | 500                         |
| -56NK                     | 56                   | 200                             | 60                  | 500               | 1550                   | 0.34                         | 500                         |
| -68NK                     | 68                   | 200                             | 60                  | 500               | 1450                   | 0.38                         | 500                         |
| -82NK                     | 82                   | 150                             | 65                  | 500               | 1300                   | 0.42                         | 400                         |
| -91NK                     | 91                   | 150                             | 65                  | 500               | 1200                   | 0.48                         | 400                         |
| -101K                     | 100                  | 150                             | 65                  | 500               | 1200                   | 0.46                         | 400                         |
| -111K                     | 110                  | 150                             | 50                  | 250               | 1000                   | 0.48                         | 400                         |
| -121K                     | 120                  | 150                             | 50                  | 250               | 1100                   | 0.51                         | 400                         |
| -151K                     | 150                  | 100                             | 50                  | 250               | 920                    | 0.56                         | 400                         |
| -181K                     | 180                  | 100                             | 50                  | 250               | 870                    | 0.64                         | 400                         |
| -221K                     | 220                  | 100                             | 50                  | 250               | 850                    | 0.70                         | 400                         |
| -241K                     | 240                  | 100                             | 44                  | 250               | 690                    | 1.00                         | 350                         |
| -271K                     | 270                  | 100                             | 48                  | 250               | 650                    | 1.00                         | 350                         |
| -331K                     | 330                  | 100                             | 48                  | 250               | 600                    | 1.40                         | 310                         |
| -391K                     | 390                  | 100                             | 48                  | 250               | 560                    | 1.50                         | 290                         |
| -471K                     | 470                  | 50                              | 33                  | 100               | 375                    | 1.70                         | 220                         |
| -561K                     | 560                  | 25                              | 23                  | 50                | 340                    | 1.90                         | 210                         |
| -621K                     | 620                  | 25                              | 23                  | 50                | 220                    | 2.20                         | 210                         |
| -681K                     | 680                  | 25                              | 23                  | 50                | 200                    | 2.20                         | 190                         |
| -751K                     | 750                  | 25                              | 23                  | 50                | 200                    | 2.30                         | 180                         |
| -821K                     | 820                  | 25                              | 23                  | 50                | 200                    | 2.35                         | 180                         |
| -102K                     | 1000                 | 25                              | 20                  | 50                | 100                    | 2.50                         | 170                         |
| -122K                     | 1200                 | 7.9                             | 18                  | 25                | 100                    | 2.50                         | 170                         |
| -152K                     | 1500                 | 7.9                             | 16                  | 25                | 100                    | 2.50                         | 170                         |
| -182K                     | 1800                 | 7.9                             | 16                  | 7.9               | 80                     | 2.50                         | 170                         |
| -222K                     | 2200                 | 7.9                             | 16                  | 7.9               | 60                     | 2.70                         | 160                         |
| -272K                     | 2700                 | 7.9                             | 16                  | 7.9               | 50                     | 2.95                         | 150                         |

## LAND PATTERN DIMENSIONS



Optional Tolerances: 8.2nH & Lower J = 5%

All Other Values: J = 5% G = 2%

\*Complete part # must include series # PLUS the dash #

For surface finish information, refer to [www.delevanfinishes.com](http://www.delevanfinishes.com)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## API Delevan:

[0805R-2N8K](#) [0805R-2N8J](#) [0805R-3N0K](#) [0805R-3N0J](#) [0805R-3N3K](#) [0805R-3N3J](#) [0805R-5N6K](#) [0805R-5N6J](#)  
[0805R-6N8K](#) [0805R-6N8J](#) [0805R-7N5K](#) [0805R-7N5J](#) [0805R-8N2K](#) [0805R-8N2J](#) [0805R-10NK](#) [0805R-10NJ](#)  
[0805R-12NK](#) [0805R-12NJ](#) [0805R-15NK](#) [0805R-15NJ](#) [0805R-18NK](#) [0805R-18NJ](#) [0805R-22NK](#) [0805R-22NJ](#)  
[0805R-24NK](#) [0805R-24NJ](#) [0805R-27NK](#) [0805R-27NJ](#) [0805R-33NK](#) [0805R-33NJ](#) [0805R-36NK](#) [0805R-36NJ](#)  
[0805R-39NK](#) [0805R-39NJ](#) [0805R-43NK](#) [0805R-43NJ](#) [0805R-47NK](#) [0805R-47NJ](#) [0805R-56NK](#) [0805R-56NJ](#)  
[0805R-68NK](#) [0805R-68NJ](#) [0805R-82NK](#) [0805R-82NJ](#) [0805R-91NK](#) [0805R-91NJ](#) [0805R-101K](#) [0805R-101J](#) [0805R-111K](#) [0805R-111J](#) [0805R-121K](#) [0805R-121J](#) [0805R-151K](#) [0805R-151J](#) [0805R-181K](#) [0805R-181J](#) [0805R-221K](#) [0805R-221J](#) [0805R-241K](#) [0805R-241J](#) [0805R-271K](#) [0805R-271J](#) [0805R-331K](#) [0805R-331J](#) [0805R-391K](#) [0805R-391J](#) [0805R-471K](#) [0805R-471J](#) [0805R-561K](#) [0805R-561J](#) [0805R-621K](#) [0805R-621J](#) [0805R-681K](#) [0805R-681J](#) [0805R-751K](#) [0805R-751J](#) [0805R-821K](#) [0805R-821J](#) [0805R-102K](#) [0805R-102J](#) [0805R-122K](#) [0805R-122J](#) [0805R-152K](#) [0805R-152J](#) [0805R-182K](#) [0805R-182J](#) [0805R-222J](#) [0805R-272K](#) [0805R-272J](#) [0805R-15NG](#) [0805R-151G](#) [0805R-271G](#) [0805R-561G](#) [0805R-121G](#)