



SERIES**CM9900R
CM9900**RoHS
CompliantTraditional
First Quality**PC Mount Common Mode Chokes**

Actual Size

**Physical Parameters**

	Inches	Millimeters
A	0.740	18.8
B	0.840	21.3
C	0.670	17.0
D	0.900	22.9
E	0.040	1.0
F	0.025	0.64
G	0.200	5.1
H	0.175	4.4
J	0.750	19.1
K	0.200	5.1
L	0.515	13.1

All dimensions are typical

Operating Temperature Range -55°C to +125°C**Current Rating at 80°C Ambient** 40°C rise**Mechanical Configuration** Tape wrapped winding sections; varnish impregnated assembly.**Notes** 1) Inductance in table is for either L1 or L2.

2) Leakage Inductance tested at L1 with L2 shorted or at L2 with L1 shorted.

3) Windings balanced within 1%.

Packaging Bulk only

DASH NUMBER*

L (μH) L1 or L2
@ 1 kHz ±25%DC RESISTANCE
MAXIMUM (OHMS)CURRENT RATING
MAXIMUM (AMPS)LEAKAGE INDUCTANCE
TYPICAL (μH)**SERIES CM9900 FERRITE CORE**

-473	47	0.016	3.5	4.0
-563	56	0.018	3.5	4.0
-683	68	0.019	3.5	5.0
-823	82	0.023	2.8	5.5
-104	100	0.025	2.8	6.0
-124	120	0.028	2.8	6.5
-154	150	0.030	2.8	7.5
-184	180	0.038	2.2	8.0
-224	220	0.044	2.2	9.0
-274	270	0.051	2.2	10
-334	330	0.058	1.7	11
-474	470	0.078	1.4	16
-564	560	0.091	1.4	18
-684	680	0.115	1.1	20
-824	820	0.131	1.1	25
-105	1000	0.194	0.88	35
-125	1200	0.219	0.88	47
-155	1500	0.278	0.70	49
-185	1800	0.306	0.70	59
-225	2200	0.431	0.55	76
-275	2700	0.469	0.55	91
-335	3300	0.531	0.55	101
-395	3900	0.669	0.44	135
-475	4700	0.760	0.44	158
-565	5600	0.853	0.44	196
-685	6800	1.24	0.35	257
-825	8200	1.40	0.35	296
-106	10000	1.61	0.35	362
-126	12000	1.98	0.27	410
-156	15000	2.24	0.27	503
-186	18000	2.45	0.27	602
-226	22000	3.49	0.22	730
-276	27000	4.60	0.17	870
-336	33000	5.21	0.17	1150
-396	39000	7.19	0.13	1300
-476	47000	7.80	0.13	1541
-566	56000	8.69	0.13	1875
-686	68000	9.69	0.13	2254
-826	82000	13.10	0.10	2702
-107	100000	14.60	0.10	3269
-127	120000	16.00	0.10	3456

*Complete part # must include series # PLUS the dash #

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

API Delevan:

[CM9900-154](#) [CM9900-274](#) [CM9900-473](#) [CM9900-563](#) [CM9900-823](#) [CM9900-104](#) [CM9900-124](#) [CM9900-184](#)
[CM9900-224](#) [CM9900-334](#) [CM9900-474](#) [CM9900-564](#) [CM9900-684](#) [CM9900-824](#) [CM9900-105](#) [CM9900-125](#)
[CM9900-155](#) [CM9900-185](#) [CM9900-225](#) [CM9900-275](#) [CM9900-335](#) [CM9900R-185](#) [CM9900R-104](#) [CM9900R-274](#)
[CM9900R-105](#) [CM9900-107](#) [CM9900R-226](#) [CM9900-566](#) [CM9900-395](#) [CM9900R-276](#) [CM9900R-826](#) [CM9900-106](#)
[CM9900R-184](#) [CM9900R-106](#) [CM9900-685](#) [CM9900R-156](#) [CM9900-565](#) [CM9900R-825](#) [CM9900-186](#) [CM9900R-](#)
[564](#) [CM9900R-473](#) [CM9900R-476](#) [CM9900R-127](#) [CM9900R-565](#) [CM9900R-475](#) [CM9900R-824](#) [CM9900-686](#)
[CM9900R-823](#) [CM9900R-563](#) [CM9900-826](#) [CM9900R-396](#) [CM9900R-335](#) [CM9900-475](#) [CM9900-126](#) [CM9900R-](#)
[683](#) [CM9900-336](#) [CM9900R-686](#) [CM9900R-126](#) [CM9900R-224](#) [CM9900R-225](#) [CM9900-825](#) [CM9900R-275](#)
[CM9900R-154](#) [CM9900-156](#) [CM9900R-107](#) [CM9900-476](#) [CM9900-276](#) [CM9900R-155](#) [CM9900R-125](#) [CM9900-396](#)
[CM9900R-334](#) [CM9900R-395](#) [CM9900R-336](#) [CM9900R-186](#) [CM9900R-124](#) [CM9900R-566](#) [CM9900-127](#)
[CM9900R-684](#) [CM9900R-474](#) [CM9900R-685](#) [CM9900-226](#)