

Molded Inductor (Carbonyl)



AMPLH7025S

Request Samples



Check Inventory



7.3 x 6.6 x 2.2 mm
RoHS/RoHS II Compliant
MSL Level = 1

Features

- Shielded construction
- Soft saturation
- Low DCR, High Efficiency
- Designed for switching frequencies between 100KHz-2MHz

Applications

- DC/DC Switching converters
- Power supplies for Notebooks, workstations, and Servers
- Low Profile applications
- High current, transient load applications

Electrical Specifications

Part Number	Inductance	Tolerance	DC Resistance		Saturation Current	Temperature Rise Current
	0.1MHz/1.0V		Max.	Typ.	Typ.	Typ.
Units	μ H	%	m Ω		A	A
Symbol	L	M	DCR		Isat	Irms
AMPLH7025S-R20M	0.20	± 20	1.9	1.6	41.0	25.0
AMPLH7025S-R33M	0.33	± 20	2.4	2.0	33.0	21.0
AMPLH7025S-R47M	0.47	± 20	4.2	3.6	27.0	19.0
AMPLH7025S-R68M	0.68	± 20	4.6	4.0	23.0	17.0
AMPLH7025S-1R0M	1.00	± 20	6.8	5.9	17.0	15.0
AMPLH7025S-1R5M	1.50	± 20	10.1	8.7	15.0	13.0
AMPLH7025S-2R2M	2.20	± 20	14.7	12.8	12.0	10.0
AMPLH7025S-3R3M	3.30	± 20	27.6	24.0	9.0	8.0
AMPLH7025S-4R7M	4.70	± 20	36.8	32.0	8.0	7.0
AMPLH7025S-5R6M	5.60	± 20	40.2	35.0	7.5	6.5
AMPLH7025S-6R8M	6.80	± 20	50.6	44.0	7.0	6.0
AMPLH7025S-8R2M	8.20	± 20	53.0	46.0	6.0	5.5
AMPLH7025S-100M	10.00	± 20	73.6	64.0	5.5	5.0

Test Conditions

Isat: DC current at which the inductance drops 30% from its initial value.

Irms: DC current that causes the temperature rise (ΔT , approximate 40°C) from 25°C ambient.

Operating Temperature: -40°C ~ +125°C (including self-temperature rise)

Storage Condition: -40°C ~ +125°C (on board), -10°C ~ +40°C (with packaging) and R.H. 85% max.

Operating Voltage: 50V (across inductor)

AMPLH7025S Series is RoHS Compliant and Pb free.

For saturation and temperature rise graphs, please visit [Abracon | Power Inductor Performance Analyzer \(PIPA\)](#)




5101 Hidden Creek Ln, Spicewood TX 78669
Phone: 512-371-6159 Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISION Initial Release :
2/28/2024

ABRACON IS
ISO9001-2015
CERTIFIED

Molded Inductor (Carbonyl)



AMPLH7025S

Request Samples




Check Inventory




7.3 x 6.6 x 2.2 mm
RoHS/RoHS II Compliant
MSL Level = 1

Part Identification




Marking



Marking Method = Ink Marking

Molded Inductor (Carbonyl)



AMPLH7025S

Request Samples




Check Inventory




7.3 x 6.6 x 2.2 mm
RoHS/RoHS II Compliant
MSL Level = 1


Mechanical Specifications




TOP VIEW



FRONT VIEW



BOTTOM VIEW



RECOMMENDED LAND PATTERN

Dimensions: Inches [mm]




5101 Hidden Creek Ln, Spicewood TX 78669
Phone: 512-371-6159 Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISION Initial Release :
2/28/2024

ABRACON IS
ISO9001-2015
CERTIFIED

Molded Inductor (Carbonyl)



AMPLH7025S

Request Samples




Check Inventory




7.3 x 6.6 x 2.2 mm
RoHS/RoHS II Compliant
MSL Level = 1

Materials



	Components	Material
a	Core	Alloy Powder
b	Wire	Polyester Wire
c	Electrode	Cu/Ni/Sn
d	Marking	Ink

Molded Inductor (Carbonyl)



AMPLH7025S

Request Samples




Check Inventory



7.3 x 6.6 x 2.2 mm
RoHS/RoHS II Compliant
MSL Level = 1

Reflow Profile



Zone	Description	Temperature	Times
1	Preheat	$T_{SMIN} \sim T_{SMAX}$ 150°C ~ 200°C	60 ~ 120 sec.
2	Reflow	T_L $\geq 217^\circ\text{C}$	60 ~ 150 sec.
3	Peak heat	T_P 260°C	30 sec. MAX

Time of 25°C to peak temperature: 8 mins Max

Ramp up rate: 3°C/Second max.

Ramp down rate: 6°C/Second max.

Molded Inductor (Carbonyl)



AMPLH7025S

Request Samples




Check Inventory




7.3 x 6.6 x 2.2 mm
RoHS/RoHS II Compliant
MSL Level = 1

Packaging

Tape & Reel: 1500 pcs/reel



A0	B0	W	F	P	D	K0	T
7.10 Ref	8.10 Ref	16.00±0.30	7.50±0.10	12.00±0.10	1.50±0.10	2.70 Ref	0.35±0.05



Type	A	B	C	D
13" x 16mm	16.4+2.0/-0.0	100.0±2.0	13.0+0.5/-0.2	330.0±0.3

Dimensions: mm

ATTENTION: Abracon LLC's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependent Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon LLC is required. Please contact Abracon LLC for more information.



5101 Hidden Creek Ln, Spicewood TX 78669
 Phone: 512-371-6159 Fax: 512-351-8858
 For terms and conditions of sales, please visit:
www.abracon.com

REVISION Initial Release :
2/28/2024

ABRACON IS
 ISO9001-2015
 CERTIFIED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ABRACON:](#)

[AMPLH7025S-5R6M-T](#) [AMPLH7025S-1R5M-T](#) [AMPLH7025S-4R7M-T](#) [AMPLH7025S-R47M-T](#) [AMPLH7025S-100M-](#)
[T](#) [AMPLH7025S-6R8M-T](#) [AMPLH7025S-2R2M-T](#) [AMPLH7025S-3R3M-T](#) [AMPLH7025S-R68M-T](#) [AMPLH7025S-](#)
[R20M-T](#) [AMPLH7025S-1R0M-T](#) [AMPLH7025S-R33M-T](#) [AMPLH7025S-8R2M-T](#) [AMPLH7025S-4R7MT](#)
[AMPLH7025S-2R2MT](#) [AMPLH7025S-6R8MT](#) [AMPLH7025S-8R2MT](#) [AMPLH7025S-5R6MT](#) [AMPLH7025S-1R0MT](#)
[AMPLH7025S-100MT](#) [AMPLH7025S-1R5MT](#) [AMPLH7025S-R68MT](#) [AMPLH7025S-R20MT](#) [AMPLH7025S-R47MT](#)
[AMPLH7025S-3R3MT](#) [AMPLH7025S-R33MT](#)