

External GSM Antenna - Adhesive Mount

APAMS-103

RoHS/RoHS II compliant

Lead in copper alloy exemption (6c); and Lead in glass exemption (7c-I)



78 x 25 x 3.8mm

MSL level: Not Applicable

FEATURES:

- High Reliability/ Sensitivity
- Compact Size
- Easy to Install (adhesive tape base)
- SGS
- ROHS Compliant


TYPICAL APPLICATIONS:

- Wireless Communications
- GSM
- GPRS
- CDMA
- UMTS
- Vehicle Monitoring

STANDARD SPECIFICATIONS:

Parameters	Min.	Typ.	Max.	Units	Note
Frequency Range	870		960	MHz	(GSM900)
	1710		1880	MHz	(GSM1800)
Bandwidth		90		MHz	(@900MHz)
		170		MHz	(@1800MHz)
VSWR at Center Frequency			2.0		
Polarization Model	Linear Polarization				
Impedance		50		Ω	
Gain	2			dBi	
Azimuth	Omni-Directional				
Operating Temperature	-40		+80	°C	
Storage Temperature	-45		+85	°C	

OUTLINE DRAWING:



Parameters	Description
L1(Cable Length)	2m
Cable Type	RG174
Connector	SMA Male
Housing	Black
Mounting Type	Adhesive Tape

Unit: mm

External GSM Antenna - Adhesive Mount

APAMS-103

RoHS/RoHS II compliant
Lead in copper alloy exemption (6c); and Lead in glass exemption (7c-I)



78 x 25 x 3.8mm

PRODUCT IMAGE:



PACKAGING:

Each 475x215x215mm size carton includes 100 pieces of antenna.



CAUTION:

- (1) Do not apply excess mechanical stress to the component body or terminations. Do not attempt to re-form or bend the components as this will cause damage to the component.
- (2) Do not expose the component to open flame.
- (3) This specification applies to the functionality of the component as a single unit. Please insure the component is thoroughly evaluated in the application circuit.

ATTENTION: Abracon Corporation's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependant Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon Corporation is required. Please contact Abracon Corporation for more information.

ABRACON IS
ISO9001:2008
CERTIFIED



Visit www.abracon.com for Terms & Conditions of Sale **Revised: 10.23.14**
30332 Esperanza, Rancho Santa Margarita, California 92688
tel 949-546-8000 | fax 949-546-8001 | www.abracon.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ABRACON:](#)

[APAMS-103](#)