

Programmable – High Performance Low Jitter SMD XO


ASG2-LJ



ESD Sensitive



RoHS / RoHS II Compliant



2.5 x 2.0 x 1.0 mm

Moisture Sensitivity Level (MSL) – 1

FEATURES:

- LVCMOS, LVDS or LVPECL output option
- +2.5V or +3.3V operation
- -40°C to +85°C standard operating temperature range
- Ultra low RMS Jitter: 0.5ps typical, 1.0ps max (12kHz to 20MHz BW)
- Miniature size 2.5 x 2.0 x 1.0 mm Ceramic SMT Package
- Short lead time

APPLICATIONS:

- Networking
- SONET/SDH
- WiMax / WLAN
- Computing
- Phase Locked Loops
- Direct Digital Synthesis (DDS)
- DSL/ADSL
- Base Terminal Stations

STANDARD SPECIFICATIONS:

Parameters		Minimum	Typical	Maximum	Units	Notes
Operating Temperature		-40		+85	°C	
Storage Temperature		-55		+125	°C	
Overall Frequency Stability		-50		+50	ppm	See Note # 1
Initial Tolerance + Stability over operating temperature		-35.00		+35.00	ppm	
Supply Voltage (V _{dd})	V _{dd} = 3.3V	3.135	3.300	3.465	V	
	V _{dd} = 2.5V	2.375	2.500	2.625	V	
Enable/Disable Function :		"1" (V _{IH} ≥ 0.7*V _{dd}) or Open: Oscillation "0" (V _{IL} < 0.3*V _{dd}) : High Z				
Phase jitter RMS (12kHz to 20MHz BW)			0.5	1	ps	

Note #1: Inclusive of initial tolerance at 25°C±3°C, operating temperature range, input voltage variation, load variation & 15 years aging at 25°C.

Key Electrical Specifications – LVCMOS

Parameters		Minimum	Typical	Maximum	Units	Notes
Frequency Range		8		200	MHz	
Supply Current (I _{dd})				40	mA	
Output Logic Level	V _{OH}	0.9*V _{dd}			V	I = ±6mA
	V _{OL}			0.1*V _{dd}	V	
Rise Time	T _r			3	ns	10% to 90%
Fall Time	T _f			3	ns	
Duty Cycle		48	50	52	%	
Output Load				15	pF	

Key Electrical Specifications – LVDS

Parameters		Minimum	Typical	Maximum	Units	Notes
Frequency Range		8		1500	MHz	
Supply Current (I _{dd})				40	mA	Freq. dependent
Differential Output Voltage Swing			350		mV	
Duty Cycle		45		55	%	@1.25V
Rise Time	T _r			600	ps	RL=100Ω/CL=10pF
Fall Time	T _f			600		

Key Electrical Specifications – LVPECL

Parameters		Minimum	Typical	Maximum	Units	Notes
Frequency Range		8		1500	MHz	
Supply Current (I _{dd})				65	mA	Freq. dependent
Output Logic Level	V _{OH}	V _{dd} - 1.025			V	50Ω nominal load
	V _{OL}			V _{dd} - 1.62	V	
Duty Cycle		45		55	%	@V _{dd} -1.3V
Rise Time	T _r			600	ps	20% to 80%
Fall Time	T _f			600		

Programmable – High Performance Low Jitter SMD XO


ASG2-LJ



ESD Sensitive




RoHS / RoHS II Compliant




2.5 x 2.0 x 1.0 mm

TEST CIRCUIT


LVC MOS Output:



LVDS Output:



LVPECL Output:



Programmable – High Performance Low Jitter SMD XO


ASG2-LJ



ESD Sensitive



RoHS / RoHS II Compliant



2.5 x 2.0 x 1.0 mm

OPTIONS & PART IDENTIFICATION:

ASG2 - LJ - MHz - -

Frequency

See Table below for available frequencies

Configuration Code

See Table below for available configurations


Packaging

Blank = Bulk

T = Tape & Reel(3k/reel)

Table of Available Configurations

Abracon P/N	Frequency (MHz)	Freq. Stability Over Temperature (ppm)	Operating Temperature (°C)	Supply Voltage (V)	Output Type
ASG2-LJ-100.000MHz-513259	100	±35	-40 to +85	3.3	LVPECL
ASG2-LJ-125.000MHz-513280	125	±35	-40 to +85	3.3	LVPECL
ASG2-LJ-125.000MHz-513281	125	±35	-40 to +85	2.5	LVPECL
ASG2-LJ-156.250MHz-513282	156.25	±35	-40 to +85	3.3	LVPECL
ASG2-LJ-156.250MHz-513283	156.25	±35	-40 to +85	2.5	LVPECL
ASG2-LJ-200.000MHz-513284	200	±35	-40 to +85	3.3	LVPECL
ASG2-LJ-212.500MHz-513285	212.5	±35	-40 to +85	3.3	LVPECL
ASG2-LJ-250.000MHz-513286	250	±35	-40 to +85	3.3	LVPECL
ASG2-LJ-312.500MHz-513287	312.5	±35	-40 to +85	3.3	LVPECL
ASG2-LJ-285.000MHz-516733	285	±35	-40 to +85	3.3	LVPECL
ASG2-LJ-400.000MHz-513288	400	±35	-40 to +85	3.3	LVPECL



OPTIONS & PART IDENTIFICATION:

Table of Available Configurations (continued)

Abrakon P/N	Frequency (MHz)	Freq. Stability Over Temperature (ppm)	Operating Temperature (°C)	Supply Voltage (V)	Output Type
ASG2-LJ-1000.000MHz-513289	1000	±35	-40 to +85	3.3	LVPECL
ASG2-LJ-100.000MHz-513290	100	±35	-40 to +85	2.5	LVDS
ASG2-LJ-125.000MHz-513291	125	±35	-40 to +85	2.5	LVDS
ASG2-LJ-156.250MHz-513292	156.25	±35	-40 to +85	2.5	LVDS
ASG2-LJ-200.000MHz-513293	200	±35	-40 to +85	2.5	LVDS
ASG2-LJ-212.500MHz-513294	212.5	±35	-40 to +85	2.5	LVDS
ASG2-LJ-250.000MHz-513295	250	±35	-40 to +85	2.5	LVDS
ASG2-LJ-312.500MHz-513296	312.5	±35	-40 to +85	2.5	LVDS
ASG2-LJ-400.000MHz-513297	400	±35	-40 to +85	2.5	LVDS
ASG2-LJ-100.000MHz-513298	100	±35	-40 to +85	2.5	LVC MOS
ASG2-LJ-125.000MHz-513299	125	±35	-40 to +85	2.5	LVC MOS
ASG2-LJ-156.250MHz-513300	156.25	±35	-40 to +85	2.5	LVC MOS
ASG2-LJ-200.000MHz-513301	200	±35	-40 to +85	2.5	LVC MOS
ASG2-LJ-1500.000MHz-515410	1500	±50 (Including 10-year aging)	-40 to +85	3.3	LVPECL

Programmable – High Performance Low Jitter SMD XO


ASG2-LJ



ESD Sensitive





RoHS / RoHS II Compliant



2.5 x 2.0 x 1.0 mm


OUTLINE DIMENSION:



Pin #	Pin Description	
	LVC MOS	LVDS/LVPECL
1	Output Enable (OE)	
2	No Connect (N/C)	
3	GND	
4	RF Output	
5	No Connect (N/C)	Complimentary Output
6	Vdd	

Dimensions: mm

RECOMMENDED REFLOW PROFILE



REVISED: 11.15.2017

Programmable – High Performance Low Jitter SMD XO


ASG2-LJ



ESD Sensitive





RoHS / RoHS II Compliant



2.5 x 2.0 x 1.0 mm

TAPE & REEL:

T= Tape and reel (3,000pcs/reel)



Dimensions: mm

ATTENTION: Abracon LLC products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependant Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon LLC is required. Please contact Abracon LLC for more information.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ABRACON:

[ASG2-LJ-100.000MHz-513298-T](#) [ASG2-LJ-100.000MHz-513259](#) [ASG2-LJ-100.000MHz-513259-T](#) [ASG2-LJ-125.000MHz-513280](#) [ASG2-LJ-125.000MHz-513280-T](#) [ASG2-LJ-125.000MHz-513281](#) [ASG2-LJ-125.000MHz-513281-T](#) [ASG2-LJ-156.250MHz-513282](#) [ASG2-LJ-156.250MHz-513282-T](#) [ASG2-LJ-156.250MHz-513283](#) [ASG2-LJ-156.250MHz-513283-T](#) [ASG2-LJ-200.000MHz-513284](#) [ASG2-LJ-200.000MHz-513284-T](#) [ASG2-LJ-212.500MHz-513285](#) [ASG2-LJ-212.500MHz-513285-T](#) [ASG2-LJ-250.000MHz-513286](#) [ASG2-LJ-250.000MHz-513286-T](#) [ASG2-LJ-312.500MHz-513287](#) [ASG2-LJ-312.500MHz-513287-T](#) [ASG2-LJ-400.000MHz-513288](#) [ASG2-LJ-400.000MHz-513288-T](#) [ASG2-LJ-1000.000MHz-513289](#) [ASG2-LJ-1000.000MHz-513289-T](#) [ASG2-LJ-100.000MHz-513290](#) [ASG2-LJ-100.000MHz-513290-T](#) [ASG2-LJ-125.000MHz-513291](#) [ASG2-LJ-125.000MHz-513291-T](#) [ASG2-LJ-156.250MHz-513292](#) [ASG2-LJ-156.250MHz-513292-T](#) [ASG2-LJ-200.000MHz-513293](#) [ASG2-LJ-200.000MHz-513293-T](#) [ASG2-LJ-212.500MHz-513294](#) [ASG2-LJ-212.500MHz-513294-T](#) [ASG2-LJ-250.000MHz-513295](#) [ASG2-LJ-250.000MHz-513295-T](#) [ASG2-LJ-312.500MHz-513296](#) [ASG2-LJ-312.500MHz-513296-T](#) [ASG2-LJ-400.000MHz-513297](#) [ASG2-LJ-400.000MHz-513297-T](#) [ASG2-LJ-125.000MHz-513299](#) [ASG2-LJ-125.000MHz-513299-T](#) [ASG2-LJ-156.250MHz-513300](#) [ASG2-LJ-156.250MHz-513300-T](#) [ASG2-LJ-200.000MHz-513301](#) [ASG2-LJ-200.000MHz-513301-T](#) [ASG2-LJ-100.000MHz-513298](#)