

Programmable - High Performance

SMD XO & VCXO (LVPECL Output)


ASG2-P



ESD Sensitive



RoHS / RoHS II Compliant



2.5 x 2.0 x 1.0 mm

Moisture Sensitivity Level (MSL) – 1

FEATURES:

- +2.5V or +3.3V operation
- -40°C to +85°C standard operating temperature range
- Miniature size 2.5 x 2.0 x 1.0 mm Ceramic SMT Package
- Short lead time

APPLICATIONS:

- Networking
- SONET/SDH
- WiMax / WLAN
- Computing
- Phase Locked Loops
- Direct Digital Synthesis (DDS)
- DSL/ADSL
- Base Terminal Stations

STANDARD SPECIFICATIONS:

Parameters		Minimum	Typical	Maximum	Units	Notes
Frequency Range		8		1500	MHz	
Operating Temperature		-40		+85	°C	
Storage Temperature		-55		+125	°C	
Overall Frequency Stability		-50		+50	ppm	<i>See Note # 1</i>
Initial Tolerance + Stability over operating temperature		-35.00		+35.00	ppm	
Supply Voltage (Vdd)	V _{dd} = 3.3V	3.135	3.300	3.465	V	
	V _{dd} = 2.5V	2.375	2.500	2.625	V	
Input Current				65	mA	Frequency dependent
LVPECL Output (OUT & $\overline{\text{OUT}}$)	Output High Voltage	V _{dd} - 1.025			V	50Ω nominal load
	Output Low Voltage			V _{dd} - 1.62	V	50Ω nominal load
	Duty Cycle	45		55	%	@V _{dd} -1.3V
	Rise Time			600	ps	80%/20%
	Fall Time			600	ps	80%/20%
Enable/Disable Function :		"1" (V _{IH} ≥ 0.7*V _{dd}) or Open: Oscillation "0" (V _{IL} < 0.3*V _{dd}) : High Z				
Control Voltage Range		0		V _{dd}	V	For VCXO Only
Absolute Pull Range		±35			ppm	For VCXO Only
Control Port Bandwidth		10			kHz	For VCXO Only
Linearity				15	%	For VCXO Only
Slope		Positive				For VCXO Only
Phase jitter RMS (12kHz to 20MHz offset)			1.0	1.8	ps	<i>See Note #2</i>

Note #1: Inclusive of initial tolerance at 25°C±3°C, operating temperature range, input voltage variation, load variation & 15 years aging at 25°C.

Note #2: The rms jitter integrated over 12kHz to 20MHz Bandwidth is dependent on the carrier and whether or not the final frequency is achieved without engaging the Fractional Mode

Programmable - High Performance SMD XO & VCXO (LVPECL Output)


ASG2-P



ESD Sensitive




RoHS / RoHS II Compliant



2.5 x 2.0 x 1.0 mm

TEST CIRCUIT



OPTIONS & PART IDENTIFICATION:

ASG2 - P - - - MHz -

Fixed or Pull-able

X = Fixed Oscillator

V = VCXO

Operating Voltage

3.30V = A

2.50V = B

Frequency in MHz



Please specify the
Frequency in MHz
e.g. 100.000 MHz

Packaging

Blank = Bulk

T = Tape & Reel

RECOMMENDED REFLOW PROFILE



Programmable - High Performance

SMD XO & VCXO (LVPECL Output)


ASG2-P



ESD Sensitive



RoHS / RoHS II Compliant




2.5 x 2.0 x 1.0 mm

OUTLINE DIMENSION:


Pin #	Pin Description For VCXO configuration
1	Voltage Control for VCXO
2	Output Enable (OE) <i>or</i> No Connect (N/C)
3	GND
4	RF Output
5	Complimentary Output
6	Vdd

Pin #	Pin Description For XO configuration
1	Output Enable (OE)
2	No Connect (N/C) for XO
3	GND
4	RF Output
5	Complimentary Output
6	Vdd


Top View



Bottom View



Recommended Land Pattern



Side View



Dimensions: mm

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ABRACON:](#)

[ASG2-P-X-A-120.000MHZ](#) [ASG2-P-X-B-120.000MHZ](#) [ASG2-P-V-A-120.000MHZ](#) [ASG2-P-V-B-120.000MHZ](#) [ASG2-P-X-B-320.000MHZ](#) [ASG2-P-V-A-320.000MHZ](#) [ASG2-P-V-B-320.000MHZ](#) [ASG2-P-X-A-500.000MHz](#) [ASG2-P-X-B-500.000MHZ](#) [ASG2-P-V-A-500.000MHZ](#) [ASG2-P-V-B-500.000MHZ](#) [ASG2-P-X-A-644.53125MHZ](#) [ASG2-P-X-B-644.53125MHz](#) [ASG2-P-X-B-644.53125MHZ-T](#) [ASG2-P-V-A-644.53125MHZ](#) [ASG2-P-V-B-644.53125MHZ](#) [ASG2-P-X-A-698.812334MHZ](#) [ASG2-P-X-B-698.812334MHZ](#) [ASG2-P-V-A-698.812334MHZ](#) [ASG2-P-V-B-698.812334MHZ](#) [ASG2-P-X-A-1000.000MHZ](#) [ASG2-P-X-B-1000.000MHZ](#) [ASG2-P-V-A-1000.000MHZ](#) [ASG2-P-V-B-1000.000MHZ](#)