

ECN/PCN No.: 3706

For Manufacturer			
Product Description: SMD Crystal Oscillator		Abracon Part Number / Part Series: ASG-ULJ	
Affected Revision: A		New Revision: EOL	
		Application: ☒ Series ☐ Part Number ☐ Safety ☒ Non-Safety	
Prior to Change: ASG-ULG Rev A 06/20/18			
After Change: EOL			
Cause/Reason for Change: Discontinuation of production capability			
Change Plan			
Effective Date: 11/10/2020		Additional Remarks:	
Change Declaration: End of Life			
Issued Date: 11/10/2020		Issued By: Stephanie Lopez	
		Issued Department: Engineering	
Approval: Thomas Culhane Engineering Director		Approval: Reuben Quintanilla Quality Director	
		Approval: Ying Huang Purchasing Director	
For Abracon EOL only			
Last Time Buy (if applicable): None		Alternate Part Number / Part Series: AK7	
Additional Approval:		Additional Approval:	
		Additional Approval:	
Customer Approval (If Applicable)			
Qualification Status: ☐ Approved ☐ Not accepted			
Note: It is considered approved if there is no feedback from the customer 1 month after ECN/PCN is released.			
Customer Part Number:		Customer Project:	
Company Name:		Company Representative:	
		Representative Signature:	
Customer Remarks:			

Ultra Low Jitter SMD Crystal Oscillator

ASG-ULJ



RoHS
Compliant



7.0 x 5.0 x 1.5 mm

Moisture Sensitivity Level (MSL) – 1

FEATURES:

- Ultra low phase Jitter: 0.2ps max integrated 12 kHz to 20 MHz BW
- ± 50 ppm total frequency stability over -40°C to $+85^{\circ}\text{C}$ temperature range
- Output type: LVCMOS, LVPECL, LVDS
- Industry standard ceramic SMD package: 7.0 x 5.0 mm

APPLICATIONS:

- Fiber Channel 10G/12G SERDES
- 10/40/400 Gigabit Ethernet
- PCI-Express
- Storage
- Communications
- Backplane reference clock
- FPGA

STANDARD SPECIFICATIONS:

Key Electrical Specifications

Parameters		Minimum	Typical	Maximum	Units	Notes
Operating Temperature		-40		+85	$^{\circ}\text{C}$	
Storage Temperature		-55		+125	$^{\circ}\text{C}$	
Overall Frequency Stability		-50		+50	ppm	See Note # 1
Initial Tolerance + Stability over operating temperature		-35.00		+35.00	ppm	
Supply Voltage (Vdd)	V _{dd} = 3.3V	3.135	3.300	3.465	V	
	V _{dd} = 2.5V	2.375	2.500	2.625	V	
Enable/Disable Function :		"1" (V _{IH} $\geq$ 0.7*V _{dd}) or Open: Oscillation "0" (V _{IL} $<$ 0.3*V _{dd}) : High Z				
Phase jitter RMS (12kHz to 20MHz BW)				0.2	ps	at 25 $^{\circ}\text{C}$

Note #1: Inclusive of initial tolerance at 25 $^{\circ}\text{C} \pm 3^{\circ}\text{C}$, operating temperature range, input voltage variation, load variation & 10 years aging at 25 $^{\circ}\text{C}$.

Key Electrical Specifications – LVCMOS

Parameters		Minimum	Typical	Maximum	Units	Notes
Frequency Range		1		200	MHz	
Supply Current (I _{dd})				40	mA	
Output Logic Level	V _{OH}	0.9*V _{dd}			V	I = ± 6 mA
	V _{OL}			0.1*V _{dd}	V	
Rise Time	T _r			3	ns	10% to 90%
Fall Time	T _f			3	ns	
Duty Cycle		45	50	55	%	
Output Load				15	pF	

Key Electrical Specifications – LVDS

Parameters		Minimum	Typical	Maximum	Units	Notes
Frequency Range		1		705.8	MHz	
Supply Current (I _{dd})				80	mA	Freq. dependent
Differential Output Voltage Swing			350		mV	
Duty Cycle		45		55	%	@1.25V
Rise Time	T _r			0.6	ns	RL=100 Ω /CL=10pF
Fall Time	T _f			0.6		

ASG-ULJ



Parameters		Minimum	Typical	Maximum	Units	Notes
Frequency Range		1		705.8	MHz	
Supply Current (I _{dd})				120	mA	Freq. dependent
Output Logic Level	V _{OH}	V _{dd} - 1.03			V	50Ω nominal load
	V _{OL}			V _{dd} - 1.6	V	
Duty Cycle		45		55	%	@Vdd-1.3V
Rise Time	Tr			0.6	ns	20% to 80%
Fall Time	Tf			0.6		



7.0 x 5.0 x 1.5 mm

PART IDENTIFICATION:

ASG - ULJ - MHz - -

Frequency

See Table below for
available frequencies

Configuration Code

See Table below for
available configurations

Packaging

Blank = Bulk
T = Tape & Reel(1k/reel)

Table of Available Configurations

Abrakon P/N	Frequency (MHz)	Overall Freq. Stability max ⁽¹⁾ (ppm)	Operating Temperature (°C)	Aging (years)	RMS Jitter max ⁽²⁾ (ps)	Supply Voltage (V)	Supply Current max. (mA)	Output Type
ASG-ULJ-156.250MHz-514613	156.250	±50	-40 to +85	10	0.15	3.3	75	LVPECL
ASG-ULJ-190.000MHz-514594	190.000	±50	-40 to +85	10	0.15 (12kHz to 5MHz BW)	3.3	40	LCVMOS
ASG-ULJ-156.250MHz-514644	156.250	±50	-40 to +85	10	0.15	2.5	75	LVPECL
ASG-ULJ-705.800MHz-514676	705.800	±50	-40 to +85	10	0.10	3.3	85	LVPECL
ASG-ULJ-100.000MHz-514895	100.000	±50	-40 to +85	10	0.15	2.5	75	LVPECL
ASG-ULJ-114.285MHz-515136	114.285	±25	-40 to +85	5	0.10 (12kHz to 5MHz BW)	3.3	30	LCVMOS
ASG-ULJ-156.250MHz-517114	156.250	±35	-40 to +85	10	0.15	3.3	75	LVPECL
ASG-ULJ-125.000MHz-514807	125.000	±35	-40 to +85	10	0.20	3.3	75	LVPECL
ASG-ULJ-114.285MHz-512383	114.285	±50	-40 to +85	10	0.10	3.3	40	LCVMOS
ASG-ULJ-98.304MHz-509595	98.304	±50	-40 to +85	10	0.10	3.3	40	LCVMOS

Note:

1. Inclusive of initial tolerance at 25°C±3°C, operating temperature range, input voltage variation, load variation & aging at 25°C.
2. RMS Jitter Max is defined over 12kHz to 20MHz BW from the carrier at 25°C, unless otherwise specified
3. Please contact Abracon for the availability of other configurations.

Ultra Low Jitter SMD Crystal Oscillator

ASG-ULJ




RoHS
Compliant





7.0 x 5.0 x 1.5 mm

OUTLINE DIMENSIONS:




Top View

Recommended Land Pattern



Bottom View



Side View

Pin #	Pin Description	
	LVC MOS	LVDS/LVPECL
1	Output Enable (OE) or No Connect (N/C)	
2	No Connect (N/C) or Output Enable (OE)	
3	GND	
4	RF Output	
5	No Connect (N/C)	Complimentary Output
6	Vdd	

Abracon P/N	OE Pin #
ASG-ULJ-156.250MHz-514613	1
ASG-ULJ-190.000MHz-514594	1
ASG-ULJ-156.250MHz-514644	1
ASG-ULJ-705.800MHz-514676	2
ASG-ULJ-100.000MHz-514895	1
ASG-ULJ-114.285MHz-515136	1
ASG-ULJ-156.250MHz-517114	1
ASG-ULJ-125.000MHz-514807	1


Dimensions: mm

Ultra Low Jitter SMD Crystal Oscillator

ASG-ULJ




RoHS
Compliant




7.0 x 5.0 x 1.5 mm

RECOMMENDED REFLOW PROFILE



TAPE & REEL:

T= Tape and reel (1,000pcs/reel)



Dimensions: mm

ATTENTION: Abracon LLC's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependant Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon LLC is required. Please contact Abracon LLC for more information.

ABRACON IS
ISO9001:2015
CERTIFIED



5101 Hidden Creek Lane Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sale please visit:
www.abracon.com

Revised: 06.20.2018

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ABRACON:

[ASG-ULJ-125.000MHz-514807-T](#) [ASG-ULJ-100.000MHz-514895-T](#) [ASG-ULJ-114.285MHz-515136-T2](#) [ASG-ULJ-100.000MHz-514895-T2](#) [ASG-ULJ-156.250MHz-514613-T2](#) [ASG-ULJ-190.000MHz-514594-T2](#) [ASG-ULJ-156.250MHz-514644-T](#) [ASG-ULJ-125.000MHz-514807-T2](#) [ASG-ULJ-156.250MHz-514613-T](#) [ASG-ULJ-705.800MHz-514676-T](#) [ASG-ULJ-156.250MHz-514644-T2](#) [ASG-ULJ-705.800MHz-514676-T2](#) [ASG-ULJ-190.000MHz-514594-T](#) [ASG-ULJ-114.285-MHz-512382-T2](#)