

LOW PROFILE SHIELDED SMD CHIP POWER INDUCTOR

ASPI-0412FS



RoHS/RoHS II Compliant



4.0 x 4.0 x 1.2mm

FEATURES:

- Small size and low profile: 1.2mm max
- Small DCR and high rated current
- High reliability to mechanical strength
- Shielded by magnetic powder molding
- Suitable for RoHS compliant reflow

APPLICATIONS:

- Mobile phones
- MP3, MP4 and other portable / communication products
- Digital cameras

ELECTRICAL SPECIFICATIONS:

Abrakon P/N:	ASPI-0412FS Series
Operating Temperature & Humidity	-25°C to +125°C
Storage Temperature & Humidity:	-5°C to +40°C and RH 70% Max. (In tape and reel)

Part Number ASPI-0412FS- Inductance Code	Inductance	L Tolerance	DC Resistance Typ	DC Resistance Max	Saturation Current	Temperature Rise Current	Inductance Code
Units	μH	—	Ω	Ω	A	A	
Symbol	L	N, M	DCR	DCR	Isat	Irms	
ASPI-0412FS-R82	0.82	N	0.050	0.0650	3.02	1.65	R82
ASPI-0412FS-1R0	1.0	N	0.050	0.0650	2.61	1.65	1R0
ASPI-0412FS-1R5	1.5	N	0.065	0.8450	2.10	1.46	1R5
ASPI-0412FS-1R8	1.8	N	0.080	0.1040	2.12	1.32	1R8
ASPI-0412FS-2R2	2.2	M	0.080	0.1040	1.76	1.32	2R2
ASPI-0412FS-2R 7	2.7	M	0.090	0.117 0	1.90	1.25	2R7
ASPI-0412FS-3R3	3.3	M	0.110	0.143 0	1.72	1.12	3R3
ASPI-0412FS-3R6	3.6	M	0.110	0.143 0	1.20	1.12	3R6
ASPI-0412FS-4R 3	4.3	M	0.140	0.1820	1.58	1.00	4R3
ASPI-0412FS-4R 7	4.7	M	0.175	0.2280	1.15	1.05	4R7
ASPI-0412FS-5R1	5.1	M	0.155	0.2015	1.55	0.95	5R1
ASPI-0412FS-5R6	5.6	M	0.140	0.1820	1.00	1.00	5R6
ASPI-0412FS-6R8	6.8	M	0.198	0.257 4	0.85	0.84	6R8
ASPI-0412FS-100	10	M	0.353	0.4590	0.80	0.77	100
ASPI-0412FS-120	12	M	0.290	0.377 0	0.66	0.70	120
ASPI-0412FS-150	15	M	0.340	0.4420	0.56	0.64	150
ASPI-0412FS-180	18	M	0.470	0.6110	0.55	0.55	180
ASPI-0412FS-220	22	M	0.720	0.93 60	0.46	0.49	220
ASPI-0412FS-270	27	M	0.720	0.93 60	0.50	0.45	270
ASPI-0412FS- 330	33	M	0.810	1.053 0	0.42	0.42	330
ASPI-0412FS-360	36	M	0.900	1.17 00	0.40	0.40	360
ASPI-0412FS-390	39	M	1.100	1.48 00	0.55	0.37	390
ASPI-0412FS-470	47	M	1.100	1.48 00	0.35	0.37	470
ASPI-0412FS-560	56	M	1.250	1.6250	0.33	0.33	560
ASPI-0412FS-680	68	M	1.950	2.53 50	0.38	0.27	680
ASPI-0412FS-820	82	M	2.140	2.7820	0.28	0.26	820
ASPI-0412FS-101	100	M	2.210	2.8730	0.25	0.25	101

LOW PROFILE SHIELDED SMD CHIP POWER INDUCTOR

ASPI-0412FS



RoHS/RoHS II Compliant



4.0 x 4.0 x 1.2mm

Test Conditions:

1. Inductance: ZM2355 LCR meter or equivalent
2. RDC: HIOKI 3540 or equivalent
3. Isat : Based on inductance change ($\Delta L/L_0 : \leq -30\%$)
4. Irms : Based on temperature rise ($\Delta T : 40^\circ\text{C TYP.}$)
5. Test Freq: 100KHz, 1Vrms

OPTIONS AND PART IDENTIFICATION

ASPI-0412FS--

Inductance Code

Please refer to the Electrical Spec Table

Tolerance

N: $\pm 30\%^*$

M: $\pm 20\%^*$



*N for L = 0.82 ~ 1.8 μH

*M for L = 2.2 ~ 100 μH


Packaging

T4: Tape and Reel
(4.5kpcs / reel)

OUTLINE DRAWING:



Recommended Land Pattern



A	B	C Max.
4.0 $\pm$ 0.2	4.0 $\pm$ 0.2	1.2

Dimension: mm

Materials

No	Components	Material
1	Ferrite Core	Ni-Zn Ferrite
2	Wire	Polyurethane System enameled copper wire
3	Magnetic Glue	Epoxy resin and magnetic powder
4	Plating Electrodes	Plating: Ag/Ni/Sn
5	Outer Electrodes	Top surface solder coating: Sn/Ag/Cu

LOW PROFILE SHIELDED SMD CHIP POWER INDUCTOR

ASPI-0412FS




RoHS/RoHS II Compliant




4.0 x 4.0 x 1.2mm

TAPE & REEL:

T4: 4,500pcs / reel




A_0	B_0	W	E	F	P_0	P_1	P_2	D_0	T	K_0
4.3 ± 0.1	4.3 ± 0.1	12.0 ± 0.3	1.75 ± 0.1	5.5 ± 0.1	4.0 ± 0.1	8.0 ± 0.1	2.0 ± 0.05	$1.5 + 0.1 / - 0.0$	0.35 ± 0.03	1.6 ± 0.1



Dimension: mm

REFLOW PROFILE:



ATTENTION: Abracon LLC's products are COTS – Commercial-Of-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependent Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon LLC is required. Please contact Abracon LLC for more information.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ABRACON:](#)

[ASPI-0412FS-100M-T4](#) [ASPI-0412FS-220M-T4](#) [ASPI-0412FS-2R2M-T4](#) [ASPI-0412FS-3R3M-T4](#) [ASPI-0412FS-4R7M-T4](#) [ASPI-0412FS-6R8M-T4](#) [ASPI-0412FS-KIT](#) [ASPI-0412FS-180M-T](#) [ASPI-0412FS-1R8N-T4](#)