

Features

- Tolerances down to 10 PPM
- Stabilities down to 5 PPM
- Temperature Ranges as wide as -55°C to +125°C


STANDARD SPECIFICATIONS	
PARAMETERS	MAX (Unless otherwise noted)
Frequency Range	7.3728 ~ 133.000 MHz
Frequency Tolerance @ 25°C	(See options below)
Frequency Stability, ref 25°C	(See options below)
Temperature Range	
Operating (T _{OPR})	(See options below)
Storage (T _{STG})	-55°C ~ +125°C
Shunt Capacitance (C ₀)	5.0 pF
Load Capacitance (C _L)	(See options below)
Drive Level	100µW
Aging per year (@ 25°C)	±5 PPM
Maximum Soldering Temp / Time	260°C / 10 Seconds x 2
Moisture Sensitivity Level (MSL) per J-STD-033	1
Termination Finish	Au over Ni
Seal Method	Seam
Lead (Pb) Free	Yes
RoHS Compliant	Yes

Frequency Range (MHz)	Operating Mode	Max ESR Ω
7.3728 ~ 7.999999	Fundamental	100
8.000 ~ 9.999999	Fundamental	70
10.000 ~ 11.999999	Fundamental	50
12.000 ~ 19.999999	Fundamental	30
20.000 ~ 24.999999	Fundamental	25
25.000 ~ 200.000	Fundamental	20
40.000 ~ 51.999999	3 RD OT	100
52.000 ~ 71.999999	3 RD OT	80
72.000 ~ 133.000	3 RD OT	70


AVAILABLE OPERATING TEMPERATURES AND STABILITIES*								
Operating Temperature	±5 PPM	±10 PPM	±15 PPM	±20 PPM	±25 PPM	±30 PPM	±50 PPM	±100 PPM
0°C ~ +70°C	X	O	O	O	O	O	O	N/A
-10°C ~ +60°C	O	O	O	O	O	O	O	N/A
-10°C ~ +70°C	X	O	O	O	O	O	O	N/A
-20°C ~ +70°C	X	O	O	O	O	O	O	N/A
-30°C ~ +85°C	X	X	O	O	O	O	O	N/A
-40°C ~ +85°C	X	X	O	O	O	O	O	N/A
-40°C ~ +105°C	X	X	X	X	X	X	O	O
-40°C ~ +125°C	X	X	X	X	X	X	O	O
-55°C ~ +125°C	X	X	X	X	X	X	O	O

Key: O = Available, X = Not Available, N/A=Not Applicable, *Does not imply a stocked part.

DIMENSIONS / MECHANICAL SPECIFICATIONS



Recommended Solder Pad Layout



Note: Dimensional drawing is for reference to critical specifications defined by size measurements. Certain non-critical visual attributes, such as side castellations, etc. may vary.


FC6BS

(Former FMB)

6mm x 3.5mm
Ceramic SMD Crystal



TAPE SPECIFICATIONS (mm)							REEL SPECIFICATIONS (mm)						
A	B	C	D	E	F	REEL QTY	G	H	I	J	K	L	M
ø1.55	4.0	8.0	5.5	12.0	1.8	-T1 = 1,000 -T2 = 2,000	2.0	ø13	ø21	ø80	ø178	13.5	2.0



Available Options & Part Identification for Ceramic SMD Crystal FC6BS ¹							
Sample PN: <u>FC6BSCCEM25.0-T1</u>							
F	C6BS	C	C	E	M	25.0	-T1
Fox	Model Number	Tolerance	Stability	Load Capacitance²	Operating Temperature	Frequency (MHz)	Values Added Options
		B = ±50 PPM C = ±30 PPM D = ±25 PPM E = ±20 PPM F = ±15 PPM H = ±10 PPM	B = ±50 PPM C = ±30 PPM D = ±25 PPM E = ±20 PPM F = ±15 PPM H = ±10 PPM L = ±5 PPM	V = 7pF E = 10pF G = 12pF J = 15pF K = 16pF L = 18pF M = 20pF N = 22pF	C = 0 to +70°C D = -10 to +60°C E = -10 to +70°C F = -20 to +70°C K = -30 to +85°C M = -40 to +85°C P = -40 to +105°C I = -40 to +125°C T = -55 to +125°C		Blank = Bulk T1 = 1,000 pcs T2 = 2,000 pcs

1 Not all frequency, tolerance, stability, load, and operating temperature combinations may be available.

2 Listed load capacitances represent the most commonly used. Other load capacitances are available. Contact us for assistance

Reliability Test Conditions
Please contact Abracon Quality Assurance department

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ABRACON:

[FC6BSCCNM14.7456-T1](#) [FC6BSCCLM25.0-T2](#) [FC6BSCCGM24.0-T1](#) [FC6BSCCLM25.0-T1](#) [FC6BSCCGM24.0-T2](#)
[FC6BSCBLM24.0-T2](#) [FC6BSCBLM24.0-T1](#) [FC6BSCCNM14.7456-T2](#) [FC6BSEBVI8.0-T1](#) [FC6BSHHEF60.751-1-T1](#)
[FC6BSHDGM18.08956-T2](#) [FC6BSCCLC25.0-T1](#) [FC6BSCBMF16.0-T1](#) [FC6BSCBMF16.0-T2](#) [FC6BSCCKF12.0-T1](#)
[FC6BSCCKF12.0-T2](#) [FC6BSCCLC25.0-T2](#) [FC6BSCCMF25.0-T1](#) [FC6BSCCMF25.0-T2](#)