


Features

- AEC Q200 Qualified
- IATF-16949 QMS
- Tolerances down to ± 10 PPM
- Stabilities down to ± 20 PPM

STANDARD SPECIFICATIONS	
PARAMETERS	MAX (Unless otherwise noted)
Frequency Range	6.000 ~ 133.000 MHz
Frequency Tolerance @ 25°C	(See options below)
Frequency Stability, ref 25°C	(See options below)
Temperature Range	
Operating (T_{OPR})	(See options below)
Storage (T_{STG})	-55°C ~ +150°C
Shunt Capacitance (C_0)	5 pF
Load Capacitance (C_L)	(See options below)
Drive Level	100 μ W
Aging per year (@ 25°C)	± 5 PPM
Maximum Soldering Temp / Time	260°C / 10 Seconds x 2
Moisture Sensitivity Level (MSL) per J-STD-033	N/A
Termination Finish	Au (0.3~0.75 μ m) over Ni (1.27~8.89 μ m)
Seal Method	Seam
Lead (Pb) Free	Yes
RoHS Compliant	Yes, no exemptions
REACH Compliant (latest version)	Yes

Frequency Range (MHz)	Operating Mode	Max ESR Ω
6.000 ~ 7.999999	Fundamental	70
8.000 ~ 9.999999	Fundamental	40
10.000 ~ 14.999999	Fundamental	35
15.000 ~ 39.999999	Fundamental	30
40.000 ~ 50.000	Fundamental	20
50.001 ~ 79.999999	3 RD OT	70
80.000 ~ 133.000	3 RD OT	60

DIMENSIONS / MECHANICAL SPECIFICATIONS



Note: Dimensional drawing is for reference to critical specifications defined by size measurements.

AVAILABLE OPERATING TEMPERATURES AND STABILITIES

Operating Temperature	± 20 PPM	± 25 PPM	± 30 PPM	± 50 PPM	± 100 PPM
-40°C ~ +85°C	O	O	O	O	O
-40°C ~ +105°C	X	X	O	O	O
-40°C ~ +125°C	X	X	X	O	O
-55°C ~ +125°C	X	X	X	O	O

Key: O = Available, X = Not Available


FC7BA

(Former FXA7050B)

7mm x 5mm
Auto Grade Crystal



TAPE SPECIFICATIONS (mm)							REEL SPECIFICATIONS (mm)						
A	B	C	D	E	F	REEL QTY	G	H	I	J	K	L	M
ø1.55	4.0	8.0	7.5	16.0	2.0	-T2 = 2,000 -T1 = 1,000	2.5	ø13	ø21	ø62	ø180	17	2.0



Available Options & Part Identification for Auto Grade Crystal C7BA¹

Sample PN: **FC7BABCVI40.0-T1**

F	C7BA	B	C	V	I	40.0	-T1
Fox	Model Number	Tolerance B = ±50 PPM C = ±30 PPM D = ±25 PPM E = ±20 PPM F = ±15 PPM H = ±10 PPM	Stability A = ±100 PPM B = ±50 PPM C = ±30 PPM D = ±25 PPM E = ±20 PPM	Load Capacitance² V = 7pF D = 8pF E = 10pF G = 12pF J = 15pF K = 16pF L = 18pF M = 20pF	Operating Temperature M = -40 to +85°C P = -40 to +105°C I = -40 to +125°C T = -55 to +125°C	Frequency (MHz)	Values Added Options Blank = Bulk T1 = 1,000 pcs T2 = 2,000 pcs

¹ Not all frequency, tolerance, stability, load, and operating temperature combinations may be available.

² Listed load capacitances represent the most commonly used. Other load capacitances are available. Contact us for assistance

Reliability Test Conditions

Please contact Abracon Quality Assurance department

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ABRACON:

[FC7BACAGI25.0](#) [FC7BACBMI25.0](#) [FC7BACALI25.0](#) [FC7BACBMI8.0-T1](#) [FC7BACBMM8.0-T1](#) [FC7BACBMM8.0-T2](#)
[FC7BABAMI8.0-T2](#) [FC7BABAMI8.0-T1](#) [FC7BACBMI8.0-T2](#) [FC7BACCMM25.0-T2](#) [FC7BABBNP16.0-T1](#)
[FC7BACALI8A0-T2](#) [FC7BABAEI48.0-T2](#) [FC7BABBN16.0-T1](#) [FC7BACAGI25.0-T1](#) [FC7BACALI25.0-T1](#)
[FC7BACBMI25.0-T1](#) [FC7BACCGM6.0-T1](#) [FC7BACCGM6.0-T2](#) [FC7BABAEM7.3728-T2](#) [FC7BABBEM7.3728-T2](#)