

Features

- Tolerances down to ± 10 PPM
- Stabilities down to ± 10 PPM
- Temperature Ranges as wide as -40°C to $+85^{\circ}\text{C}$


STANDARD SPECIFICATIONS	
PARAMETERS	MAX (Unless otherwise noted)
Frequency Range	32.000 ~ 80.000 MHz
Frequency Tolerance @ 25°C	(See options below)
Frequency Stability, ref 25°C	(See options below)
Temperature Range	
Operating (T_{OPR})	(See options below)
Storage (T_{STG})	$-55^{\circ}\text{C} \sim +125^{\circ}\text{C}$
Shunt Capacitance (C_0)	2 pF
Load Capacitance (C_L)	(See options below)
Drive Level	100 μW (10 μW Typical)
Aging per year (@ 25°C)	± 3 PPM
Maximum Soldering Temp / Time	260°C / 10 Seconds x 2
Moisture Sensitivity Level (MSL) per J-STD-033	N/A
Termination Finish	Au (0.3~1 μm) over Ni (1.27~8.89 μm)
Lead (Pb) Free	Yes
RoHS Compliant	Yes, no exemptions
REACH Compliant (latest version)	Yes

Frequency Range (MHz)	Operating Mode	Max ESR Ω
32.000 ~ 32.999999	Fundamental	100
33.000 ~ 36.999999	Fundamental	80
37.000 ~ 80.000	Fundamental	60

AVAILABLE OPERATING TEMPERATURES AND STABILITIES				
Operating Temperature	± 10 PPM	± 15 PPM	± 20 PPM	± 25 PPM
$-20 \sim +70^{\circ}\text{C}$	O	O	O	O
$-30 \sim +85^{\circ}\text{C}$	X	O	O	O
$-40 \sim +85^{\circ}\text{C}$	X	O	O	O


Key: O = Available, X = Not Available

DIMENSIONS / MECHANICAL SPECIFICATIONS



Note: Dimensional drawing is for reference to critical specifications defined by size measurements. Certain non-critical visual attributes, such as side castellations, etc. may vary.

TAPE SPECIFICATIONS (mm)							REEL SPECIFICATIONS (mm)						
A	B	C	D	E	F	REEL QTY	G	H	I	J	K	L	M
ø1.5	4.0	4.0	3.5	8.0	0.45	-T5 = 5,000	2.0	ø13	ø21	ø60	ø180	9.0	1.5



Available Options & Part Identification for CABS¹

Sample PN: **FCABSFFDM40.0-T5**

F	CABS	F	F	D	M	40.0	-T5
Fox	Model Number	Tolerance D = ±25 PPM E = ±20 PPM F = ±15 PPM H = ±10 PPM	Stability D = ±25 PPM E = ±20 PPM F = ±15 PPM H = ±10 PPM	Load Capacitance² B = 6 pF V = 7 pF D = 8 pF E = 10 pF G = 12 pF	Operating Temperature F = -20 ~ +70°C K = -30 ~ +85°C M = -40 ~ +85°C	Frequency (MHz)	Values Added Options Blank = Bulk T5 = 5,000 pcs

1 Not all frequency, tolerance, stability, load, and operating temperature combinations may be available.

2 Listed load capacitances represent the most commonly used. Other load capacitances are available. Contact us for assistance

Reliability Test Conditions

Please contact Abracon Quality Assurance department

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ABRACON:](#)

[FCABSFEVK38.4](#) [FCABSFEVK37.4](#) [FCABSFEVK52.0](#)