

# Chip Multilayer Hybrid Couplers

## Directional Coupler



Part Number	Frequency Range (MHz)	Coupling (dB)	Insertion Loss (dB)	Isolation (min.) (dB)	VSWR (max.)	Characteristic Impedance (Nom.) (ohm)	Power Capacity (W)	Application
LDC15450M25Q-360	450 ±50MHz	25.1 ±1.8dB	0.15 max. (at 25°C)	38.0	1.5	-	3 max. (50ohm Load)	CDMA450
LDC15707M21Q-360	707 ±9MHz	21.1 ±1.0dB	0.23 max. (at 25°C)	35.0	1.4	-	3 max. (50ohm Load)	UMTS(Band12)
LDC15836M30Q-392	836.5 ±12.5MHz	30.6 ±1.0dB	0.20 max. (at 25°C)	38.0	1.4	-	3 max. (50ohm Load)	UMTS(Band5)
LDC15874M27Q-359	874 ±51MHz	27.2 ±1.0dB	0.20 max. (at 25°C)	42.0	1.4	50	3 max. (50ohm Load)	UMTS(Band5/8)
LDC15897M26SB008	897.5 ±17.5MHz	26.4 ±1.0dB	0.15 max. (at 25°C)	-	1.4	50	3 max. (50ohm Load)	UMTS(Band8)
LDC15906M19SB001	906.0 ±19.0MHz	19.3 ±1.0dB	0.22 max. (at 25°C)	-	1.4	50	3 max. (50ohm Load)	CDMA
LDC151G4418Q-352	1441 ±12MHz	18.9 ±1.0dB	0.23 max. (at 25°C)	32.0	1.4	50	3 max. (50ohm Load)	WCDMA
LDC151G7313Q-360	1732.5 ±22.5MHz	13.6 ±1.0dB	0.42 max. (at 25°C)	24.0	1.4	50	3 max. (50ohm Load)	UMTS(Band4)
LDC151G7424Q-392	1747 ±37.5MHz	24.1 ±1.0dB	0.20 max. (at 25°C)	30.0	1.4	50	3 max. (50ohm Load)	UMTS(Band4)
LDC151G7421Q-359	1747.5 ±37.5MHz	21.2 ±1.0dB	0.22 max. (at 25°C)	35.0	1.4	50	3 max. (50ohm Load)	UMTS(Band3)
LDC151G8117Q-352	1810 ±100MHz	17.0 ±1.2dB	0.25 max. (at 25°C)	32.0	1.4	50	3 max. (50ohm Load)	GSM
LDC151G8620Q-359	1865 ±115MHz	20.5 ±1.0dB	0.22 max. (at 25°C)	34.0	1.4	50	3 max. (50ohm Load)	UMTS(Band2)
LDC151G8824Q-393	1880 ±30MHz	24.7 ±1.0dB	0.20 max. (at 25°C)	32.0	1.4	50	3 max. (50ohm Load)	UMTS(Band2)

Continued on the following page.

 Continued from the preceding page.

Part Number	Frequency Range (MHz)	Coupling (dB)	Insertion Loss (dB)	Isolation (min.) (dB)	VSWR (max.)	Characteristic Impedance (Nom.) (ohm)	Power Capacity (W)	Application
<b>LDC151G9120Q-359</b>	1915 ±65MHz	20.4 ±1.0dB	0.22 max. (at 25°C)	34.0	1.4	50	3 max. (50ohm Load)	UMTS(Band1)
<b>LDC151G9523Q-392</b>	1950 ±30MHz	23.2 ±1.0dB	0.20 max. (at 25°C)	30.0	1.4	50	3 max. (50ohm Load)	UMTS(Band1)
<b>LDC152G1419Q-359</b>	2140 ±30MHz	19.4 ±1.0dB	0.26 max. (at 25°C)	33.0	1.5	50	3 max. (50ohm Load)	UMTS(Band1)
<b>LDC152G3518Q-359</b>	2350 ±50MHz	18.7 ±1.0dB	0.28 max. (at 25°C)	31.0	1.4	50	3 max. (50ohm Load)	WLAN
<b>LDC152G4518Q-359</b>	2450 ±50MHz	18.4 ±1.0dB	0.29 max. (at 25°C)	31.0	1.4	50	3 max. (50ohm Load)	WLAN
<b>LDC152G5318Q-359</b>	2535 ±35MHz	18.1 ±1.0dB	0.30 max. (at 25°C)	31.0	1.4	50	3 max. (50ohm Load)	UMTS(Band7)
<b>LDC18836M32Q-370</b>	836.5 ±12.5MHz	32.2 ±1.2dB	0.17 max. (at 25°C)	44.0	1.5	50	3 max. (50ohm Load)	UMTS(Band5)
<b>LDC18897M20Q-361</b>	897.5 ±17.5MHz	20.5 ±1.0dB	0.22 max. (at 25°C)	33.0	1.5	50	3 max. (50ohm Load)	UMTS(Band8)
<b>LDC181G7426Q-370</b>	1747.5 ±37.5MHz	26.0 ±1.2dB	0.17 max. (at 25°C)	49.0	1.5	50	3 max. (50ohm Load)	UMTS(Band4)
<b>LDC181G8825Q-370</b>	1880.0 ±30.0MHz	25.3 ±1.2dB	0.22 max. (at 25°C)	45.5	1.5	50	3 max. (50ohm Load)	UMTS(Band2)
<b>LDC181G9525Q-370</b>	1950.0 ±30.0MHz	25.0 ±1.2dB	0.22 max. (at 25°C)	44.0	1.5	50	3 max. (50ohm Load)	UMTS(Band1)
<b>LDC21836M20B-027</b>	836.5 ±12.5MHz	20.6 ±1.0dB	0.15 max. (at 25°C)	28.0	1.4	50	3 max. (50ohm Load)	CDMA
<b>LDC211G8820B-042</b>	1880.0 ±30.0MHz	20.0 ±1.0dB	0.23 max. (at 25°C)	26.0	1.4	50	3 max. (50ohm Load)	CDMA
<b>LDC211G9517B-031</b>	1950.0 ±30.0MHz	17.3 ±1.0dB	0.27 max. (at 25°C)	21.0	1.4	50	3 max. (50ohm Load)	UMTS(Band1)

Operating Temperature Range: -40°C to +85°C

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Murata:

[LDC211G9220H-062](#) [LDC21847M10B-028](#) [LDC211G7410H-057](#) [LDC211G7420H-055](#) [LDC211G8114H-160](#)  
[LDC18897M18B-325](#) [LDC21897M18B-032](#) [LDC211G8820H-059](#) [LDC21897M14E-085](#) [LDC211G8814H-054](#)  
[LDC31847M10B-749](#) [LDC18847M14B-322](#) [LDC211G9619B-042](#) [LDC31820M10B-002](#) [LDC31820M20B-001](#)  
[LDC312G1003B-773](#) [LDC312G1403B-769](#) [LDC18836M20B-320](#) [LDC181G6320B-327](#) [LDC31866M14B-003](#)  
[LDC31933M19B-001](#) [LDC31933M09B-002](#) [LDC312G4518B-752](#) [LDC31937M09B-002](#) [LDC31937M19B-001](#)  
[LDC31931M09B-002](#) [LDC31931M19B-001](#) [LDC431G6003B-200](#) [LDC18836M15B-323](#) [LDC181G8810B-321](#)  
[LDC31836M14B-704](#) [LDC21897M10B-028](#) [LDC21897M20B-027](#) [LDC31897M20B-001](#) [LDC31897M10B-002](#)  
[LDC311G9214B-716](#) [LDC181G9513B-320](#) [LDC181G9013B-320](#) [LDC181G7410B-323](#) [LDC181G7420B-327](#)  
[LDC181G9520B-328](#) [LDC21836M20B-027](#) [LDC21836M10B-028](#) [LDC31836M20B-001](#) [LDC31836M10B-002](#)  
[LDC18897M20B-320](#) [LDC182G1416B-778](#) [LDC31915M09B-730](#) [LDC211G8815B-035](#) [LDC181G6315B-320](#)  
[LDC211G9518H-073](#) [LDC21897M20H-056](#) [LDC311G7418B-005](#) [LDC211G4417L-070](#) [LDC211G4417L-053](#)  
[LDC211G7418B-031](#) [LDC18847M20B-320](#) [LDC18906M17B-325](#) [LDC212G1419B-042](#) [LDC31836M15B-003](#)  
[LDC181G9519B-327](#) [LDC181G9509B-321](#) [LDC181G9019B-327](#) [LDC21906M20B-027](#) [LDC31902M10B-002](#)  
[LDC31902M20B-001](#) [LDC21902M10B-028](#) [LDC182G4517B-327](#) [LDC211G4419B-031](#) [LDC311G4419B-005](#)  
[LDC311G4819B-005](#) [LDC211G8809B-037](#) [LDC312G2503B-723](#) [LDC182G4512B-320](#) [LDC211G7409B-029](#)  
[LDC312G5003B-743](#) [LDC212G0610B-038](#) [LDC21924M17E-166](#) [LDC31888M14B-003](#) [LDC31915M20B-732](#)  
[LDC211G0210D-171](#) [LDC212G4520H-151](#) [LDC31950M19B-001](#) [LDC31950M09B-002](#) [LDC31911M14B-003](#)  
[LDC21897M17H-098](#) [LDC31920M14B-003](#) [LDC21814M20B-027](#) [LDC21897M19D-079](#) [LDC21897M19D-078](#)  
[LDC21897M19D-081](#) [LDC21897M14H-058](#) [LDC312G1519B-720](#) [LDC18906M19B-320](#) [LDC21815M20H-069](#)  
[LDC31914M14B-003](#) [LDC21902M14B-029](#) [LDC31902M14B-003](#) [LDC211G9517B-031](#) [LDC21869M20B-027](#)