


Features

- Digital Temperature Compensation

STANDARD SPECIFICATIONS	
PARAMETERS	MAX (Unless otherwise noted)
Frequency Range (MHz)	8.000 ~ 40.000
Temperature Range	
Operating (T_{OPR})	See table below
Storage (T_{STG})	-40°C ~ +85°C
Supply Voltage (V_{DD})	3.3 VDC $\pm$ 5%
Input Current (I_{DD})	6.0 mA
Initial Frequency Tolerance @ 25°C (after reflow) ($T5CV: V_c = 1.65V$) ¹	$\pm$ 2.0 PPM
Frequency Stability	
Over Temperature Range	See table below
Over Supply Voltage Change (3.3V $\pm$ 5%)	$\pm$ 0.3 PPM
Over Load Change (15pF $\pm$ 5%)	$\pm$ 0.3 PPM
Rise Time (0.5V ~ 80% V_{DD})	10 nS
Fall Time (80% V_{DD} ~ 0.5V)	10 nS
Symmetry (50% V_{DD})	40% ~ 60%
Output Voltage (V_{OL})	0.5V
(V_{OH})	80% V_{DD} Min
Output Load	15pF
Aging per year	$\pm$ 1.0 PPM
Startup Time (T_s)	2.0 mS Max
Phase Noise @ 1kHz offset	-130 dBc/Hz Typical
Reflow Soldering Temp	260°C / 10 Seconds x 2
Moisture Sensitivity Level (MSL)	1
Termination Finish	Au over Ni
Lead-Free	Yes
RoHS/REACH Compliant	Yes



Available Options by Stability & Operating Temp				
Operating Temperature	$\pm$ 1 PPM	$\pm$ 1.5 PPM	$\pm$ 2 PPM	$\pm$ 2.5 PPM
-30 ~ +85°C	O	O	O	O
-40 ~ +85°C	X	O	O	O

Key: O = Available, X =Not Available

¹ All specifications subject to change without notice.

FT5HN


(Former FOX924B)

5.0mm x 3.2mm

HCMOS TCXO



TAPE SPECIFICATIONS (mm)							REEL SPECIFICATIONS (mm)						
A	B	C	D	E	F	REEL QTY	G	H	I	J	K	L	M
ø1.5	4.0	8.0	5.5	12.0	1.7	-T1 = 1,000	2.0	ø13	ø21	ø80	ø180	13.5	2.0



Available Options & Part Identification for TCXO Model T5HN¹

Sample PN: **FT5HNBPK25.0-T1**

F	T5HN	B	P	K	25.0	-T1
Fox	Model Number T5HN = TCXO	Voltage B = +3.3V±5%	Stability T = ±1.0 PPM S = ±1.5 PPM R = ±2.0 PPM P = ±2.5 PPM	Operating Temperature K = -30 to +85°C M = -40 to +85°C	Frequency (MHz)	Values Added Options Blank = Bulk T1 = 1,000 pcs

¹ Not all frequencies in the frequency range, or every combination of stability, temp range, and voltage available.
See stabilities/operating temp table.

Reliability Test Conditions

Please contact Abracon Quality Assurance department

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ABRACON:](#)

[FOX924B-10.000](#) [FT5HNBPK19.44-T1](#) [FT5HNBPK27.0-BULK](#) [FT5HNBPM25.0-T1](#) [FT5HNBPK19.44-BULK](#)
[FT5HNBPK10.0-BULK](#) [FT5HNBPK12.0-BULK](#) [FT5HNBPK19.6608-BULK](#) [FT5HNBPK20.0-BULK](#)
[FT5HNBPK14.75526-BULK](#) [FT5HNBPK14.75526-T1](#) [FT5HNBPK16.0-BULK](#) [FT5HNBPK20.48-BULK](#)
[FT5HNBPK20.48-T1](#) [FT5HNBPK24.0-T1](#) [FT5HNBPK25.0-T1](#) [FT5HNBPK14.7456-BULK](#) [FT5HNBPK24.0-BULK](#)
[FT5HNBPK26.0-T1](#) [FT5HNBPK25.0-BULK](#) [FT5HNBPK12.288-BULK](#) [FT5HNBPK25.0-BULK](#) [FT5HNBPK26.0-BULK](#)
[FT5HNBPK12.288-T1](#) [FT5HNBPK25.0-T1](#) [FT5HNBPK10.0-T1](#) [FT5HNBPK16.0-T1](#) [FT5HNBPK27.0-T1](#)
[FT5HNBPK20.0-T1](#) [FT5HNBPK14.7456-T1](#) [FT5HNBPK12.0-T1](#) [FT5HNBTK25.0-T1](#) [FT5HNBTK25.0-BULK](#)
[FT5HNBTK12.288-T1](#) [FT5HNBPK19.6608-T1](#) [FT5HNBPK13.2-T1](#)