


Features

- Analog Temperature Compensation

STANDARD SPECIFICATIONS	
PARAMETERS	MAX (Unless otherwise noted)
Frequency Range (MHz)	8 ~ 52.000
Temperature Range	
Operating (T_{OPR})	(See table below)
Storage (T_{STG})	-40°C ~ +90°C
Supply Voltage (V_{DD}) ($\pm 5\%$)	1.8V; 2.5V; 2.7V; 2.8V; 3.0V; 3.3V
Input Current (I_{DD})	2.0 mA
Initial Frequency Tolerance @ 25°C (after reflow) ($T3AV: V_c = V_{DD}/2$) ¹	± 2.0 PPM
Frequency Stability	
Over Temperature Range	(See table below)
Over Supply Voltage Change ($V_{DD} \pm 5\%$)	± 0.2 PPM
Over Load Change [10k Ω /10pF] $\pm 10\%$	± 0.2 PPM
Output Voltage Level (V_{OL})	0.8V _{p-p} min
Output Voltage (VOL)	0.4V
Output Load	[10k Ω /10pF] $\pm 10\%$
Pullability	
($T3AV: V_c = V_{DD} \pm 1.0V$; $T3AVK 0.9V \pm 0.9V$) ¹	$\pm 3 \sim \pm 15$ PPM
Aging per year (@ 25°C)	± 1.0 PPM
Startup Time (T_s)	3.0 mS
Phase Noise	
@ 1kHz offset	-130 dBc/Hz Typical
Reflow Soldering Temp	260°C / 10 Seconds x 2
Moisture Sensitivity Level (MSL)	1
Termination Finish	Au over Ni
Lead-Free	Yes
RoHS/REACH Compliant	Yes



Available Options by Stability & Operating Temp					
Operating Temperature	± 1 PPM	± 1.5 PPM	± 2 PPM	± 2.5 PPM	± 15 PPM
-30 ~ +85°C	O	O	O	O	NA
-40 ~ +85°C	Δ	O	O	O	NA
-40 ~ +105°C	X	X	X	X	O

Key: O=Available, X=Not Available, NA=Not Applicable, Δ = Consult Fox Engineering

¹For proper operation, a control voltage (V_c) must be applied to pin 1 of VCTCXO's. All specifications subject to change without notice.

FT3AV


(Former FOX923_A)

3.2mm x 2.5mm

CSW VCTCXO



TAPE SPECIFICATIONS (mm)							REEL SPECIFICATIONS (mm)						
A	B	C	D	E	F	REEL QTY	G	H	I	J	K	L	M
ø1.5	4.0	4.0	3.5	8.0	1.4	-T3 = 3,000 default -T2 = 2,000 -T1 = 1,000	2.0	ø13	ø21	ø60	ø180	9.0	1.5



Available Options & Part Identification for VCTCXO Model T3AV¹

Sample PN: **FT3AVBPK25.0-T3**

F	T3AV	B	P	K	25.0	-T3
Fox	Model Number T3AV = VCTCXO	Tolerance B = +3.3V±5% D = +3.0V±5% Q = +2.8V±5% S = +2.7V±5% H = +2.5V±5% K = +1.8V±5%	Stability T = ±1.0 PPM S = ±1.5 PPM R = ±2.0 PPM P = ±2.5 PPM F = ±15 PPM	Operating Temperature K = -30 to +85°C M = -40 to +85°C P = -40 to +105°C	Frequency (MHz)	Values Added Options Blank = Bulk T1 = 1,000 pcs T2 = 2,000 pcs T3 = 3,000 pcs

¹ Not all frequencies in the frequency range, or every combination of stability, temp range, and voltage available.
See stabilities/operating temp table.

Reliability Test Conditions

Please contact Abracon Quality Assurance department

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ABRACON:](#)

[FT3ANKUK38.4-T3](#)