



SPECIFICATIONS:					
NUMBER OF PHASES: 2			ROTOR INERTIA: 14 g-cm ² (0.08 oz-in ²) NOM		
STEPS PER REVOLUTION: 400			DETENT TORQUE: 10 mNm (1.42 oz-in) MIN		
STEP ANGLE: 0.9°			BEARINGS: 625ZZ		
STEP TO STEP ACCURACY: ±0.045°			INSULATION CLASS: B		
POSITIONAL ACCURACY: ±5%			HYSTERESIS: N/A%		
SHAFT RUNOUT: 0.03 mm T.I.R. MAX			TEMP. RISE: 80 °C MAX.		
RADIAL PLAY: 0.02 mm MAX (.5KG RADIAL LOAD)			OPERATING TEMP. RANGE: -20 TO +50 °C		
END PLAY: 0.08 mm MAX (.5KG AXIAL LOAD)			STORAGE TEMP. RANGE: -30 TO +70 °C		
MAXIMUM RADIAL LOAD: 21N (4.72lb)			RELATIVE HUMIDITY RANGE: 15 TO 85 %		
MAXIMUM AXIAL LOAD: 10N (2.25lb)			WEIGHT: 0.16 kg (0.35 lb)		
[7]		[8]		[1]	
[1]		[8]		[1]	
SPECIFICATION		RESISTANCE PER PHASE (ohm ±10%)		INDUCTANCE PER PHASE (mH ±20%)	
CONNECTION		RATED CURRENT (amp)		HOLDING TORQUE (Nm MIN)	
BI-POLAR SERIES		6.6		0.6	
		8		0.07	
				9.91	


NOTES, UNLESS OTHERWISE SPECIFIED:



- [1] MEASUREMENTS MADE AT RATED CURRENT IN EACH PHASE.
- [2] BETWEEN ANY TWO ADJACENT FULL STEP POSITIONS.
- [3] MAXIMUM ERROR IN 360°.
4. HIPOT 500 VAC, 60 Hz FOR ONE MINUTE.
5. CONNECTOR: JST S11B-ZR(LF)(SN)
6. INSULATION RESISTANCE: 100 MEGOHMS MIN AT 500 VDC.
- [7] AS MEASURED ACROSS EACH PHASE.
- [8] AS MEASURED ACROSS EACH PHASE USING AN A.C. INDUCTANCE BRIDGE AT 1 KHz.
- [9] AS MEASURED BY THE CHANGE IN RESISTANCE METHOD, WITH RATED CURRENT APPLIED TO 2 PHASES; WITH MOTOR AT REST.
- [10] ADD "D" TO END OF PART NUMBER IF DOUBLE SHAFT IS REQUIRED. ENCODER HOLES INCLUDED WITH REAR SHAFT VERSION ONLY.
11. ROTOR & STATOR LAMINATED CONSTRUCTION.
12. THIS MOTOR TO BE MANUFACTURED IN COMPLIANCE WITH EU DIRECTIVE "ROHS 2002/95/EC".
- [13] MOTOR LABEL TO INCLUDE "ROHS" COMPLIANT, AMP P/N, 'MADE IN (COUNTRY OF ORIGIN)', AND DATE CODE.



REVISIONS				
ECO NO.	REV	DESCRIPTION	DATE	APPROVED
6947	A	PRELIMINARY RELEASE	4/11/14	D.MACLEOD
7048	B	ERROR CORRECTION	8/11/14	D.MACLEOD
—	—	—	—	—
—	—	—	—	—
—	—	—	—	—
—	—	—	—	—
—	—	—	—	—
—	—	—	—	—
—	—	—	—	—
—	—	—	—	—
—	—	—	—	—
—	—	—	—	—

LABEL DETAIL



CONTRACT NO. —		 APPLIED MOTION PRODUCTS, INC.					
APPROVALS		DATE		STEP MOTOR OUTLINE			
DRAWN K.KESLER		8/11/14					
CHECKED —		—					
APPROVED —		—					
APPROVED —		—		B	COMPUTER DATA BASE DRAWING	DWG NO. 5014-897	REV B
APPROVED —		—		SCALE: NONE		SHEET 1 OF 2	



TOLERANCES		THIRD ANGLE PROJECTION		 APPLIED MOTION PRODUCTS, INC.		
*ALL DIMENSIONS IN MM DECIMALS: MM X.XX = ±0.13 X.X = ±0.25 ANGLES: MACH. = ±0.5° CHAM. = ±5°						
		APPROVALS	DATE	STEP MOTOR OUTLINE		
		DRAWN K.KESLER	8/11/14			
		CHECKED —	—	B	DWG NO. 5014-897	REV B
		APPROVED —	—			
COMPUTER DATA BASE DRAWING				SCALE: NONE		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Applied Motion:](#)

[5014-897D](#) [5014-897](#)