



NC3MX-HD-B

PHASE OUT

direct replacement / successor: NC3MXX-HD-B

alternative product: NC3MX1-TOP

3 pole male cable connector, "heavy duty", black metal boot and stainless steel shell, gold contacts

The X-HD Series is a "heavy duty" XLR cable connector for outdoor use. All metal design, dust and water protected according to IP 65. Gold contacts are standard.

Features & Benefits

- | | |
|---|---|
| <ul style="list-style-type: none">• "Heavy duty" cable connector for outdoor use | <ul style="list-style-type: none">• All metal design |
| <ul style="list-style-type: none">• Male connector in stainless steel | <ul style="list-style-type: none">• NC*MX-HD mates with NC*FX-HD cable connector |
| <ul style="list-style-type: none">• Dust and water protected according IP 65 in mated condition | <ul style="list-style-type: none">• Gold contacts |
| <ul style="list-style-type: none">• Chuck type strain relief system for secure clamping of cables | <ul style="list-style-type: none">• Boot with rubber gland gives high protection against bending stresses |

Technical Information

Product	
Title	NC3MX-HD-B
Connection Type	XLR
Gender	male

Electrical	
Capacitance between contacts	$\leq 4 \text{ pF}$
Contact resistance	$\leq 3 \text{ m}\Omega$
Dielectric strength	1,5 kVdc
Insulation resistance	$> 10 \text{ G}\Omega$ (initial)
Rated current per contact	16 A
Rated voltage	$< 50 \text{ V}$

Mechanical	
Cable O.D.	3.5 - 8.0 mm
Insertion force	$\leq 20 \text{ N}$
Withdrawal force	$\leq 20 \text{ N}$
Lifetime	> 1000 mating cycles
Wiresize	max. 2.5 mm^2
Wiresize	max. 14 AWG
Wiring	Solder contacts
Locking device	Latch lock

Material	
Boot	Polyurethan
Bushing	Stainless steel
Contact plating	0.2 µm Au hard alloy over 2 µm Ni
Contacts	Brass (CuZn39Pb3)
Insert	Polyamide (PA66)
Locking element	Stainless steel
Shell	Stainless steel
Shell plating	Black chromium
Strain relief	Polyacetal (POM)
Sealing jacket	EPDM

Environmental	
Approvals	UL
Flammability	UL 94 V-0
Standard compliance	IEC 61076-2-103
Protection class	IP 65
Solderability	Complies with IEC 68-2-20
Temperature range	-30 °C to +80 °C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Neutrik:](#)

[NC3MX-HD-B](#)