

## Important notice

Dear Customer,

On 7 February 2017 the former NXP Standard Product business became a new company with the tradename **Nexperia**. Nexperia is an industry leading supplier of Discrete, Logic and PowerMOS semiconductors with its focus on the automotive, industrial, computing, consumer and wearable application markets

In data sheets and application notes which still contain NXP or Philips Semiconductors references, use the references to Nexperia, as shown below.

Instead of <http://www.nxp.com>, <http://www.philips.com/> or <http://www.semiconductors.philips.com/>, use **<http://www.nexperia.com>**

Instead of [sales.addresses@www.nxp.com](mailto:sales.addresses@www.nxp.com) or [sales.addresses@www.semiconductors.philips.com](mailto:sales.addresses@www.semiconductors.philips.com), use **[salesaddresses@nexperia.com](mailto:salesaddresses@nexperia.com)** (email)

Replace the copyright notice at the bottom of each page or elsewhere in the document, depending on the version, as shown below:

- © NXP N.V. (year). All rights reserved or © Koninklijke Philips Electronics N.V. (year). All rights reserved

Should be replaced with:


- © **Nexperia B.V. (year). All rights reserved.**

If you have any questions related to the data sheet, please contact our nearest sales office via e-mail or telephone (details via **[salesaddresses@nexperia.com](mailto:salesaddresses@nexperia.com)**). Thank you for your cooperation and understanding,

Kind regards,

Team Nexperia

# DATA SHEET



## **PMEG2010AEB**

20 V, 1 A ultra low  $V_F$  MEGA  
Schottky barrier rectifier in  
SOD523 package

## 20 V, 1 A ultra low $V_F$ MEGA Schottky barrier rectifier in SOD523 package

### PMEG2010AEB

#### FEATURES

- Forward current: 1.0 A
- Reverse voltage: 20 V
- Ultra low forward voltage
- Ultra small SMD package.

#### APPLICATIONS

- Low voltage rectification
- High efficiency DC/DC conversion
- Voltage clamping
- Inverse-polarity protection
- Low power consumption applications.

#### DESCRIPTION


Planar Maximum Efficiency General Application (MEGA) Schottky barrier rectifier with an integrated guard ring for stress protection, encapsulated in a SOD523 (SC-79) ultra small plastic SMD package.

#### QUICK REFERENCE DATA

SYMBOL	PARAMETER	MAX.	UNIT
$I_F$	forward current	1	A
$V_R$	reverse voltage	20	V

#### PINNING

PIN	DESCRIPTION
1	cathode
2	anode



**Marking code:** L6.

The marking bar indicates the cathode.

Fig.1 Simplified outline (SOD523; SC-79) and symbol.

#### ORDERING INFORMATION

TYPE NUMBER	PACKAGE		
	NAME	DESCRIPTION	VERSION
PMEG2010AEB	–	plastic surface mounted package; 2 leads	SOD523

#### RELATED PRODUCTS

TYPE	DESCRIPTION	FEATURE
PMEG2005EB	0.5 A; 20 V very low $V_F$ MEGA Schottky rectifier	Lower $I_R$ in same package
PMEG2010EA	1 A; 20 V very low $V_F$ MEGA Schottky rectifier	Lower forward current, lower $I_R$ SOD323 (SC76)

## 20 V, 1 A ultra low $V_F$ MEGA Schottky barrier rectifier in SOD523 package

PMEG2010AEB

### LIMITING VALUES

In accordance with the Absolute Maximum Rating System (IEC 60134).

SYMBOL	PARAMETER	CONDITIONS	MIN.	MAX.	UNIT
$V_R$	continuous reverse voltage		–	20	V
$I_F$	continuous forward current	$T_s \leq 55\text{ °C}$	–	1.0	A
$I_{FRM}$	repetitive peak forward current	$t_p \leq 1\text{ ms}$ ; $\delta \leq 0.5$	–	3.5	A
$I_{FSM}$	non-repetitive peak forward current	$t = 8\text{ ms}$ square wave	–	6	A
$T_{stg}$	storage temperature		–65	+150	°C
$T_j$	junction temperature	note 1	–	150	°C
$T_{amb}$	operating ambient temperature	note 1	–65	+150	°C

### Note

- For Schottky barrier rectifiers, thermal run-away has to be considered, as in some applications the reverse power losses  $P_R$  are a significant part of the total power losses. Nomograms for determination of the reverse power losses  $P_R$  and  $I_{F(AV)}$  rating will be available on request.

### THERMAL CHARACTERISTICS

SYMBOL	PARAMETER	CONDITIONS	VALUE	UNIT
$R_{th(j-a)}$	thermal resistance from junction to ambient	in free air; notes 1 and 2	400	K/W
$R_{th(j-s)}$	thermal resistance from junction to soldering point	notes 2 and 3	75	K/W

### Notes

- Refer to SOD523 (SC-79) standard mounting conditions.
- For Schottky barrier rectifiers, thermal run-away has to be considered, as in some applications the reverse power losses  $P_R$  are a significant part of the total power losses. Nomograms for determination of the reverse power losses  $P_R$  and  $I_{F(AV)}$  rating will be available on request.
- Solder point of cathode tab.

# 20 V, 1 A ultra low $V_F$ MEGA Schottky barrier rectifier in SOD523 package

PMEG2010AEB

## CHARACTERISTICS

$T_{amb} = 25\text{ }^{\circ}\text{C}$  unless otherwise specified.

SYMBOL	PARAMETER	CONDITIONS	TYP.	MAX.	UNIT
$V_F$	forward voltage	$I_F = 0.1\text{ mA}$	30	60	mV
		$I_F = 1\text{ mA}$	80	110	mV
		$I_F = 10\text{ mA}$	140	190	mV
		$I_F = 100\text{ mA}$	230	290	mV
		$I_F = 1000\text{ mA}$	510	620	mV
$I_R$	continuous reverse current	$V_R = 10\text{ V}$ ; note 1	0.17	0.6	mA
		$V_R = 20\text{ V}$ ; note 1	0.32	1.5	mA
$C_d$	diode capacitance	$V_R = 1\text{ V}$ ; $f = 1\text{ MHz}$	19	25	pF


### Note

1. Pulse test:  $t_p \leq 300\text{ }\mu\text{s}$ ;  $\delta \leq 0.02$ .

# 20 V, 1 A ultra low $V_F$ MEGA Schottky barrier rectifier in SOD523 package


PMEG2010AEB

## GRAPHICAL DATA




- (1)  $T_{amb} = 85^\circ\text{C}$ .
- (2)  $T_{amb} = 25^\circ\text{C}$ .
- (3)  $T_{amb} = -40^\circ\text{C}$ .

Fig.2 Forward current as a function of forward voltage; typical values.



- (1)  $T_{amb} = 85^\circ\text{C}$ .
- (2)  $T_{amb} = 25^\circ\text{C}$ .
- (3)  $T_{amb} = -40^\circ\text{C}$ .

Fig.3 Reverse current as a function of reverse voltage; typical values.



$f = 1\text{ MHz}$ ;  $T_{amb} = 25^\circ\text{C}$ .

Fig.4 Diode capacitance as a function of reverse voltage; typical values.


20 V, 1 A ultra low  $V_F$  MEGA Schottky  
barrier rectifier in SOD523 package

PMEG2010AEB

PACKAGE OUTLINE

Plastic surface mounted package; 2 leads

SOD523V



# 20 V, 1 A ultra low $V_F$ MEGA Schottky barrier rectifier in SOD523 package

PMEG2010AEB

## DATA SHEET STATUS

DOCUMENT STATUS <sup>(1)</sup>	PRODUCT STATUS <sup>(2)</sup>	DEFINITION
Objective data sheet	Development	This document contains data from the objective specification for product development.
Preliminary data sheet	Qualification	This document contains data from the preliminary specification.
Product data sheet	Production	This document contains the product specification.

## Notes

1. Please consult the most recently issued document before initiating or completing a design.
2. The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL <http://www.nxp.com>.

## DISCLAIMERS

**General** — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information.

**Right to make changes** — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

**Suitability for use** — NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in medical, military, aircraft, space or life support equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors accepts no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

**Applications** — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

**Limiting values** — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) may cause permanent damage to the device. Limiting values are stress ratings only and operation of the device at these or any other conditions

above those given in the Characteristics sections of this document is not implied. Exposure to limiting values for extended periods may affect device reliability.

**Terms and conditions of sale** — NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at <http://www.nxp.com/profile/terms>, including those pertaining to warranty, intellectual property rights infringement and limitation of liability, unless explicitly otherwise agreed to in writing by NXP Semiconductors. In case of any inconsistency or conflict between information in this document and such terms and conditions, the latter will prevail.

**No offer to sell or license** — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

**Export control** — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from national authorities.

**Quick reference data** — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.



# ***NXP Semiconductors***

## **Customer notification**

This data sheet was changed to reflect the new company name NXP Semiconductors. No changes were made to the content, except for the legal definitions and disclaimers.

## **Contact information**

For additional information please visit: **<http://www.nxp.com>**

For sales offices addresses send e-mail to: **[salesaddresses@nxp.com](mailto:salesaddresses@nxp.com)**

© NXP B.V. 2009

All rights are reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner.

The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent- or other industrial or intellectual property rights.

Printed in The Netherlands

R76/01/pp8

Date of release: 2003 Dec 03

Document order number: 9397 750 11911

founded by

**PHILIPS**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Nexperia:](#)

[PMEG2010AEB,115](#) [PMEG2010AEBF](#)