



Featuring flexible PVC insulation, this tin-plated single conductor copper wire is perfect for working on breadboards, test jigs, jtag, or other electronics on the fly. This wire also features the following:

- Works great for soldering on laptops, motherboards, LCDs, breadboards, PCBs, or other electronic devices
- Tin-plated copper conductor provides flexibility and corrosion resistance
- PVC insulation provides temperature resistance up to 176°F (80°C)

SPECIFICATIONS	WP30BL-1000	WP30BK-1000
COLOR	Blue	Black
WIRE GAUGE	30 AWG (0.25 mm)	30 AWG (0.25 mm)
INSULATION TYPE	PVC	PVC
INSULATION THICKNESS	0.005" (0.127 mm)	0.005" (0.127 mm)
OVERALL DIAMETER	0.0197" (0.50 mm)	0.0197" (0.50 mm)
MATERIAL	Tin Plated Copper	Tin Plated Copper
VOLTAGE	Not Rated	Not Rated
LENGTH	1000 ft (304 m)	1000 ft (304 m)
WEIGHT	0.36 lb (163 g)	0.36 lb (163 g)
UPC #	810053350447	810053350430



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Jonard Industries:](#)

[WP30BK-1000](#) [WP30BL-1000](#)