



**UMA**

5mmL, Standard, For General Purposes

Anti-Solvent  
Feature


- Standard series with 5mm height.
- Compliant to the RoHS directive (2011/65/EU, (EU)2015/863).



## Specifications


Item	Performance Characteristics								
Category Temperature Range	-40 to +85°C								
Rated Voltage Range	4 to 50V								
Rated Capacitance Range	1 to 470μF								
Rated Capacitance Tolerance	±20% at 120Hz, 20°C								
Leakage Current	After 2 minutes' application of rated voltage at 20°C, leakage current is not more than 0.01CV or 3(μA), whichever is greater.								
Tangent of loss angle (tan δ)	Measurement frequency : 120Hz at 20°C								
	Rated voltage (V)	4	6.3	10	16	25	35	50	Figures in ( ) are for UMR.
	tan δ (MAX.)	0.35	0.24 (0.30)	0.20 (0.24)	0.16 (0.20)	0.14 (0.18)	0.12 (0.16)	0.10 (0.13)	
Stability at Low Temperature	Measurement frequency : 120Hz								
	Rated voltage (V)		4	6.3	10	16	25	35	50
	Impedance ratio (MAX.)	Z-25°C / Z+20°C	7	4	3	2	2	2	2
		Z-40°C / Z+20°C	15	8	6	4	4	3	3
Endurance	The specifications listed at right shall be met when the capacitors are restored to 20°C after the rated voltage is applied for 2000 hours at 85°C.				Capacitance change		Within ±20% of the initial capacitance value (UMR & φ3 product : Within ±25%)		
					tan δ		200% or less than the initial specified value		
					Leakage current		Less than or equal to the initial specified value		
Shelf Life	After storing the capacitors under no load at 85°C for 1000 hours and then performing voltage treatment based on JIS C 5101-4 clause 4.1 at 20°C, they shall meet the specified values for the endurance characteristics listed above.								
Marking	Printed with white color letter on black sleeve.								

## Radial Lead Type



● Please refer to page 20 about the end seal configuration.

## Type numbering system (Example : 25V 10μF)



### ※ 1 Configuration

φ D	Pb-free leadwire Pb-free PET sleeve
3	CD
4 to 8	DD

※ 2 In case at φ 3 units, put [2] as size code.

## Dimensions

Cap.(μF)	V	4	6.3	10	16	25	35	50
Code		0G	0J	1A	1C	1E	1V	1H
1	010							4×5(3×5) 8.4(8.0)
2.2	2R2							● 4×5 13(10)
3.3	3R3					3×5 10	● 4×5 15(10)	4×5 17
4.7	4R7				3×5 10	● 4×5 16(12)	4×5 18	5×5 20
10	100		3×5 15		● 4×5 23(18)	5×5 27	5×5 29	6.3×5 33
22	220	3×5 19	● 4×5 28(21)	5×5 33	5×5 37	6.3×5 42	6.3×5 46	□ 8×5 52(48)
33	330	4×5 28	5×5 37	5×5 41	○ 6.3×5 49(43)	6.3×5 52	□ 8×5 62(52)	8×5 71
47	470	4×5 33	5×5 45	○ 6.3×5 52(43)	6.3×5 58	□ 8×5 70(62)	8×5 80	
100	101	5×5 56	○ 6.3×5 70(68)	□ 8×5 80(76)	□ 8×5 92(86)	8×5 110		
220	221	6.3×5 96	□ 8×5 110(90)	8×5 135				
330	331	8×5 145	8×5 170					
470	471	8×5 185						

Size φ3×5 is available for capacitors marked. "●"/ Size φ5×5 is available for capacitors marked. "○"  
Size φ6.3×5 is available for capacitors marked. "□" In such a case, [M][R] will be put at 2nd and 3rd digit of type numbering system.

Rated ripple current (mA rms) at 85°C 120Hz  
( ) = φ3 units and UMR.

## Frequency coefficient of rated ripple current

Frequency	50 Hz	120 Hz	300 Hz	1 kHz	10kHz or more
Coefficient	0.70	1.00	1.17	1.36	1.50

Please refer to page 20, 21, 22 about the formed or taped product spec.  
Please refer to page 4 for the minimum order quantity.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Nichicon:

[UMA1H0R1MDD](#) [UMA1H100MDD](#) [UMA1H100MDD1TP](#) [UMA1E3R3MCD2](#) [UMA1E470MDD](#) [UMA1H220MDD](#)  
[UMA1H2R2MDD](#) [UMA1HR33MDD](#) [UMA1V4R7MDD](#) [UMA1E4R7MDD](#) [UMA1H010MDD](#) [UMA1H4R7MDD](#)  
[UMA1HR22MDD](#) [UMA1V3R3MDD](#) [UMA1V470MDD](#) [UMA1H330MDD](#) [UMA1H3R3MDD](#) [UMA1V220MDD](#)  
[UMA1V2R2MCD2](#) [UMA1V330MDD](#) [UMA1HR47MDD](#) [UMA1V100MDD](#) [UMR1A470MDD](#) [UMR1C100MCD2](#)  
[UMR1C101MDD](#) [UMR1V330MDD](#) [UMR1V3R3MCD2](#) [UMR0J221MDD](#) [UMR1A101MDD](#) [UMR1H220MDD](#)  
[UMR1H2R2MCD2](#) [UMR0J101MDD](#) [UMR0J220MCD2](#) [UMR1E4R7MCD2](#) [UMR1C330MDD](#) [UMR1E470MDD](#)  
[UMA1H100MDD1TE](#) [UMA1H330MDD1TP](#) [UMA1E3R3MCD2TP](#) [UMA1H2R2MDD1TP](#) [UMA1V470MDD1TP](#)  
[UMA1H3R3MDD1TP](#) [UMA1H010MDD1TP](#) [UMA1E4R7MDD1TP](#) [UMA1HR47MDD1TP](#) [UMA1E330MDD1TP](#)  
[UMA1E470MDD1TP](#) [UMA1H4R7MDD1TP](#) [UMA1V100MDD1TP](#) [UMA1V3R3MDD1TP](#) [UMA1V330MDD1TP](#)  
[UMA1HR22MDD1TP](#) [UMA1V2R2MCD2TP](#) [UMA1H220MDD1TP](#) [UMA1V220MDD1TP](#) [UMA1H0R1MDD1TP](#)  
[UMA1HR33MDD1TP](#) [UMR1E470MDD1TE](#) [UMA1V4R7MDD1TP](#) [UMR1A101MDD1TE](#) [UMA1H4R7MDD1TE](#)  
[UMR1A101MDD1TP](#) [UMA1E470MDD1TE](#) [UMA1V4R7MDD1TE](#) [UMA1H010MDD1TE](#) [UMA1H3R3MDD1TE](#)  
[UMR1A470MDD1TP](#) [UMR1C101MDD1TP](#) [UMA1C4R7MDD1TP](#)