



Designed with unique compact housings and 20-1000 meters of fiber, these launch cables are perfect for eliminating dead zones in reflectometric tests using an OTDR. These launch cable also features the following:

- Compact housing and shoulder strap make this perfect for on-the-go use
- Steel, interlocked armor under the fiber jacket protects the fiber from accidental damage
- Polishing types are color coded for quick and easy identification of the launch cable
- Convenient magnet on bottom of housing allows for quick and easy mounting to fiber racks

SPECIFICATIONS	FLC-202	FLC-1001	FLC-1005	FLC-1006	FLC-1007	FLC-3501	FLC-3505
FIBER LENGTH	20 m	1000 m	1000 m	1000 m	1000 m	350 m	350 m
CONNECTOR TYPE	SC/APC, SC/APC	SC/UPC, LC/UPC	SC/APC, SC/UPC	SC/UPC, SC/APC	SC/UPC, LC/APC	SC/UPC, LC/UPC	SC/UPC, SC/APC
UPC #	810053352311	810053351871	810053351888	810053352380	810053352397	810053352298	810053352304
PRODUCT FAMILY SPECIFICATIONS							
INPUT/OUTPUT LENGTH	4.9 ft (1.5 m)						
MAX INSERTION LOSS @ 1310 NM	≤ 0.35 dB/km						
MAX INSERTION LOSS @ 1550 NM	≤ 0.22 dB/km						
MAX INSERTION LOSS @ 800 NM	≤ 2.50 dB/km						
MAX INSERTION LOSS @ 1300 NM	≤ 0.70 dB/km						
SM CONNECTOR INSERTION LOSS	≤ 0.1 dB						
MM CONNECTOR INSERTION LOSS	≤ 0.15 dB						
RETURN LOSS	RL ≥ 65 dB (APC); RL ≥ 55 dB (UPC)						



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Jonard Tools:

[FLC-1006](#) [FLC-1007](#) [FLC-202](#) [FLC-3501](#) [FLC-3505](#)