


**ASW-12**

**ASW-916**

Our **patented** speed wrenches are designed to get your job done more efficiently. This line of speed wrenches is made to work on splitters, F Connectors, and all 7/16" connections. These wrenches are made of chrome vanadium steel, chrome plated, and polished to a high gloss finish.

Speed heads make tightening and loosening quick and easy while the circular hole in the tool allows you to add this to your carabiner and/or tool belt.

SPECIFICATIONS	ASW-12	ASW-716	ASW-7916	ASW-916	ASW-R12	ASW-R716	ASWS-716	ASWS-R716
<b>WRENCH TYPE</b>	Speed	Speed	Speed	Speed	Combination, Ratcheting, Speed	Combination, Ratcheting, Speed	Speed	Combination, Speed, Ratcheting
<b>SIZE</b>	1/2" (12.7mm)	7/16" (11.11mm)	7/16" (11.11mm), 9/16" (14.29mm)	9/16" (14.29mm)	1/2" (12.7mm)	7/16" (11.11mm)	7/16" (11.11mm)	7/16" (11.11mm)
<b>HEAD ANGLE</b>	15 Degrees	15 Degrees	Patented open-ended head	15 Degrees	Patented open-ended head	Patented open-ended head	15 Degrees	Patented open-ended head
<b>MATERIAL</b>	Chrome Vanadium Steel	Chrome Vanadium Steel	Chrome Vanadium Steel	Chrome Vanadium Steel	Chrome Vanadium Steel	Chrome Vanadium Steel	Chrome Vanadium Steel	Chrome Vanadium Steel
<b>FINISH</b>	Polished Chrome Plating	Polished Chrome Plating	Polished Chrome Plating	Polished Chrome Plating	Polished Chrome Plating	Polished Chrome Plating	Polished Chrome Plating	Polished Chrome Plating
<b>LENGTH</b>	6-1/2" (165.1mm)	6-1/2" (165.1mm)	7-1/2" (190.5mm)	7-1/2" (190.5mm)	6-1/2" (165.1mm)	6-1/2" (165.1mm)	4" (100mm)	3 3/4" (95.25 mm)
<b>WEIGHT</b>	0.248 lbs (112.49g)	0.239 lbs (108.41g)	0.297 lbs (134.72g)	0.280 lbs (127.01g)	0.269 lbs (122.02g)	0.215 lbs (97.52g)	0.089 lbs (40.37g)	0.119 lbs (53.98g)
<b>UPC NO.</b>	811490011199	811490010680	811490012011	811490011205	811490012417	811490019652	811490016507	811490016491

**MADE FOR LIFE®**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Jonard Tools:

[ASW-R716](#) [ASW-R12](#) [ASW-12](#) [ASW-716](#) [ASW-916](#) [ASWS-R716](#) [ASWS-716](#)