

WB26SM - Wire Wrapping Bit, 26 AWG - Data Sheet

Fully compatible with any make or model wire wrapping tool. Gauge Size: 26 AWG. Wrap Type: Modified. Max Insulation Diameter “: 0.031. Minimum Terminal Diagonal “: 0.023. Max Terminal Diagonal “: 0.038. Terminal Hole Depth “: 0.75. Effective Radius “: 0.075. Terminal Hole Diameter “: 0.04. This tool is recommended for .025” square terminals on .100” center to center of the pins. Compatible Sleeve Part #: P26LN.



Specifications	
Wrap Function	Wrap
Wrap Type	Modified
Wire Gauge	26 AWG (0.40 mm)
Maximum Insulation Diameter	0.031” (0.79 mm)
Minimum Terminal Diagonal	0.023” (0.58 mm)
Maximum Terminal Diagonal	0.038” (0.96 mm)
Terminal Hole Depth	0.75” (19.05 mm)
Terminal Hole Dia.	0.040” (1.02 mm)
Effective Radius	0.075” (1.9 mm)
Wrap Post Size	0.025” (0.63 mm)
For Use With	.025” (0.63 mm) square terminals on .100” (2.54 mm) center to center of the pins.
Features	Provides 1.5 to 2 turns of insulation
Sleeve Part No.	P26LN (Sold Separately)
Length	3” (76.2mm)
Weight	0.052 lbs
UPC No	811490013056

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Jonard Industries:](#)

[WB26SM](#)