

Bi-Polarized, For Audio Equipment













- Suited for audio signal circuits.
- Compliant to the RoHS directive (2011/65/EU,(EU)2015/863).

Valued marked with an % in the dimension table are scheduled to be discontinued and are not recommended for new designs.






■ Specifications

Item	Performance Characteristics								
Category Temperature Range	-40 to +85°C								
Rated Voltage Range	6.3 to 50V								
Rated Capacitance Range	1 to 1000μF								
Capacitance Tolerance	±20% at 120Hz, 20°C								
Leakage Current ※	After 1 minute's application of rated voltage at 20°C, leakage current is not more than 0.03CV or 3 (μA), whichever is greater.								
	Measurement frequency : 120Hz at 20°C								
Tangent of loss angle (tan δ)	Rated voltage (V)	6.3	10	16		25		35	50
	tan δ (max.)	0.24	0.20	0.16		0.16	0.	14	0.12
	Measurement frequency : 120Hz								
	Rated voltage (V)		6.3	10	16	2	5	35	50
Stability at Low Temperature	Impedance ratio	Z(-25°C) / Z(+20°C)	4	3	2	2	2	2	2
	(max.)	Z(-40°C) / Z(+20°C)	8	6	4	4		4	4
Endurance	The specifications	Capacitance change Within ±20% of the initial capacitance value							
	capacitors are restored to 20°C after the rated voltage is applied for 1000 hours at 85°C with the polarity inverted every 250 hours.			tan δ		150% or less than the initial specified value			
				Leakage cur	rent	Less than or equal to the initial specified value			ecified value
Shelf Life	After storing the capacitors under no load at 85°C for 1000 hours and then performing voltage treatment based on JIS C 5101-4 clause 4.1 at 20°C, they shall meet the specified values for the endurance characteristics listed above.								
Marking	Printed with black color letter on clear green sleeve.								


※ I : Leakage Current (μA), C : Rated Capacitance (μF), V : Rated Voltage (V)

■ Radial Lead Type



• Please refer to the Guidelines for Aluminum Electrolytic Capacitors for end seal configuration information.

Type numbering system (Example: 10V 47µF)



UES

■Dimensions

Rated Voltage (V) (code)	Rated Capacitance (µF)	Case Size φD×L(mm)	tan δ	Leakage Current (µA) (at 20°C after 1 minute	Part Number
6.3 (0J)	33	5×11	0.24	6.237	*UES0J330MDM
	47	6.3×11	0.24	8.883	%UES0J470MEM
	100	8×11.5	0.24	18.9	UES0J101MPM
	220	10×12.5	0.24	41.58	UES0J221MPM
	330	10×16	0.24	62.37	UES0J331MPM
	470	10×20	0.24	88.83	UES0J471MPM
	1000	12.5×25	0.24	189	UES0J102MHM
	22	5×11	0.20	6.6	₩UES1A220MDM
	33	6.3×11	0.20	9.9	₩UES1A330MEM
	47	6.3×11	0.20	14.1	₩UES1A470MEM
10	100	10×12.5	0.20	30	UES1A101MPM
(1A)	220	10×16	0.20	66	UES1A221MPM
	330	10×20	0.20	99	UES1A331MPM
	470	12.5×20	0.20	141	UES1A471MHM
	1000	16×25	0.20	300	UES1A102MHM
-	10	5×11	0.16	4.8	**UES1C100MDM
	22	6.3×11	0.16	10.56	**UES1C220MEM
	33	6.3×11	0.16	15.84	**UES1C330MEM
	47	8×11.5	0.16	22.56	UES1C470MPM
16 (1C)	100	10×12.5	0.16	48	UES1C101MPM
(10)	220	10×20	0.16	105.6	UES1C221MPM
	330	12.5×20	0.16	158.4	UES1C331MHM
	470	12.5×25	0.16	225.6	UES1C471MHM
	1000	16×25	0.16	480	UES1C102MHM
	4.7	5×11	0.16	3.525	₩UES1E4R7MDM
	10	5×11	0.16	7.5	₩UES1E100MDM
	22	6.3×11	0.16	16.5	₩UES1E220MEM
25 (1E)	33	8×11.5	0.16	24.75	UES1E330MPM
	47	10×12.5	0.16	35.25	UES1E470MPM
	100	10×16	0.16	75	UES1E101MPM
	220	12.5×25	0.16	165	UES1E221MHM
	330	12.5×25	0.16	247.5	UES1E331MHM
	470	16×25	0.16	352.5	UES1E471MHM
	1000	16×30.5	0.16	750	UES1E102MHM
35 (1V)	4.7	5×11	0.14	4.935	**UES1V4R7MDM
	10	6.3×11	0.14	10.5	%UES1V100MEM
	22	8×11.5	0.14	23.1	UES1V220MPM
	33	10×12.5	0.14	34.65	UES1V330MPM
	47	10×12.5	0.14	49.35	UES1V470MPM
\ 1 ♥ /	100	10×20	0.14	105	UES1V101MPM
	220	12.5×25	0.14	231	UES1V221MHM
	330	16×25	0.14	346.5	UES1V331MHM
	470	16×25	0.14	493.5	UES1V471MHM

For cut leads, formed leads or taped parts, please add the appropriate code after the size code (12th digit). If there is no size code in the part number, please add size code "1" and then add the appropriate code.



■Dimensions

Rated Voltage (V) (code)	Rated Capacitance (µF)	Case Size φD×L(mm)	tan δ	Leakage Current (µA) (at 20°C after) 1 minute	Part Number
50 (1H)	1	5×11	0.12	3	*UES1H010MDM
	2.2	5×11	0.12	3.3	*UES1H2R2MDM
	3.3	5×11	0.12	4.95	*UES1H3R3MDM
	4.7	6.3×11	0.12	7.05	*UES1H4R7MEM
	10	8×11.5	0.12	15	UES1H100MPM
	22	10×12.5	0.12	33	UES1H220MPM
	33	10×16	0.12	49.5	UES1H330MPM
	47	10×20	0.12	70.5	UES1H470MPM
	100	12.5×25	0.12	150	UES1H101MHM
	220	16×25	0.12	330	UES1H221MHM
	330	16×30.5	0.12	495	UES1H331MHM

For cut leads, formed leads or taped parts, please add the appropriate code after the size code (12th digit). If there is no size code in the part number, please add size code "1" and then add the appropriate code.

[•] For formed lead or taped product specifications and minimum order quantity, please refer to the Guidelines for Aluminum Electrolytic Capacitors.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Nichicon:

```
UES0J101MPM UES0J102MHM UES0J221MPM UES0J330MDM UES0J331MPM UES0J470MEM
UES0J471MPM UES1A101MPM UES1A102MHM UES1A220MDM UES1A221MPM UES1A330MEM
UES1A331MPM UES1A470MEM UES1A471MHM UES1C100MDM UES1C101MPM UES1C102MHM
UES1C220MEM UES1C221MPM UES1C330MEM UES1C331MHM UES1C470MPM UES1C471MHM
UES1E100MDM UES1E101MPM UES1E102MHM UES1E221MHM UES1E330MPM UES1E331MHM
UES1E470MPM UES1E471MHM UES1E4R7MDM UES1H010MDM UES1H100MPM UES1H220MPM
UES1H221MHM UES1H2R2MDM UES1H330MPM UES1H331MHM UES1H3R3MDM UES1H470MPM
UES1H4R7MEM UES1V101MPM UES1V220MPM UES1V221MHM UES1V330MPM UES1V331MHM
UES1V470MPM UES1V471MHM UES1V4R7MDM UES1H101MHM UES1E220MEM UES1V100MEM
UES0J471MHM UES1H330MPM1TD UES1V101MPM1TD UES1A221MPM1TD UES1E100MDM1TD
UES1H470MPM1TD UES0J331MPM1TD UES1C470MPM1TD UES0J102MHM1TO UES1V330MPM1TD
UES1C331MHM1TO UES1A331MPM1TD UES1V4R7MDM1TD UES1H100MPM1TD UES1C221MPM1TD
UES1E101MPM1TD UES1C102MHM1TO UES1H3R3MDM1TD UES1C471MHM1TO UES0J101MPM1TD
UES0J221MPM1TD UES1A101MPM1TD UES1C100MDM1TD UES1C220MEM1TD UES1E220MEM1TD
UES1E221MHM1TO UES1E330MPM1TD UES1E4R7MDM1TD UES1H010MDM1TD UES1H220MPM1TD
UES1H4R7MEM1TD UES1V100MEM1TD UES1V220MPM1TD UES1V470MPM1TD UES1H101MHM1TO
UES1C101MPM1TD UES1A220MDM1TD UES1H2R2MDM1TD UES1E470MPM1TD UES1C330MEM1TD
UES1A470MEM1TD UES0J470MEM1TD UES1V221MHM1TO UES1A471MHM1TO UES1E331MHM1TO
UES0J330MDM1TD
```