

WB3032M - Wire Wrapping Bit, 30-32 AWG - Data Sheet

Fully compatible with any make or model wire wrapping tool. Gauge Size: 30-32 AWG. Wrap Type: Modified. Max Insulation Diameter “: 0.027. Minimum Terminal Diagonal “: 0.034. Max Terminal Diagonal “: 0.038. Terminal Hole Depth “: 0.75. Effective Radius “: 0.064. Terminal Hole Diameter “: 0.04. This tool is recommended for .025” square terminals on .100” center to center of the pins. Compatible Sleeve Part #: P3032.



Specifications

Wrap Function	Wrap
Wrap Type	Modified
Wire Gauge	30-32 AWG (0.25-0.20 mm)
Maximum Insulation Diameter	0.027” (0.69 mm)
Minimum Terminal Diagonal	0.034” (0.86 mm)
Maximum Terminal Diagonal	0.038” (0.96 mm)
Terminal Hole Depth	0.75” (19.05 mm)
Terminal Hole Dia.	0.040” (1.02 mm)
Effective Radius	0.066” (1.67 mm)
Wrap Post Size	0.025” (0.63 mm)
Features	Recommend for .025” square terminals on .100” center to center of the pins
Sleeve Part No.	P3032 and P3032INS (Sold Separately)
Length	3” (76.2mm)
Weight	0.048 lbs
UPC No	811490013124

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Jonard Industries:](#)

[WB3032M](#)