G6DN PCB Power Relay

SPST Slim Power Relay for 5 A switching

- Slim 5-mm width and miniature size. (20 × 5.08 × 12.5 mm)
- High switching capability 5 A (250 VAC and 30 VDC), and high contact reliability by crossbar-twin contact.
- Low power consumption 110 mW.
- Meets application standards EN61010-1 and EN61010-2-201 for reinforced insulation (CTI 600 V min. and Rated insulation voltage 300 V). (Except G6DN-1A-CF Models)
- · Actualize electrical durability 100 Kops (-L type)
- Lineup of high temperature types with an ambient temperature of 105°C (-CF type)

3. Enclosure Rating

Model Number Legend

Ordering Information

G6DN-00-00

- $\frac{1}{1} \frac{2}{2} \frac{3}{4} \frac{4}{5}$
- 1. Number of Poles
- 1: 1-pole
- 2. Contact Form A: SPST-NO (1a)

None: Fully sealed **4. Classification** None: Standard (E-LIFE 80 Kops) L: High durability type (E-LIFE 100 Kops) SL: General purpose

5. Coil Insulation Class None: Class B CF: Class F (High temperature)

Application Examples

- · Programmable Controller output
- Temperature Controller
- Building Automation
- · Output of control system

c¶us 🖳 🛕

Contact form	Enclosure rating	Terminal shapes	Model	Minimum packing unit	
	Fully sealed	PCB terminal	G6DN-1A	25 pag/ tuba	
			G6DN-1A-L	20 pcs/ tube	
3F31-NO (1a)			G6DN-1A-SL	100pcs/tray	
			G6DN-1A-CF		
	Contact form SPST-NO (1a)	Contact form Enclosure rating SPST-NO (1a) Fully sealed	Contact form Enclosure rating Terminal shapes SPST-NO (1a) Fully sealed PCB terminal	Contact form Enclosure rating Terminal shapes Model SPST-NO (1a) Fully sealed PCB terminal G6DN-1A-L G6DN-1A-L G6DN-1A-SL G6DN-1A-SL G6DN-1A-CF G6DN-1A-CF	

Note 1. When ordering, add the rated coil voltage to the model number. Example: G6DN-1A DC5

However, the notation of the coil voltage on the product case as well as on the packaging will be marked as Example: G6DN-1A 5VDC

Note 2. When placing an order, please specify the number in package multiples.

Ratings

Coil

		Rated current	Coil resistance	Must operate voltage (V)	Must release voltage (V)	Max. voltage (V)	Power consumption
Classification	Rated voltage	(mA)	(Ω)	% of rated voltage		(mW)	
4	4.5 VDC	24.4	184				
Standard	5 VDC	22.0	227		5% min.	160%	Approx 110
Stanuaru	12 VDC	9.2	1,309				Applox. 110
	24 VDC	4.6	5,236				
	5 VDC	36.0	139	70% max. *			
High durability	12 VDC	15.0	800				Approx. 180
	24 VDC	7.5	3,200				
	5 VDC	22.0	227				
General purpose	12 VDC	9.2	1,309				
	24 VDC	4.6	5,236				
	4.5 VDC	24.4	184				Approx. 110
High temperature	5 VDC	22.0	227	1			
	12 VDC	9.2	1,309				
	24 VDC	4.6	5.236	1			

Note. The rated current and resistance are measured at a coil temperature of 23°C with a tolerance of ±10%.

* Operating voltage is less than 72% when the relay is sideways and the marking is right way.

Contacts

G 6 D N

Item	Classification	Standard High durability General purpose		High temperature	
Load		Resistive load	Inductive load ($\cos \phi = 0.4$)(L/R = 7 ms)	Resistive load	Inductive load (cos ϕ = 0.4)(L/R = 7 ms)
Contact Type		Cross bar twin			
Contact material		Ag-Alloy and Au plating *			
Rated load 5 A a 5 A a		5 A at 250 VAC 2 A at 250 VAC 5 A at 250 VAC 1 A at 250 VAC 5 A at 30 VDC 2 A at 30 VDC 5 A at 30 VDC 2 A at 30 VDC			1 A at 250 VAC 2 A at 30 VDC
Rated carry current		5 A	L.		
Max. switching voltag	je	277 VAC, 125 VDC			
Max. switching currer	nt	5 A			

* Au plating is applied to stationary contact.

Characteristics

		Standard	High durability	General purpose	High temperature			
Contact resistance	*1	100 mΩ max.						
Operate time		10 ms max.						
Release time		5 ms max.						
Insulation resistance	e *2	1,000 MΩ min. (at 500 VDC)	1					
	Between coil and contacts	3,000 VAC, 50/60 Hz for 1 m	nin					
Dielectric strength	Between contacts of the same polarity	750 VAC, 50/60 Hz for 1 mir	0 VAC, 50/60 Hz for 1 min					
Surge withstand voltage	Between coil and contacts	6 kV (1.2 $ imes$ 50 μ s)						
Vibration	Destruction	10 to 55 to 10 Hz, 2.5 mm si	ngle amplitude (5.0 mm double	amplitude)				
resistance	Malfunction	10 to 55 to 10 Hz, 0.75 mm	single amplitude (1.5 mm doubl	e amplitude)				
Shock resistance	Destruction	1,000 m/s²						
Chock resistance	Malfunction 100 m/s ²							
	Mechanical	20,000,000 operations min.	(at 18,000 operations/hr)					
Durability	Electrical	100,000 operations min. (3 A at 250 VAC, 3 A at 30 VDC Resistive load) 80,000 operations min. (5 A at 250 VAC, 5 A at 30 VDC Resistive load) 100,000 operations min. (2 A at 250 VAC, 2 A at 30 VDC Inductive load)	100,000 operations min. (5 A at 250 VAC, Resistive load) 100,000 operations min. (5 A at 30 VDC, Resistive load) 200,000 operations min. (2 A at 250 VAC, Inductive load) 200,000 operations min. (2 A at 30 VDC, Inductive load)	50,000 operations min. (5 A at 250 VAC, Resistive load) 50,000 operations min. (5 A at 30 VDC, Resistive load) 100,000 operations min. (2 A at 250 VAC, Inductive load) 100,000 operations min. (2 A at 30 VDC, Inductive load)	10,000 operations min. (5 A at 250 VAC Resistive load 105°C) 100,000 operations min. (3 A at 250 VAC Resistive load 105°C) 10,000 operations min. (5 A at 30 VDC Inductive load 105°C) 100,000 operations min. (1 A at 250 VAC Inductive load 105°C) 100,000 operations min. (2 A at 30 VDC Inductive load 105°C)			
Failure rate (P level) (reference value *3)		0.1 mA at 0.1 VDC						
Ambient temperature	Operating	-40°C to +90°C (with no icing or condensation) -40°C to +105°C *4 (with no icing or conde			-40°C to +105°C *4 (with no icing or condensation)			
Humidity		5% RH to 85% RH						
Weight		Approx. 3 g						

Note. This value was measured at a switching frequency of 120 operations/min.

*1. Values in the above table are initial values.

*2. The contact resistance is measured with 1 A applied at 5 VDC using a fall-of-potential method.

*3. *4. The insulation resistance is measured between coil and contacts and between contacts of the same polarity at 500 VDC.

For installation, please see "Mounting" on page 6.

Engineering Data

Maximum Switching Capacity

• G6DN-1A, G6DN-1A-L, G6DN-1A-CF



Durability

•G6DN-1A, G6DN-1A-CF



Note. The durability curve is based on room temperature data.

Maximum Coil Voltage G6DN-1A, G6DN-1A-L, G6DN-1A-CF (%) 20 Maximum coil voltage 180 G6DN-1A-CF 160 140 120 100 80 G6DN-1A, G6DN-1A-L 60 40 20 0 10 20 30 40 50 60 70 80 90 100 110

•Ambient Temperature vs.

Ambient temperature (°C)

Note. The maximum coil voltage refers to the maximum voltage in a varying range of operating power voltage, not a continuous voltage.

 Ambient Temperature vs. Must Operate and Must Release Voltages G6DN-1A, G6DN-1A-L



G6DN-1A-CF



Shock Malfunction



Sample: G6DN-1A Number of Relays: 5 pcs Test conditions: Impose a shock in the $\pm X$, $\pm Y$, and $\pm Z$ directions three times each with the Relay energized to check the shock values that cause the Relay to malfunction. Standard:100 m/s²

CAD Data

Dimensions CAD Data Please visit our website, which is noted on the last page. **PCB Mounting Holes** Terminal Arrangement/ G6DN-1A(-L) 5.08 max. (5.05)* Internal Connections (Bottom View) 20 max. (19.97)* (Bottom View) ŧ ->+7.62±0.1 12.5 max (12.45)* Four, 1.1-dia. holes 2.54±0. 8 102 5 3.3 (No coil polarity) (1.32) -Two, 0.4-dia t 0.2 t 0.26 (1.28) 2-0.8 **⊷** (1.28) 7.62 7.62 2.54 - (1.32) CAD Data * Average value 5.08 max. (5.05)* PCB Mounting Holes Terminal Arrangement/ G6DN-1A(-SL)(-CF) 20 max. (19.97)* (Bottom View) Internal Connections (Bottom View) +7.62±0. → 7 62+0.1 Four, 1.1-dia. holes 12.5 max. 2.54±0.1 102 5 Г ₩ 3.3 2-t0.3 4 (1.32) t 0.26 t 0.2 (1.28) (No coil polarity) 2-0.5 2-0.8 **⊷** (1.28) 7.62 7.62 (1.32) 2.54

* Average value

■Approved Standards

•The rated values approved by each of the safety standards may be different from the performance characteristics individually defined in this datasheet.

UL/C-UL-approved models CNUs (File No. E41515)

Model	Contact form	Coil ratings	Contact ratings	Operations
			5 A at 277 VAC (Resistive) 95°C	6,000
			5 A at 30 VDC (Resistive) 90°C	6,000
			3A, 250V ac, Resistive 85°C	100,000
			1/10 hp 125 VAC 95°C	1,000
	SDST NO	4.5 to 24 VDC	1/10 hp 277 VAC 95°C	1,000
GODIN-TA(-SL)(-CF)	3231-110		D300 120 VAC/240 VAC 95°C	6,000
			C300 120 VAC/240 VAC 95°C	6,000
			R300 125 VDC/250 VDC 95°C	6,000
			5 A 250 VAC (Resistive) 105°C	10,000
			5 A 30 VDC (Resistive) 105°C	10,000
	SPST-NO	5 to 24 VDC	5 A 250 VAC (Resistive) 95°C	100,000
			2 A 250 VAC (General Use) 95°C	100,000
			2 A 30 VDC (General Use) 95°C	100,000
G6DN-1A-L			1/10 hp 120 VAC 40°C	6,000
			C300 120 VAC/240 VAC 95°C	6,000
			D150 120 VAC 95°C	6,000
			R150 125 VDC 95°C	6,000

Note. CSA certification CSA 22.2 No.14 can be recognized by C-UL.

VDE (EN61810-1) (Certificate No. 40042696)

Model	Contact form	Coil ratings	Contact ratings	Operations
		4.5, 5, 12, 24 VDC	5 A at 250 VAC (coso= 1.0) 90°C	10,000
GODIN-TA	3F31-NO		5 A at 30 VDC (L/R = 0 ms) 90°C	10,000
G6DN-1A-L	SPST-NO	5, 12, 24 VDC	5 A 250 VAC (coso= 1.0) 90°C	100,000
			2 A 250 VAC (coso= 0.4) 90°C	100,000
			2 A 250 VAC (coso= 0.6) 90°C	100,000
			5 A 30 VDC (L/R = 0 ms) 90°C	100,000
			2 A 30 VDC (L/R = 7 ms) 90°C	100,000

TÜV (EN61810-1) (Registration No. R 50396359)

Model	Contact form	Coil ratings	Contact ratings	Operations
G6DN-1A(-SL)(-CF) S	SPST-NO	5, 12, 24 VDC	5 A at 250 VAC (coso= 1.0) 90°C	10,000
			5 A at 30 VDC (L/R = 0 ms) 90°C	10,000
			5 A at 250 VAC (coso= 1.0) 105°C	10,000
			5 A at 30 VDC (coso= 1.0) 105°C	10,000

Clearance distance	3.5 mm min.
Creepage distance	3.6 mm min.
Type of insulation coil-contact circuit	Basic (PD.2)
open contact circuit	Micro disconnection
Rated Insulation voltage	300 V
Pollution degree	2
Rated voltage system	250 V
Over voltage category	II
Category of protection according to IEC 61810-1	RT III (Sealed)
Insulation material group	1
Tracking resistance according to IEC 60112	CTI 600 V min.
Flammability class according to UL94	V-0
Coil insulation system according to UL	Class B (Standard/High durability/General purpose)/Class F (High temperature)

Precautions

●Please refer to "PCB Relays Common Precautions" for correct use.

Correct Use

Mounting

When mounting a number of relays on a PCB in 90°C to 105°C, be sure to provide a minimum mounting space of 1.27 mm min. as shown below.



Please check each region's Terms & Conditions by region website.

OMRON Corporation **Device & Module Solutions Company**

Regional Contact Americas https://components.omron.com/us Asia-Pacific https://components.omron.com/ap Korea https://components.omron.com/kr

Europe https://components.omron.com/eu China https://components.omron.com.cn Japan https://components.omron.com/jp

© OMRON Corporation 2015-2023 All Rights Reserved. In the interest of product improvement, specifications are subject to change without notice.

Cat. No. K276-E1-10 1023 (1115)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Omron:

G6DN-1A-CF DC12 G6DN-1A-CF DC24 G6DN-1A-CF DC5 G6DN-1A-CF DC4.5