





DESCRIPTION: 9 POS - FEMALE - SURFACE MOUNT

MATERIAL/FINISH:

SHELL: STEEL, NICKEL PLATED
BRACKET: BRASS, NICKEL PLATED
INSULATOR: NYLON 6T-UL 94V-0, BLACK
PROCESS TEMP: 260° C
INSULATOR: PATONE #322C, COLOR = Pc99
CONTACT: PHOSPHOR BRONZE, TIN PLATED
GOLD FLASH - MATING AREA
TIN - TERMINATING AREA



ELECTRICAL:


RATED CURRENT: 5 AMPS
RATED VOLTAGE: 300VDC
WITHSTANDING VOLTAGE: 500VAC (rms) FOR 1 Min.
INSULATION RESISTANCE: > 1,000mOhms AT 500VDC
CONTACT RESISTANCE: 13mOhms Max.
DIELECTRIC STRENGTH: 1,000VAC FOR 1 MINUTE
OPERATING TEMPERATURE: -55° ~ +105° C

DO NOT SCALE FROM DRAWING

RoHS COMPLIANT


	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: C. SMITH		DATE: 03-30-09		
		SCALE: NTS		SHEET 1 OF 2		REV 14
		DWG NO. 190-009-263R001				

DESCRIPTION: 9 POS PCB LAYOUT - SURFACE MOUNT - FEMALE




RECOMMENDED PCB LAYOUT

CONTACT ARRANGEMENT
1 6 2 7 3 8 4 9 5




DETAIL "B"
CONTACT COPLANARITY

SEE DETAIL "B"
FOR CONTACT
COPLANARITY



DETAIL "A"



**NOTE:

RECOMMENDED PCB THICKNESS IS
0.063 [1.60] ± 0.002 [0.05] TO MAINTAIN
ANGLE TOLERANCE

DO NOT SCALE FROM DRAWING

	THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.	DRAWN: C. SMITH		DATE: 03-30-09		
NorComp		SCALE: NTS	SHEET 2		OF 2	REV 14
		DWG NO. 190-009-263R001				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NorComp:](#)

[190-009-263R001](#) [190-025-263R001](#)