

820K YYY - 1 7 3 L YY 1

SERIES
11.00 [0.433]

OF POSITIONS
(Ex. 002)
SEE CHART A

1 = MALE

CABLE MOUNT

1 = GOLD FLASH

COLLET SIZE
SEE CHART B

RoHS COMPLIANT

NICKEL/CHROME PLATED SHELL

CHARACTERISSTICS

MATERIALS

HOUSING : BRASS

HOUSING PLATING : 196µ" NICKEL MIN.

SHELL & COLLET NUT: BRASS, 196µ" CHROME PLATED MIN.

CONTACTS : COPPER ALLOY

CONTACT PLATING : 7µ" GOLD PLATED OVER 196µ" NICKEL MIN.

INSULATOR : PPS (HIGH TEMPERATURE)

STRAIN RELIEF(BOOT) : THERMOPLASTIC POLYURETHANE

O-RING: SILICONE

MECHANICAL

DURABILITY: 5000 CYCLES

OPERATING TEMP. RANGE: -40° C ~ +200° C

PROCESS TEMPERATURE : 260°C FOR 5 SECONDS

MAX. TOURQUE VALUE : 0.7 Nm [6.0 IN/LBS]

SHIELDING: 75dB @ 10MHz

40dB @ 1GHZ

IP RATING: 67




CHART B

COLLET SIZE	WIRE DIAMETER
30	2.50 [0.098] ~ 3.20 [0.126]
40	3.30 [0.130] ~ 4.20 [0.165]
50	4.30 [0.169] ~ 5.20 [0.205]

CHART A

● = KEY LOCATION **VIEW FROM TERMINATION END**

 2 POSITION 22 AWG MAX. 10 AMP MAX. PIN Ø = 0.90 [0.035] CONTACT RESISTANCE = 6 mΩ TEST VOLTAGE = 1000V WORKING VOLTAGE = 330V	 3 POSITION 22 AWG MAX. 8 AMP MAX. PIN Ø = 0.90 [0.035] CONTACT RESISTANCE = 6 mΩ TEST VOLTAGE = 1200V WORKING VOLTAGE = 400V	 4 POSITION 24 AWG MAX. 7 AMP MAX. PIN Ø = 0.70 [0.028] CONTACT RESISTANCE = 7.5 mΩ TEST VOLTAGE = 850V WORKING VOLTAGE = 280V	 5 POSITION 24 AWG MAX. 6.5 AMP MAX. PIN Ø = 0.70 [0.028] CONTACT RESISTANCE = 7.5 mΩ TEST VOLTAGE = 850V WORKING VOLTAGE = 280V	 6 POSITION 28 AWG MAX. 2.5 AMP MAX. PIN Ø = 0.50 [0.020] CONTACT RESISTANCE = 10 mΩ TEST VOLTAGE = 850V WORKING VOLTAGE = 280V	 7 POSITION 28 AWG MAX. 2.5 AMP MAX. PIN Ø = 0.50 [0.020] CONTACT RESISTANCE = 10 mΩ TEST VOLTAGE = 800V WORKING VOLTAGE = 260V	 9 POSITION 28 AWG MAX. 2 AMP MAX. PIN Ø = 0.50 [0.020] CONTACT RESISTANCE = 10 mΩ TEST VOLTAGE = 600V WORKING VOLTAGE = 200V
---	--	---	---	--	--	--

RoHS COMPLIANT

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

NorComp:

<u>820K003-173L301</u>	<u>820K009-173L301</u>	<u>820K006-173L401</u>	<u>820K004-173L501</u>	<u>820K007-173L501</u>	<u>820K006-173L301</u>
<u>820K003-173L501</u>	<u>820K005-173L501</u>	<u>820K005-173L301</u>	<u>820K003-173L401</u>	<u>820K002-173L501</u>	<u>820K002-173L301</u>
<u>820K005-173L401</u>	<u>820K004-173L301</u>	<u>820K009-173L401</u>	<u>820K009-173L501</u>	<u>820K004-173L401</u>	<u>820K006-173L501</u>
<u>820K007-173L301</u>	<u>820K002-173L401</u>	<u>820K007-173L401</u>			