


GU140X32F-7003B

SIMPLIFIED DATASHEET

■ Features

4 line simultaneous display capable wide screen VFD module. Same size and shape as LCD, for easy drop-in replacement. 3.3V power model and reduced-size PCB slim-type models are also available.

■ Physical dimension



Specifications

■ Electrical Ratings

Parameter	Symbol	Min.	Typ.	Max.	Unit	Condition
Power supply voltage	VCC	4.75	5.00	5.25	VDC	-

■ Electrical Characteristics

Parameter	Symbol	Min.	Typ.	Max.	Unit	Condition
'L' Logic Input Current SIN, SCK, /CS, /RESET	IIL	-	-	-0.6	mA	VIN=0V
'H' Logic Input Current SIN, SCK, /CS, /RESET	IIH	-	-	1.0	μA	VIN=5V
Logic Input Voltage SIN, SCK, /CS, /RESET	VIH	0.8VCC	-	VCC	VDC	-
Logic Input Voltage SIN, SCK, /CS, /RESET	VIL	0	-	0.2VCC	VDC	-
Logic Output Voltage SBUSY	VOH	3.8	-	VCC	VDC	IOH=-1.5mA
Logic Output Voltage SBUSY	VOL	0	-	0.6	VDC	IOL=1.6mA
Power Supply Current 1	ICC-1	-	400	520	mADC	All dots ON
Power Supply Current 2	ICC-2	-	330	430	mADC	All dots OFF
Power Supply Current 3	ICC-3	-	35	45	mADC	Display power OFF
Power Consumption		-	2.0	2.6	W	All dots ON

■ Optical Specifications

Parameter	
Luminance	350 cd/m ² Min. (700 cd/m ² Typ.)
Color of illumination	Green (Blue-Green)

■ Environmental Specifications

Parameter	
Operating Temperature	-40 ~ +85 degrees celsius
Storage Temperature	-60 ~ +85 degrees (Under 168 hours)/-40 ~ +85 degrees (Or more)
Operating Humidity	20 ~ 80% R.H. (non-condensing)
Storage Humidity	20 ~ 80% R.H. (non-condensing)
Vibration (non-operating)	10-55-10Hz, all amplitude 1mm, 30 minutes, X-Y-Z
Shock (non-operating)	392m/s ² (40G) 9ms X-Y-Z, 3 times each direction

■ Physical Specifications

Parameter	
Number of Dots	4,480 (140 x 32)
Display Area	69.85mm x 21.61 mm
Dot Size (X x Y)	0.35 mm x 0.53 mm
Dot Pitch (X x Y)	0.50 mm x 0.68 mm
Weight	About 60 g

■ Interface

Sync/Asynchronous Serial, SPI(CMOS)

■ Pin Assignment

(Synchronous)

Pin No.	Signal
1	VCC
2	SIN
3	GND
4	SBUSY
5	SCK
6	/RESET
7	NC

(SPI)

Pin No.	Signal
1	VCC
2	SIN
3	GND
4	SBUSY
5	SCK
6	/RESET
7	/CS

(Asynchronous)

Pin No.	Signal
1	VCC
2	SIN
3	GND
4	SBUSY
5	NC
6	/RESET
7	NC

Baud Rate Setting

9600bps
19200bps
38400bps*
115200bps
(*:Default setting)

■ Selectable Font

Parameter		*ANK(Alphabet, Numeric, Kana)
Character font type	5 x 7	ANK, International
Character width	Fixed/Proportional character format 1&2	
Character numbers	20 x 4 by 5 x 7 dot ASCII	
	23 x 4 by 5 x 7 dot Proportional	

■ Functions

Parameter
Control command
Scroll display action
Proportional Font function
User-Windows function
AND/OR/XOR Mixture display
Reverse display
Dot unit real-time bit image display
Download character function
Font Magnification function
etc.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Noritake:](#)

[GU140X32F-7003B](#)