

# CRYSTAL TEST & BURN IN SOCKET

AXS-1147-02-02

Precision test socket for 11.4 x 4.7mm,  
2 pad crystal packages.



**RoHS**  
Compliant




## FEATURES:

- Accurate and reliable testing of frequency control devices
- Contact force ideal for avoiding measurement error
- Highest quality socket available
- Clam shell design for easy open and close
- Reliable gold plated POGO pins
- Suitable for high temperature burn-in test
- Operating Temperature: -30 ~ +150°C


## APPLICATIONS:

- Design stage component engineering evaluation
- Supplier comparison tests
- High temperature burn-in board testing
- Prototyping


## SIDE VIEW (OPEN):




## POCKET TOP VIEW:



## END VIEW:



## SUITABLE CRYSTAL PACKAGE DIMENSIONS:



Dimensions: mm

## ORDERING INFORMATION:

When ordering, please refer to part number

**AXS-1147-02-02**

## RECOMMENDED FOR USE WITH DEVICE PACKAGE DIMENSIONS:

**11.4 x 4.7 x 4.2 to 5.5mm**


## COMPATIBLE ABRACON SURFACE MOUNT CRYSTAL:

### ABLS Series

(for a pdf download go to [www.abracon.com/Resonators/ABLS.pdf](http://www.abracon.com/Resonators/ABLS.pdf))

*\* ABRACON test and burn in sockets are compatible with all industry standard frequency control packages.*

ABRACON IS  
ISO 9001 / QS 9000  
CERTIFIED



**ABRACON**  
CORPORATION

Visit [www.abracon.com](http://www.abracon.com) for Terms & Conditions of Sale **Revised: 08.21.09**  
30332 Esperanza, Rancho Santa Margarita, California 92688  
tel 949-546-8000 | fax 949-546-8001 | [www.abracon.com](http://www.abracon.com)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ABRACON:](#)

[AXS-1147-02-02](#)